
Two layers of overpressure protection? You can't afford not to.



FISHER*

Protecting your gas distribution systems is paramount. While a single level of overpressure protection is required for a North American gas distribution operator, a 2 level protection approach is gaining importance for the reassurance that your customers and assets are completely protected.

Customer Overpressure Protection

To meet unique customer requirements Emerson has designed solutions with the following options for overpressure protection:

- Next generation in True-Monitor™ Protection
- Enhanced slam-shut capability
- Improved internal relief valve
- The evolution of Secondary Seat[™] Protection combined with internal relief

Engineered with robustness and safety in mind the Commercial Service Regulator family is a unique modular design offering:


- Easy product sizing and selection
- Broad platform, wide application coverage
- Reduced inventory through shared parts
- Reduced training and maintenance through streamlined design



Customized safety options to match your unique requirements

True-Monitor™ Protection

- Combines the operation of a conventional two regulator wide-open monitor set into one body.
- Multiple body sizes to fit new and replacement applications.
 Will still protect the system in the event of a lever disconnect of one device.



Internal Relief

- Full capacity internal relief supplements any secondary overpressure protection devices.
- Balanced or Unbalanced trims.




Slam-Shut Capability

- Discontinues gas service by shutting the gas off if there is an overpressure or underpressure condition.
- Reduced training and maintenance through streamlined design.



Secondary Seat™ Protection

- Provides overpressure protection in case of lockup failure of the primary orifice and seat.
- External, internal or dualregistration for flexible skid and field installation.





Emerson Automation Solutions

Americas

T +1 800 558 5853 T +1 972 548 3574

Europe

T+39 051 419 0611

Asia Pacific T +65 6777 8211

Middle East / Africa T +971 4811 8100

- webadmin.regulators@emerson.com
- Q Fisher.com
- Facebook.com/EmersonAutomationSolutions
- in LinkedIn.com/company/emerson-automation-solutions
- Twitter.com/emr_automation



The distinctive swirl pattern cast into every actuator casing uniquely identifies the regulator as part of the Fisher™ brand Commercial Service Regulator family and assures you of the highest-quality engineering, performance, and support traditionally associated with Fisher™ and Tartarini™ regulators. Visit www.fishercommercialservice.com to access interactive applications.

