

Discontinued and Limited Use Products

Control Valves, Actuators, Accessories, and Instruments

In keeping with Emerson's commitment to continually improve our products, streamline our portfolio, and focus our resources on technologies with the highest customer value, it is inevitable that there are products from the Fisher™ portfolio that have been discontinued since the business was founded in 1880.

This bulletin contains both discontinued and limited availability products. Service and parts may continue to be available once a product has been discontinued, but planning should begin replacing the product with an active product model. This is not a complete list of discontinued products but a representation of those more recent or more popular configurations.

If the discontinued product you are looking for is not listed, visit [Emerson.com](https://www.emerson.com) or contact your [Emerson sales office](#) for more information.

Limited Availability Products

Limited use products are not generally available for sale but are supported under specific restricted circumstances. These products are typically only sold as direct replacements to an existing installation. In this case, provide the serial number to be duplicated to your Emerson sales office for a quote and lead time. Other conditions of sale are listed in Table 1 below.

Discontinued Products

The discontinued products in Table 2 are no longer available for purchase. Recommended spare parts are typically available for 10 years after the last production on manufactured trim replacement parts and 5 years of best effort on die cast parts, elastomers, buyout components, and electronic components. After that time, service and parts for the discontinued products will be limited. Provide your [Emerson sales office](#) with existing process conditions to receive a quote for a suitable replacement product.

Limited Availability Products

These products are supported with specific restrictions on availability. In all situations other than those listed in Table 1, the product is discontinued and no longer available for sale. The replacement product listed should be evaluated for acceptance in the application prior to selecting the discontinued product for continued use even when the restrictions for use are met. Work with your [Emerson sales office](#) to determine the best replacement for these products based on your current process conditions.

Table 1. Limited Availability Products

Limited Availability Product	Description	Preferred Product	Restrictions on Use
470, 471, 472, 473 series	Pneumatically operated piston actuator	657/667, 585C	Nuclear replacements only
546	Electro-pneumatic transducer	---	Nuclear Replacements only
657-8	657 actuator; long stroke with clevis style connection	---	Nuclear replacements only
1052, size 20 - 60	Spring and diaphragm rotary actuator	2052	Nuclear replacements only after application review
1069	Pneumatic-piston rotary actuator	---	Application Review required
1073, 1074		1077, 1078, 1079	Nuclear replacements only
2506R, 2516FR, 2506R	Receiver/controller	---	
4211	Position transmitter	---	Nuclear replacements only
6014 (Diffuser)	WhisperFlo™ vent diffuser for aerodynamic noise control	---	
7600	Butterfly valve	8580, A11	Direct replacement is allowed for CL600+ only if application cannot be met with another butterfly product. Nuclear replacements.
7700	Butterfly valve	8560 & 8510B	Nuclear replacements only
7800	Butterfly valve	None	Nuclear replacements only
8510	Butterfly valve	8532	14 to 24-in. European requirements only
8510B	Butterfly valve	8580	PN 63 and PN 100 ratings only

Limited Availability Product	Description	Preferred Product	Restrictions on Use
8560	High-performance butterfly valve	8580	NACE metal seal, Fire Safe seal, or CL VI metal seal only
9100	Butterfly valve	8510B & 8560	Nuclear European use only 14 to 20-in.
9200	Butterfly valve	8510B & 8560	Nuclear replacement only
A Single port (25 to 300 mm)	General purpose globe valve, single port	GX, easy-e™	Part of a licensed process, nuclear replacement
A Single port (50 to 400 mm)	General purpose globe valve, single port	easy-e	Part of a licensed process, nuclear replacements
A Double Port, 2 through 16 in. / 50 through 400 mm	General purpose globe valve, double port	---	
A31A	High-performance butterfly valve	8580, 8532	Nuclear applications with EPDM seal rings
A31D	Double-flanged body casting based on A31A platform	8580, 8532	Double flanged cryogenic applications
A41	High-performance butterfly valve	8580	Nuclear applications with EPDM seal rings
AA, AA Spec E	Standard angle body	EA	For non-EA applications only
AC (size 10-in. only)	High-pressure globe style body with piston - balanced valve plug	ET	Nuclear replacements only
Baumann™ TX-450E	Electronic modulating actuator	None	Direct replacements only
Cavitrol™ V trim	Trim for V100 or U ball valve body	Cavitrol Hex trim	Nuclear replacements only
CCV-E	Fuel control valve with special trim for linear flow characteristic and efficient downstream static pressure recovery.	None	Direct replacements only
CVP	Steam pressure reducing/vent valve	Angle PRV	Direct replacement only when required by application
CVS-A, CVS-C	Steam conditioning valve	TBX, PRV w/ Desuperheater	Direct replacement only when required by application
CVS-E	Steam conditioning valve	CVX	Direct replacement only when required by application
CVX-A, CVX-AA	Steam conditioning valve	TBX, PRV w/ Desuperheater	Direct replacement only when required by application
CVX-AY	Steam conditioning valve	Globe PRV w/ Desuperheater	Direct replacement only when required by application

Limited Availability Product	Description	Preferred Product	Restrictions on Use
CVX-C, -CA	Steam conditioning valve	TBX, PRV w/ Desuperheater	Direct replacement only when required by application
CVX-CY,-CZ	Steam conditioning valve	Globe PRV w/ Desuperheater	Direct replacement only when required by application
CVX-P	Steam conditioning valve	Angle PRV	Direct replacement only when required by application
DB	---	HP, EH	Nuclear replacements only
DBQ, DBAQ	---	HP, EH, Gulde 1089	Nuclear replacements only
E High Pressure	---	HP & EH	Nuclear replacements only
EHP	---	C-Seal	Nuclear replacements only
EL, ELD, ELS, ELT	---	EU & EW	Direct replacements only
ENA	Class 900 nuclear feedwater valve similar to E valve	---	Nuclear only
EP, EAP, EWP	---	easy-e or EW w/C-Seal	Nuclear replacements only
Lever-Lock Hand lever Actuators	---	None	Nuclear replacements only
HS & HSV	---	EH	Nuclear replacements only
HSY, HSY Y	Class 1500 body with stud bolting on bonnet and bottom flange	None	Application review required
HVP	High-viscosity control valves	None	Direct replacements only
Series M	Manual gear for 7600 butterfly valve	None	Direct replacements mounted on 7600 only
SS-117	Globe valve body with seal weld - balanced Class 1500 - High Pressure E	None	Nuclear replacements only
SS-108	Buttwelding end stainless steel angle valve with Cavitrol III trim	None	Nuclear replacements only
SS-113	Globe valve body with bellows seal weld - unbalanced Class 600	None	Nuclear replacements only
SS-114	Globe valve body with bellows and seal weld - unbalanced Class 1500 - High Pressure E	None	Nuclear replacements only
SS-115	Globe valve body with bellows and seal weld - unbalanced Class 1500 - High Pressure E	None	Nuclear replacements only

Limited Availability Product	Description	Preferred Product	Restrictions on Use
SS-116	Globe valve body with bellows and seal weld - unbalanced Class 1500 or 2500 - DBQ	None	Nuclear replacements only
SS-118	Globe valve body with seal weld - unbalanced Class 1500 - DBQ	None	Nuclear replacements only
SS-127	Balanced globe valve with seal weld seat ring	None	Nuclear replacements only
SS-200	Balanced Vee-Ball™ valve for nuclear service	None	Nuclear replacements only
SS-254	A31A/A11 with double offset for nuclear service	None	Nuclear replacements only
SS-256	High-temperature Bi-directional TCM seal for V150, V200 or V300 Vee-Ball platform	None	Application review required
SS-271	High-temperature gas damper assembly based on 7600 valve design	None	Application review required
SS-77	High-pressure cryogenic valve body	None	Application review required
SS-79	Class 1500 E body	None	Nuclear replacements only
SS-85	3 position, 3-way aeration valve with manual operator for secondary water treatment	None	Direct replacements only
SS-91	1-in. high-pressure DBQ with extension bonnet for cryogenic service	None	Application review required
SS-92	3-in. Class 900 YD three-way valve	None	Direct replacements only
SS-93	8-in. Class 600 high-temperature valve	None	Direct replacements only
SS-97	Class 1500 welding end Vee-Ball valve for slurry service	None	Direct replacements only
SS-98	10-in. Class 2500 three-way valve	None	Direct replacements only
U (4, 6, 8, 10, 12-in)	Segmented ball valve	V150	Direct replacement of high chrome iron and nuclear only
U (16 & 24-in)	Segmented ball valve	V150	Nuclear replacements only
Y, YY	---	YD, YS	Greater than 150 mm only

Discontinued Products

These products are not available for sale. If a direct replacement is available, it has been listed here. Work with your Emerson sales office to review alternate current products to meet your application needs based on your existing process conditions.

Table 2. Discontinued Products

Discontinued Fisher Product	Description	Date Discontinued (if available)	Recommended Replacement (Fisher branded unless otherwise noted)
7 Series, 8 Series	Lever actuators	2000-2006	None
7 EHO, 7S, 8S	Electromechanical actuators	2000-2006	ACT Buyout
125	Compact, reversible diaphragm actuator for oil and gas industries	---	357
126, 127, 128 Series	Yokeless diaphragm actuator	1991 - 2002	D2T, D3, D4
169A & 169AS	Electro-pneumatic switch	---	None
249A	Level-Trol displacer sensor (cast iron cage, 25 in. displacer)	---	249B
249PT	Fabricated Level-Trol unit for top mounting using a TFE lined 3-in. tee	---	None
249V	Cast Level-Trol unit for side mounting	2009	249VS
249VT	Fabricated Level-Trol unit for side mounting. TFE-lined tee is not furnished	---	None
259B	Fabricated steel cage for Level-Trol pilots	---	249B
273	Internal tank float control unit with brass packing box	---	249 Series
279V, 279VB, 279VBU	Side-mounted level control sensor	---	None
304 Series	Electrical position switch	2009	4400
314, 315	Hydraulic snubber for 657 diaphragm actuator	2003	None
320, 321, 323, 329	Electro-hydraulic actuator	2001	ACT Buyout
330SA	Servo actuator	2001	None

Discontinued Fisher Product	Description	Date Discontinued (if available)	Recommended Replacement (Fisher branded unless otherwise noted)
346, 347	Electro-hydraulic actuator	---	ACT Buyout
350, 352, 353, 354	Electro-hydraulic control valve actuator	---	ACT Buyout
357	Oilfield dump valve	2003	D3, D4
364, 365	Electro-hydraulic actuator	---	ACT Buyout
421, 422, 424	Spring-return piston actuator	---	None
475, 476	Pneumatically operated piston actuator	2000	585C
477	High temperature, spring return piston actuator	---	None
478	470 actuator with clevis type stem connection	2001	1061
490, 491, 495	Pneumatic piston actuator	2000	685, 785C
494, 496, 498	Pneumatic piston actuator	---	None
513	Reversible diaphragm actuator sizes 20 and 32	1996	Baumann Spring & Diaphragm Actuator
528TY	Three-way valve body and actuator	---	None
529	34 sq. in. spring and diaphragm actuator	2005	GX
551	Electro-hydraulic transducer	2006	None
570, 571, 572, 573, 570S, 573S	S body (boot style pinch valve) and associated actuators	---	None
585 (Size 100), 585R	Piston actuator (spring open)	2003	657, 667, 585C
585CLS	Pneumatic piston actuator with long stroke capability	---	785C
603	Pump governor actuator	2009	None
607	Lever valve actuator	---	None
608	Heavy duty lever valve actuator	---	None
610	Lever and weight actuator	---	None
617 & 618	Float valve actuator	2005	None
643	Differential pressure pump governor actuator	---	None

Discontinued Fisher Product	Description	Date Discontinued (if available)	Recommended Replacement (Fisher branded unless otherwise noted)
650, 651, 652	Hydraulic valve	1998	None
658 Series	Diaphragm or piston lever actuator with bracket, lever connects below 657 or 470 actuator	---	None
688	Lever and weight diaphragm actuator	---	None
864	Pneumatic long-stroke cylinder actuator	---	None
1004, 1005, 1006, 1009	Manual actuator	---	None
1018S	Sliding-stem control valve	2004	GX
1031	Piston rotary actuator with scotch yoke	2001	G Series
1032	Piston rotary actuator with rack-and-pinion	2004	ACT Buyout
1033	Fire-Sentry fail-safe gear actuator	2005	None
1035	Rack-and-pinion rotary actuator. (Double-acting and spring-return)	2014	Bettis RPE
1051	Spring-and-diaphragm rotary actuator	---	2052
1065	Electro-hydraulic rotary actuator	---	ACT Buyout
1063, 1064, 1066, 1066SR	On/off piston rotary actuator	2014	Bettis RPE
1075, 1076, 1079	Manual gear actuator for rotary valves	---	
1082, 1083	Hand lever actuator (for rotary valve)	---	None
1100 Series	Sliding-stem control valve	2015	easy-e
1250, 1250R	Spring-and-diaphragm actuator (direct-acting)	2001	GX
2390/2390B	Liquid level transmitter	2000	DLC3100

Discontinued Fisher Product	Description	Date Discontinued (if available)	Recommended Replacement (Fisher branded unless otherwise noted)
2602	Reverse-acting air relay	---	None
2680-268T	Oilfield level controller	2002	L2
3024C, 3024S	Spring-and-diaphragm actuator	2004	GX
3025 size P462, P900, P460-200	Spring-and-diaphragm actuator	---	3025 size 1 and 2
3575	Electro-hydraulic positioner used on 320 Series electro-hydraulic actuator	2006	None
3576, 3577	Pneumatic valve positioners with one relay, monitors input signal and relay output pressures	2005	None
3579	Solenoid manifold assembly for 479 and 489 actuators	---	None
3580	Valve positioner	---	3582
3583	Valve stem motion transmitter (with pressure gauges) replaces 3581 transmitter	2019	None
4150, 4160 Series	Wizard II pressure controller	2003	4190 Series, C1, or DPC2K
4200 Series	Position transmitter	2025	4400
4300 Series	Position transmitter	2022	4400
6000 Silencers	In-line downstream silencer - horizontal	---	None
6020 Silencers	In-line upstream silencer - horizontal	---	None
8500, 8501	High performance butterfly valve	---	None
8510 (NPS 3-12, 30, 36)	High performance butterfly valve	1996	8580
8511, 8515, 8516	High performance butterfly valve	---	8580
8555, 8556	High performance butterfly valve	---	8580
8570, 8570A, 8570B	Fire-qualified high performance butterfly valve	---	8560
9000	Continental butterfly valves	2005	
9280	Butterfly valve	---	

Discontinued Fisher Product	Description	Date Discontinued (if available)	Recommended Replacement (Fisher branded unless otherwise noted)
9400	Butterfly valve	---	
9710	Butterfly valve nitrile, viton, and EPDM lined	---	None
A Double Port (NPS 1 and 1-1/2; 25 and 40 mm)	General purpose globe valve, double port	---	easy-e
A21	High performance butterfly valve	---	
A31A	High performance butterfly valve	2002	8532/8580
A41	High performance butterfly valve	---	8580
A61D	On/off butterfly valve	2002	8532/8580
A81	High performance butterfly valve	2015	8580
AA Spec C, F	Standard angle body	---	EA
AC (except NPS 10)	High-pressure globe style body with piston-balanced valve plug	---	ET
AP, AQR, AR, ARS	Large, high capacity, general purpose, reverse-acting control valve body	---	easy-e
AS	Steam dump valve using two actuators	---	easy-e
AV	A body with heavy duty guiding and V-slot seat rings	---	easy-e
B	Bar stock globe valve	---	Baumann 24000SB
B21, B21A	High performance butterfly valve	1996	8532/8580
BA	Bar stock angle body	---	None
Baumann 10	Spring and diaphragm rotary actuator for the 42000	2009	None
Baumann 25	Spring and diaphragm rotary actuator for the 42000	2009	None
Baumann 54R	Spring and diaphragm rotary actuator, nominal effective area 54 square In.	2009	None
Baumann 863-1	Baumann Electro-pneumatic single-acting positioner	2009	3661

Discontinued Fisher Product	Description	Date Discontinued (if available)	Recommended Replacement (Fisher branded unless otherwise noted)
Baumann 865-1	Baumann Pneumatic single-acting positioner	2009	3660
Baumann 21000	Elastomer lined butterfly control valve	2009	None
Baumann 25000	Low torque and low noise butterfly control valve	- - -	None
Baumann 42000	Rotary eccentric plug control valve	2009	None
Baumann 84000BR	Baumann Back pressure regulator	2010	Sanitary regulators
Baumann 86000	Corrosion resistant control valve	2009	None
Baumann 88000	Control valve	2009	None
Baumann 96000	Sanitary pneumatic pressure controller	2009	None
Baumann MV - Jordan, VA - Jordan	Electronic modulating actuator	- - -	None
Baumann NV Series Electric Actuator	Electric actuator	- - -	Baumann SV Series electric actuator
Baumann Resistance Plate Multi-Port	- - -	2010	None
BF, BFC	Bar stock or investment cast body with quick change trim (Class 150)	2001	easy-e sliding-stem control valve
BP	Plastic bar stock body	- - -	None
BV500	Rotary eccentric plug control valve	2009	V500, Vee-Ball rotary control valve
C	Forged steel high pressure body	- - -	None
Cavitrol I	Trim for E-Body	- - -	
CC	High-pressure angle body with special rating above Class 2500	2001	EH
CE	Globe valve body (single seated stem guided)	1996	GX
CP	General and chemical Service globe valve with integral flanges, stem guiding, clamped-in seat rings, and quick-change trim	2005	GX, easy-e

Discontinued Fisher Product	Description	Date Discontinued (if available)	Recommended Replacement (Fisher branded unless otherwise noted)
CVG	Specialty control valves	2001	Globe PRV
CVX-S	Steam conditioning valve	2004	TBX-S, 6010, 6011, Whisper™ Disk
CZA	Cryogenic globe valve	2002	None
D2	Control valve for oil and gas industry	2015	D2T
DH, DHY	Class 1500 single-port globe valve & three-way body for dehydration service	- - -	None
DLC3010	Digital level controller for mounting on Fisher 249 displacer cages	2022	DLC3100
DN, DNY	Class 900 single-port globe and three-way valves for dehydration service	- - -	None
DS, DSE	Class 600 single-port globe body for dehydration service	2002	ED, ET
DSV	High-performance e-disc digester switching valve	2020	8580/8532
DVC5000 Series	Digital valve controller	2003	DVC7K or DVC6200
DVC6000 Series ⁽¹⁾	Digital valve controller	2013	DVC7K or DVC6200
DVC6200 HW1	Digital valve controller	2022	DVC7K or DVC6200
DVG, DVG/AF	Variable geometry desuperheater	2012	DFA
DVG-RSH	Desuperheater	2000	DFA, DMA, DMA/AF, DMA/AF-HTC
DY	Class 600 three-way body for dehydration service	- - -	None
EAB	Cageless E angle-style valve	2001	None
EC, EAC	Single-seated E body & Angle-body for hard-to- handle fluids	- - -	None
ED Class 900-2500, NPS 6 and smaller	High pressure E body with balanced plug	- - -	HP
EF, EF-M	Single-seated E valve	- - -	None
1. Does not include DVC6005, DVC6015, DVC6025, and DVC6035. These products are still Active.			

Discontinued Fisher Product	Description	Date Discontinued (if available)	Recommended Replacement (Fisher branded unless otherwise noted)
EHAD, EHAS, EHAT 1 to 8 in. CL 1500 & 1500 intermediate rated	High-pressure angle valve body (balanced, high temperature)	2012	HPAD, HPAS, HPAT
EHD, EHS, EHT 1 to 8 x 6 in. CL 1500 & 1500 intermediate rated	High-pressure globe valve body	2003	HPD, HPS, HPT
EJ/EWJ	High-temperature, low-leakage, balanced E globe valve	---	ED Multi Ring
EK & EKR	Soft-seat DE body with balanced plug	2000	ET, EZ
ESR	Reverse-acting single-ported E body	2000	easy-e, EDR, ETR
EST	---	---	None
EU, 12 to 20 in.	E valve, 12 and larger with ANSI Class 600 rating	---	Large E
EWB	Cageless E reduced-trim globe valve	---	None
F & FA	Forged steel globe body, 6000 lb.	---	None
FBG	Fabricated globe-style valve with cage-guided trim	---	Large ET/ED
FBS	Unbalanced FB body	---	None
FG	Class 1500 globe body with Cavitrol IV and trim	---	Cav4
FSV	Stop isolation valve	2004	None
FY	Three-way, three-position steel body	---	None
GL, GS	Single port globe valve	2001	24000, GX
Gulde 1011, 1013	---	prior to 2015	easy-e or EH
Gulde 1012	---	---	EH
Gulde 1018	---	2004	GX or easy-e
Gulde 1019, 1088	---	---	EA
Gulde 1021	---	---	easy-e
Gulde 1030	---	---	easy-e

Discontinued Fisher Product	Description	Date Discontinued (if available)	Recommended Replacement (Fisher branded unless otherwise noted)
Gulde 1035	---	---	HP/EH
Gulde 1040	---	---	YD/YS/GX
Gulde 1042	---	---	None
Gulde 1045	---	---	YD/YS up to PN100
Gulde 1051	---	---	EA or HPA
Gulde 1065, 1070/1072	---	---	HPA
Gulde 1075, 1076, 1078, 1080, 1081/1083, 1089	---	2004	None
Gulde 1162	---	---	ET-C
Gulde 1163, 1215, 1500	---	---	None
Gulde 1210	---	---	Vee-Ball
Gulde 2016, 2101, 3026, 3027, 3030	---	prior to 2019	None
Gulde 3024	---	2004	None
GY	Three-way G body	---	None
H, HH, HD	Class 1500 steel body, single or double port	---	None
HC, HCB	4000 psi to 10,000 psi single port angle body for heater choke service	---	None
HSC, HSQ, HSS	HS body with cage-type trim	2019	EH
IC	Single-port body with integral extension for cryogenic service	---	easy-e w/Style 3 Ext, IC2
M, MY, MFY, 1664	Iron angle body, seats cut into body, three-way, 2 to 3 position options with diaphragm actuator	---	None
NL	Full and reduced bore on/off pipeline ball valve for general service	2018	DSV1000
SBV	Butterfly control valve body (for erosive slurry service)		V150S
SS-105	Slant valve body with balanced trim for cryogenic service (Class 900)		None

Discontinued Fisher Product	Description	Date Discontinued (if available)	Recommended Replacement (Fisher branded unless otherwise noted)
SS-110	Three-way, three-position valve (for manifold service)	---	None
SS-121	Class 900 ANSI globe valve body with Whisper I trim™		None
SS-124	High pressure globe valve body with seal weld construction	---	None
SS-125	Bodiless ball valve	---	None
SS-128	Slant valve body with internally piloted trim for cryogenic service (CL900 ANSI)	---	None
SS-130	High performance rotary valve	---	None
SS-136	External trim angle valve body (for noise applications)	---	None
SS-138, SS-138A	Modified V100 with metal flow ring construction	---	SS 138B
SS-139	Globe valve body with Cavitrol IV trim	---	None
SS-141	High performance rotary valve body	---	None
SS-143	Fabricated angle valve body (Class 2500 FB) with special EH trim	---	None
SS-145	Diffuser plate or plate assembly containing either Cavitrol or Whisper holes	2013	2013
SS-146	Cryogenic valve trim	---	ET-C, EWT-C, EZ-C
SS-147	Class 900 CE valve (NPS 1)	2008	None
SS-154	Bellows seal bonnet for ES & EZ globe valve body, Nuclear	2008	None
SS-157	Class 600 NPS 1-1/2- and 2-in. E body with Special Bellows Seal Bonnet	2008	None
SS-158	6-in. Class 900 EH with Special Trim	---	None

Discontinued Fisher Product	Description	Date Discontinued (if available)	Recommended Replacement (Fisher branded unless otherwise noted)
SS-162	6-in. Cavitrol IV three-stage trim with bolt-in seat ring	---	None
SS-165	3-in. Class 2500 angle valve hung cage with seal welded seat ring turbine drain application	---	None
SS-172	6 in. class 2500 three-way valve; YD style trim in a forged body	---	None
SS-205	Special groove end, 300 psig	---	None
SS-252A	Modified V200 or V300 with Alloy 6 flat metal seal construction	---	None
SS-261	High-recovery angle body with suspended plug guide with linear characteristic on a contoured plug	---	None
SS-267	Angle body incorporated with DMA/HTC variation	---	None
SS-268	Flush mounted one nozzle DMA/HTC	---	None
SS-269	Post-guided valve trim in a modified EH body	---	None
SS-30	Liquid metal valve	---	None
TBX-S	Steam conditioning valve	---	
V100	Characterized ball valve	2001	V150, V200, V300
Vonk Choke Valves	Choke valve	2021	None
Whisper V	---	---	Diffuser, Whisper NXV
Yarway™ AT-11	Desuperheater	2018	GX/EZ
Yarway AT-13/23	Desuperheater	2018	DMA-AF
Yarway AT-14/44	Desuperheater	2016	DSA application
Yarway AT-24/34	Desuperheater	2016	DSA application

Discontinued Fisher Product	Description	Date Discontinued (if available)	Recommended Replacement (Fisher branded unless otherwise noted)
Yarway AT-54	Desuperheater	2019	AT-18
Yarway AT-55/65	Desuperheater	2018	DMA-AF/HTC
Yarway AT-59	Desuperheater	2018	AT-18
Yarway AT-60/70	Desuperheater	2016	DMA family
Yarway AT-64	Desuperheater	2019	AT-28
Yarway AT-68	Desuperheater	2016	DMA-AF/HTC
Yarway AT-69	Desuperheater	2018	AT-28
Yarway AT-78	Desuperheater	2016	DMA-AF/HTC
Yarway AT-79	Desuperheater	2018	DMA-AF/HTC
Yarway AT-80/81	Desuperheater	2018	TBX-T
Yarway AT-88	Desuperheater	2018	DVI
Yarway AT-90/91	Desuperheater	2019	AT-38 special dimensions
Yarway AT-92/93	Desuperheater	2019	AT-18 special dimensions
Yarway AT-98	Desuperheater	2016	DMA-AF/HTC
YSC	Unbalanced 3-way valve body (with composition seats)	2008	None
Z	Single port, split-constructed, flanged, alloy body	---	None
Z500	Severe service ball valve	2020	None
ZLA	Split-angle body, fully lined for corrosive service	---	RSS



Fisher.com



Facebook.com/FisherValves



LinkedIn.com/groups/3941826



X.com/FisherValves

D104336X012 © 2018, 2025 Emerson. All rights reserved. The Emerson logo is a trademark and service mark of Emerson Electric Co. Fisher, FIELDVUE, ValveLink, Baumann, easy-e, Whisper, WhipperFlo, Whisper Trim, Cavitrol, Vee-Ball and Yarway are each a mark of an entity in the Emerson family of businesses. HART is a registered trademark of FieldComm Group. All other marks are the property of their respective owners.

Neither Emerson, nor any of its affiliated entities assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson
Marshalltown, Iowa 50158 USA
Sorocaba, 18087 Brazil
Cernay, 68700 France
Dubai, United Arab Emirates
Singapore 128461 Singapore

www.Fisher.com

FISHER™

