Next Generation LNG Tank PRV Optimizes Tank Design

RESULTS

- Met overpressure protection needs with single comprehensive solution
- Superior valve capacity reduced penetrations and bracing saving \$260K

APPLICATION

Pressure Relief Valves

CUSTOMER

Large LNG Liquefaction facility in North America

CHALLENGE

With the design of the facility calling for a single large LNG Tank, reliability and uptime were key considerations. Protecting a vessel of this size from overpressure events requires dozens of large pilot operated pressure relief valves which each necessitate rooftop penetrations, bracing and isolation. The design team needed a way to ensure protection from overpressure while minimizing the initial and future cost of installation and maintenance.

SOLUTION

Emerson offered the Anderson Greenwood[™] 9300H, a low pressure pilot operated valve with the largest flow capacities available. The unrivaled performance of the 9300H reduced the required number of valves and penetrations by three saving significant costs. In addition, the 18 valves provided were identical allowing a single spare valve to cover the entire facility.

RESOURCES

Anderson Greenwood 9300H Overview Anderson Greenwood 9300H Video



With its superior flow capacity, the Anderson Greenwood 9300H reduced installation costs by \$260K by requiring fewer tank penetrations and support infrastructure.



EMERSON

Emerson Automation Solutions

Americas T +1 800 558 5853 T +1 972 548 3574

Europe T +39 051 419 0611

Asia Pacific T +65 6777 8211

Middle East / Africa T +971 4811 8100

- webadmin.regulators@emerson.com
- C Emerson.com
- Facebook.com/EmersonAutomationSolutions
- in LinkedIn.com/company/emerson-automation-solutions
- Y Twitter.com/emr_automation

D353197X012 © 2021 Emerson Process Management Regulator Technologies, Inc. All rights reserved. 9/21. The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their prospective owners.