






Replacing the Sensor Cable for the 4200 Transmitter and the 5700 Transmitter




1 Replacing the 4200 Sensor Cable




1.1




1.2




1.3




1.4




1.5




1.6




1.7




1.8




1.9




1.10




1.11




1.12




1.13




1.14




1.15




1.16




1.17




1.18




1.19




1.20







1.21




1.22




2 Replacing the sensor cable on a 5700 transmitter




2.1




2.2




2.3




2.4




2.5




2.6




2.7




2.8




2.9




2.10




2.11




2.12




2.13




2.14




2.15




2.16




2.17




2.18




2.19




2.20




2.21



2.22



2.23





MMI-20058388
Rev. AA
2019

Emerson Automation Solutions

Worldwide Headquarters
7070 Winchester Circle
Boulder, Colorado USA 80301
T: +1 800-522-6277
T: +1 303-527-5200
F: +1 303-530-8459
Mexico: 52 55 5809 5300
Argentina: 54 11 4837 7000
Brazil: 55 15 3413 8147
Chile: 56 2 2928 4800

Emerson Automation Solutions

Central Europe: +41 41 7686 111
Eastern Europe: +41 41 7686 111
Dubai: +971 4 811 8100
Abu Dhabi: +971 2 697 2000
Austria: +43 2236 607-0
France: 0800 917 901
Germany: +49 (0) 2173 3348 0
Italy: 8008 77334
The Netherlands: +31 318 495 555
Belgium: +32 2 716 77 11
Spain: 900 901 986
U.K.: 0870 240 1978
Russian/CIS: +7 495 981 9811

Emerson Automation Solutions

Australia: (61) 3 9721 0200
China: (86) 21 2892 9000
India: (91) 22 6662 0566
Japan: (81) 3 5769 6803
South Korea: (82) 31 8034 0000
Singapore: (65) 6 363 7766

©2019 Micro Motion, Inc. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Micro Motion, ELITE, ProLink, MVD and MVD Direct Connect marks are marks of one of the Emerson Automation Solutions family of companies. All other marks are property of their respective owners.

MICRO MOTION™

