

The Copeland Scroll[™] Outdoor Condensing Unit (X-Line Series) for commercial refrigeration applications offers c-store operators the greatest energy efficiency, performance and flexibility available in a standard condensing unit.

X-Line Units



Perfectly suited for: Walk-in coolers and freezers Display cases Other refrigeration needs.

Range 3/4 – 6 HP



The X-Line Advantage

The X-Line Series' features make it the best option on the market for c-store

Have you ever wished for greater installation flexibility?



Do you have to operate your store within noise ordinance constraints?

Are you concerned about regulatory constraints for your region? Do you feel pressured by your headquarters to maintain energy costs?

Have you ever wanted to track and monitor your equipment performance?

Is your refrigeration equipment more of a problem than it should be?

The X-Lines' **slim profile, lighter weight** and **wall mount capabilities** means that operators avoid more costly solutions due to location issues. These features also mean lower installation costs and **improved appearance**. For Manhattan Diner, the flexible installation options offered by the X-Line made all the difference.



Manhattan Diner, located in NYC at 94th & Broadway, could not install conventional condensing units on the roof of its six-story building due to space constraints. A seven-foot wide alley was the only other location option. The X-Line condensing unit's **slim profile allowed the units to be installed safely on the building** wall using heavy-duty brackets – high enough not to interfere with the ground areas between New York City's alleyways.

"After seeing how easy the installation was, I am going to use the X-Line for another job because of the ease of installation." Nick Benetos, Owner, Gibsen HVAC

SLIM PROFILE

The X-Line Advantage

The X-Line Series' features make it the best option on the market for c-store

Have you ever wished for greater installation flexibility?

Do you have to operate your store within noise ordinance constraints?



Are you concerned about regulatory constraints for your region? Do you feel pressured by your headquarters to maintain energy costs?

Have you ever wanted to track and monitor your equipment performance?

Is your refrigeration equipment more of a problem than it should be?



The X-Line Condensing Unit's **ultra-quiet design** means that it **operates at a low decibel level**, providing a more peaceful atmosphere for customers and neighbors. For Sun King Brewery, the X-Line's low decibel levels were a game changer.



Sun King Brewery, a craft brewery located in Indianapolis, Indiana, was forced to put its condensing unit in the front of its downtown location, within close proximity to the main parking lot and front entrance of the building. A discreet solution was critical. The X-Line was **selected for its ultra-low sound levels** compared to typical outdoor condensing units.

"The X-Line Condensing Units exceeded my expectations. The solution makes sense for small business owners who need peace of mind that their equipment will work" Omar Robinson, President, Sun King Brewery

The X-Line Advantage

The X-Line Series' features make it the best option on the market for c-store

Have you ever wished for greater installation flexibility?

Do you have to operate your store within noise ordinance constraints?

Are you concerned about regulatory constraints for your region? Do you feel pressured by your headquarters to maintain energy costs?

Have you ever wanted to track and monitor your equipment performance?

Is your refrigeration equipment more of a problem than it should be?



Educational facilities in the U.S. and Canada spend about \$16 billion on energy each year. Schools spend more on energy than any other expense except personnel. However, energy is one of the few expenses a school can reduce without sacrificing educational quality.



ENERGY

EFFICIENT

Sidney High School depends on Eck Refrigeration to recommend energy-saving service practices and new refrigeration technologies. Eck approached Sidney High School with a plan to compare their current refrigeration equipment to Copeland X-Line technology in a real-world field test.

The energy efficiency of the entire system was improved beyond initial expectations. The X-Line Condensing Unit accounted for approximately 36% energy savings when compared to the old unit. This corresponds to a peak demand reduction of 719 W and an annual energy savings of 11,182 kWh per year.

The X-Line Series' features make it the best option on the market for c-store

Have you ever wished for greater installation flexibility?

Do you have to operate your store within noise ordinance constraints?

Are you concerned about regulatory constraints for your region? Do you feel pressured by your headquarters to maintain energy costs?

Have you ever wanted to track and monitor your equipment performance?

Is your refrigeration equipment more of a problem than it should be?



Diagnostics protection and electronic controls reduce potential service costs and result in a reliable, longer-lasting unit. United Dairy Farmers has seen how connectivity minimizes maintenance costs and maximizes system reliability.



CONNECTIVITY



United Dairy Farmers installed X-Line Condensing Units in conjunction with Site-Controller technologies from Emerson Retail Solutions. The X-Line's One-Way Communication Board **communicates with site controllers** which receive alarms and notice statuses from the X-Line.

"With more pressure than ever on operating profits, our use of Emerson's solutions have delivered greater energy and maintenance savings than any other initiatives. This helps our store managers focus on delivering the superior customer service United Dairy Farmers is known for, while enabling our operations team to save energy and ensure stores run optimally"

Brad Lindner, CEO, United Dairy Farmers

The X-Line Series' features make it the best option on the market for c-store

Have you ever wished for greater installation flexibility?

Do you have to operate your store within noise ordinance constraints?

Are you concerned about regulatory constraints for your region? Do you feel pressured by your headquarters to maintain energy costs?

Have you ever wanted to track and monitor your equipment performance?

Is your refrigeration equipment more of a problem than it should be?



The X-Line unit is **built to withstand harsh environments**. Protective coatings resist corrosion in coastal zones, and **intelligent controls adapt to Arctic blasts and Death Valley heat**. CoreSense protects against common failures and identifies nuisance conditions, avoiding unneeded service.



Maverick Convenience stores selected the X-Line condensing unit **for its ability to handle the heat** – literally. Maverick tested the unit in a Mesquite, Nevada location where temperatures soar to 147 degrees in July. The unit has **performed efficiently without any need for maintenance** for more than two years.

" I knew if it would work in 147 degree heat in Mesquite, Nevada, it would work anywhere. Two years later, I have yet to receive a service call."

Jim Alexander, Epic Refrigeration

PROTECTION

The X-Line Advantage


The X-Line Series' features make it the best option on the market for c-store



Large condenser coils Increases efficiency







Large condenser coils

Increases efficiency, aids in heat transfer, lowers condensing temperatures and allows units to operate in a wider range of ambient temperatures.

Copper tube and coated aluminum fin construction

Superior reliability and protection against corrosive environments. The hydrophilic coating resists dirt and water, so it stays cleaner longer and is suitable for coastal applications.



Variable speed fan motor control Quiet and efficient head pressure control




High efficiency variable speed PSC motor

- Proven PSC motor reliability and efficiency
- Eliminates the need for a mechanical head pressure control valve so less refrigerant is needed
- Allows for floating head pressure and low condensing operation for higher efficiency
- Fan blade design offers virtually noiseless operation (as low as 53 decibels at 10 feet).











Enhanced vapor injection (low temp models only)

Improves capacity and energy efficiency by utilizing a subcooling circuit. Additionally, vaporized refrigerant from the sub-cooling circuit is injected into the Scroll set, offering increased over-heat protection.

Heated and insulated receiver Allows operation in low-ambient situations.







Heated and insulated receiver

A heated and insulated receiver, along with a liquid line check valve and smart controls, allows the unit to operate in low-ambient temperatures.

Smart controls turn the heater on only when needed so energy is not wasted in warmer weather. A factory installed pressure relief valve allows compliance with municipal zoning codes.



Electronic controls Offer greater reliability than traditional mechanical controls.





Electronic controls

Integrated electronics control unit operation, diagnostics, compressor protection, and provide communication. The single control consolidates pressure controls, fan controls, defrost controls, temperature sensors, and electrical sensors. This consolidation allows the control to monitor system operation and make adjustments to maximize efficiency and reliability.

CoreSense [™] Diagnostics And Protection

- •Over Current protection
- Incorrect Phase Detection
- •High Pressure Lockout
- •Flood-Back Prediction
- •Demand Cooling™

- Flooded Start Protection ("Bump-Start" Logic)Discharge Temp. Protection
- •Anti-Short Cycle Time Delay
- •Digital Fault Code Display / Remote Alarming
- •Over/Under Voltage Protection





Copeland Scroll[™] compressor technology

Provides the most reliable, highest efficiency compression technology available.




Copeland Scroll[™] compressor technology

Provides the most reliable, highest efficiency compression technology available on the market today and serves as the workhorse and intelligence of the condensing unit. There are more than 100 million Copeland Scrolls in operation today.

Large condenser coils Increases efficiency

Variable speed fan motor control Quiet and efficient head pressure control



Improves capacity and energy efficiency

Heated and insulated receiver



Electronic controls Offer greater reliability than traditional mechanical controls.

Copeland Scroll[™] compressor technology

Provides the most reliable, highest efficiency compression technology available.





Visit <u>Emerson.com/CopelandOutdoorUnit</u> for more information about the Copeland X-Line.