



Commercial & Residential Solutions

This is a list of Emerson Tool Company products protected by United States patents. This listing is intended to satisfy the virtual patent marking provisions of U.S. patent law. This listing of products may be all inclusive, and other Emerson Tool Company products not listed may be protected by patents. The products may also be covered by patents outside of the U.S. Pending patent applications in the U.S. and elsewhere may also apply. By listing patents in this document, Emerson Tool Company makes no admission that other patents do not apply.

Emerson Tool Co.
12969 Manchester Road
St. Louis, MO 63131
USA

PRODUCT

U.S. PATENT NUMBER

PRODUCT		U.S. PATENT NUMBER
RIDGID Wet/Dry Vacuum	-	-
1200RV	12 GAL WET/DRY VAC RTC	D670048; 9675225; D1021303
1250RV	12 GAL WET/DRY VAC 2.5" RTC	9675225; D1021303
1600RV	16 GAL WET/DRY VAC	9675225; D1021303
1650RV	16 GAL WET/DRY VAC 2.5" RTC	9675225; D1021303; 12011137
4000RV	4 GAL WET/DRY VAC RTC	D537992; 9675225; D1021303
4500RV	RTC 4.5 GAL WET/DRY PRO PACK VAC W/ WANDS	9675225; D1021303
6000RV	6 GAL WET/DRY VAC RTC	9675225; D1021303
6000RV	6 GAL WET/DRY VAC RTC	9675225; D1021303
HD0300	3 GAL WET/DRY RIDGID VAC	D1021303; 11786089; D1089912; D1087733
HD0300PG	HD0300 PRO GEAR ACCESSORY BUNDLE	D1021303; 11786089; D1056379; D1089912; D1087733
HD0300PROMO	3 GAL WET/DRY RIDGID VAC PG0300 PROMO	D1021303; 11786089; D1056379; D1089912; D1087733
HD0318	3 GAL 18V CORDLESS WET/DRY VAC	D1021303; 11786089; D1089912; D1087733
HD0320	3 GAL 18V CORDLESS W/D VAC W/BATTERY AND CHARGER	D1021303; 11786089; D1089912; D1087733
HD0600	6 GAL WET/DRY VAC	D867702; 11027894; D876738; 10702111; 11684226; D1021303
HD0600M	6 GAL WET/DRY VAC	D867702; 11027894; D876738; 10702111; 11684226; D1021303
HD0900	9 GAL WET/DRY VAC	D867702; 11027894; D876738; 10702111; 11684226; D1021303
HD0900M	9 GAL WET/DRY VAC	D867702; 11027894; D876738; 10702111; 11684226; D1021303
HD0918	9 GAL CORDLESS WET/DRY VAC	D867702; 11027894; D929687; D929688; D929689; D876039; 10702111; D874765; D1021303
HD1200	12 GAL WET/DRY VAC	D868404; D865305; 11027894; 11083352; D876739; 10702111; D1021303; D1081048
HD1200M	12 GAL WET/DRY VAC	D868404; D865305; 11027894; 11083352; D876739; 10702111; D1021303; D1081048
HD1200T	12 GAL WET/DRY VAC	D868404; D865305; 11027894; 11083352; D876739; 10702111; D1021303; D1081048
HD1280	12 GAL WET/DRY VAC DETACH	D865305; D971534; D934518; D934518; D876739; D891716; 10702111; D1021303; D1081048
HD1400	14 GAL WET/DRY VAC	D868404; D865305; 11027894; 11083352; D934518; D882892; 10702111; D1021303; D1081048
HD1400M	14 GAL WET/DRY VAC	D868404; D865305; 11027894; 11083352; D934518; D882892; 10702111; D1021303; D1081048
HD1402	14 GAL WET/DRY VAC	D868404; D865305; 11027894; 11083352; D934518; D882892; 10702111; D1021303; D1081048
HD1600	16 Gal WET/DRY DETACH VAC	D868404; D865305; 11027894; 9675225; D971534; D934518; D891716; D882892; 10702111; D1021303; D1081048
HD1600M	16 Gal WET/DRY DETACH VAC	D868404; D865305; 11027894; 9675225; D971534; D934518; D891716; D882892; 10702111; D1021303; D1081048
HD1800	16 GAL WET/DRY VAC	D868404; D865305; 11027894; 11083352; D915698; D901112; D882892; D875333; 10702111; D1021303; D1081048
HDB600	RIDGID BACKPACK VAC	PENDING
MOB1200	12 GAL MOTOR ON BOTTOM WET/DRY VAC	10888207; 11464379; 10702111; D1021303; 12011137; 11819183; 12011137
RV2400A	14 GAL 2-STAGE VAC	6035485
RV2600B	16 GAL 2-STAGE VAC	6035485
RV3410	14 GAL SELF CLEANING FILTER VAC	9675225; D1021303
VAC1100	RIDGID ECOMM W/D CART VAC	8973196; 9572465; D1021303
VAC1100	RIDGID W/D VAC CART SYSTEM	8973196; 9572465; 9675225; 9510718; D1021303
VAC1200	6 GAL WET/DRY VAC CANADA	9675225; D1021303
VAC4000	RIDGID ECOMM 4GAL W/D VAC	D544090; D537992; 60335485; D1021303
VAC4010	4 GAL WET/DRY DETACH VAC	D666369; 9675225; D1021303
VAC5000	RIDGID ECOMM 5GAL W/D WALL VAC	D559904; 9675225; D1021303
WD0318	SUPPLIED DETACHED	7971314; D1021303
WD0319	3 GAL WET/DRY CORDLESS VAC	7971314; 9675225; D1021303
WD0319	3 GAL WET/DRY CORDLESS VAC	9675225; D1021303
WD0625	6 GAL WET/DRY VAC	D492823; D1021303
WD0640EX	6 GAL WET/DRY VAC W/EXTRA FILTER NUT	D1021303
WD0645	6 GALLON WET/DRY VAC	D1021303
WD0655BR	6 GAL WET/DRY VAC 120V W/D VAC BRAZIL	D1021303
WD0656BR	6 GAL WET/DRY VAC CANADA	D1021303
WD0670	6 GAL WET/DRY VAC	9675225; D1021303

WD0670C	6 GAL WET/DRY VAC MEXICO	9675225; D1021303
WD0670M	6 GAL WET/DRY VAC	9675225; D1021303
WD0671	6 GAL WET/DRY VAC EXPORT	9675225; D1021303
WD0671EX	6 GAL WET/DRY VAC PROMO	9675225; D1021303
WD0672	6 GAL WET/DRY VAC PROMO	9675225; D1021303
WD0672C	9 GAL WET/DRY VAC	9675225; D1021303
WD0945	9 GAL WET/DRY VAC	D492823; D1021303
WD0947	9 GAL WET/DRY VAC	D492823; D1021303
WD0950	9 GAL WET/DRY VAC 120V	9675225; D1021303
WD0950	9 GAL WET/DRY VAC 120V	D492823; D1021303
WD0950M	9 GAL WET/DRY VAC 130V MEXICO	9675225; D1021303
WD0950MP	9 GAL WET/DRY VAC 130V MEXICO	9675225; D1021303
WD0957	9 GAL WET/DRY VAC 120V	D492823; D1021303
WD0970	9 GAL WET/DRY VAC	9675225; D1021303
WD0970C	9 GAL WET/DRY VAC MEXICO	9675225; D1021303
WD0970M	9 GAL WET/DRY VAC PROMO CANADA	9675225; D1021303
WD0975	9 GAL WET/DRY VAC PROMO	9675225; D1021303
WD0975C	9 GALLON WET/DRY VAC - PROMO LED NOZZLE	9675225; D1021303
WD0976	12 GAL WET/DRY VAC CANADA	9675225; D1021303
WD1270	12 GAL WET/DRY VAC	D670048; 9675225; D1021303
WD1270C	12 GAL WET/DRY VAC 230V EXPORT	9675225; D1021303
WD1270EX	12 GAL WET/DRY VAC PROMO CREVICE TOOL	9675225; D1021303
WD1271	45L WET/DRY VAC CANADA	9675225; D1021303
WD1271	12 GAL WET/DRY VAC PROMO CREVICE TOOL	D670048; 9675225; D1021303
WD1272C	12 GAL WET/DRY VAC	D670048; 9675225; D1021303
WD1273	12 GAL WET/DRY VAC PROMO W/ LIGHTED CAR NOZZLE & (2) DUST BAGS	D670048; 9675225; D1021303
WD1276	12 GAL WET/DRY VAC (1-7/8" ACC)	D670048; D1021303
WD1278	12 GAL DETACHED WET/DRY VAC	9675225; D1021303
WD1280	12 GAL DETACHED WET/DRY VAC CANADA	9675225; D1021303
WD1280	12 GAL DETACHED WET/DRY VAC	9675225; D1021303
WD1280	12 GAL DETACHED WET/DRY VAC	9675225; D1021303
WD1280C	12 GAL DETACHED WET/DRY VAC	9675225; D1021303
WD1285	16 GAL WET/DRY VAC CANADA	9675225; D1021303
WD1285	12 GAL DETACHED WET/DRY VAC	9675225; D1021303
WD1285	12 GAL DETACHED WET/DRY VAC	9675225; D1021303
WD1451	14 GAL WET/DRY PRO VAC W/AUTO DETAIL KIT	8533907; 9675225; D1021303
WD1480	14 GAL DET PROMO	D666369; 9675225; D1021303
WD1481	14 GAL WET/DRY DETACH VAC	D666369; 9675225; D1021303
WD1481	14 GAL WET/DRY DETACH VAC	D666369; 9675225; D1021303
WD1637	16 GAL WET/DRY VAC	D492824; D1021303
WD1670	16 GAL WET/DRY DETACH VAC	9675225; D1021303
WD1670BR	16 GAL WET/DRY DETACH VAC CANADA	9675225; D1021303
WD1670C	16 GAL WET/DRY DETACH VAC EXPORT	9675225; D1021303
WD1670EX	16 GAL WET/DRY DETACH VAC MEXICO	9675225; D1021303
WD1670M	16 GAL WET/DRY VAC	9675225; D1021303
WD1671	16 GAL WET/DRY DETACH VAC	9675225; D1021303
WD1680C	16 GAL WET/DRY DETACH VAC CANADIAN	9675225; D1021303
WD1680EX	16 GAL WET/DRY DETACH VAC 230V EXPORT	9675225; D1021303
WD1681	16 GAL WET/DRY VAC	9675225; D1021303
WD1851	16 GAL WET/DRY PRO VAC W/O FPS	9675225; D1021303
WD1870	MOTOR ON BOTTOM	9675225; D1021303
WD3050	3 GALWET/DRY VAC	9675225; 9282861; D1021303
WD3053C	3 GAL WET/DRY VAC CANADIAN PROMO	8533907; 9675225; D1021303
WD4050	4 GAL WET/DRY VAC	D537992; 9675225; D1021303
WD4050S	4 GAL WET/DRY VAC	9675225; D1021303
WD4070	4 GAL WET/DRY VAC	9675225; D1021303
WD4070	4 GAL WET/DRY VAC	9675225; D1021303
WD4071	4 GAL WET/DRY VAC	D596360; 9675225; D1021303
WD4075BR	4 GAL WET/DRY VAC 230V BRAZIL	D596362; 9675225; D1021303
WD4076BR	4 GAL WET/DRY VAC 120V BRAZIL	D596361; 9675225; D1021303
WD4080	4 GAL BLOWER VAC WET/DRY	D666369; 9675225; D740504; D1021303
WD4080C	4 GAL WET/DRY DETACH VAC CANADA	D666369; 9675225; D740504; D1021303
WD4081	4 GAL BLOWER VAC WET/DRY W/ CAR ACCESSORY KIT	D666369; 9675225; D740504; D1021303

WD4522	4.5 GAL WET/DRY PRO PACK VAC W/ WANDS	9675225; D1021303
WD4550	4.5 GAL WET/DRY VAC	9675225; D1021303
WD4550	5 GAL WET/DRY PRO PACK VAC	9675225; D1021303
WD5500	5 GAL WET/DRY "STOR 'N GO" WALL VAC	D559904; 9675225; D1021303
WD5540	5 GAL WET/DRY WALL VAC	D559904; 9675225; D1021303
WD7000	RIDGID W/D VAC CART SYSTEM	8973196; 9572465; 9675225; 9510718; D1021303
WORKSHOP Wet/Dry Vacuum	-	-
WS0300VA	3 GALLON, 3.5 PEAK HP PORTABLE WET/DRY VAC	7971314; 9675225; D1021303
WS0300VA0	3 GALLON WET/DRY VAC	9675225; D1021303
WS0301VA	SUPPLIED DETACH PLUS CAR CLEANING KIT	7971314; D1021303
WS0301VA	WS0300VA PLUS CAR CLEANING KIT	8533907; D1021303
WS0400DE	4 GAL BLOWER WET/DRY VAC	D666369; 9675225; D740504; D1021303
WS0400VA	4 GALLON, 5.0 PEAK HP PORTABLE WET/DRY VAC	D537922; 9675225; D1021303
WS0401VA	WS0400VA PLUS CAR CLEANING KIT	D537922; D1021303
WS0401VA	WS0400VA PLUS CAR CLEANING KIT	8533907; D1021303
WS0450VA	4.5 GALLON WET/DRY VAC	9675225; D1021303
WS0450VA0	4.5 GALLON WET/DRY VAC	9675225; D1021303
WS0500WM	5 GALLON WET/DRY VAC	D559904; 9675225; D1021303
WS0501WM	WS0500WM PLUS CAR CLEANING KIT	8533907; D1021303
WS0501WM	WS0500WM PLUS CAR CLEANING KIT	D559904; 9675225; D1021303
WS0600VA	6 GALLON WET/DRY VAC	9675225; D1021303
WS0610VA	WS0610VA	9675225; D1021303
WS0900VA	9 GALLON WET/DRY VAC	9675225; D1021303
WS0910VA	9 GALLON WET/DRY VAC	9675225; D1021303
WS1100CA	11 GALLON SMARTCART	8973196; 9572465; 9675225; 9510718; D1021303
WS1200DE	12 GALLON WET/DRY VAC WITH DETACHABLE BLOWER	9675225; D1021303
WS1200DE	12 GALLON, 5.0 PEAK HP WET/DRY VAC WITH DETACHABLE BLOWER	9675225; D1021303
WS1200VA	12 GALLON WET/DRY VAC	9675225; D1021303
WS1200VAEX	12 GAL WET/DRY VAC 230V EXPORT	9675225; D1021303
WS1250	12 GALLON DETACHED WET/DRY VAC	9675225; D1021303
WS1400CA	14 GALLON WET/DRY VAC WITH CART	9675225; D1021303
WS14045F	FILTER ASM 4.75 WET FILTER WORKSHOP	D691338
WS1600VA	16 GALLON WET/DRY VAC	9675225; D1021303
WS24200F	WET APPLICATION FILTER 2PK	D691338; 9510718
WS25025A	MUFFLER/DIFFUSER 2 1/2"	D544090
PROTEAM Wet/Dry Vacuum	-	-
107128	PROTEAM PROGUARD 4	D537992; 9675225; D1021303
107130	PROTEAM PROGUARD 15 WET/DRY VAC	D670046; D676205; D1021303
107131	PROTEAM PROGUARD 20 WET/DRY VAC	D670046; D676205; D1021303
107183	SUPPLIED DETACHED	D669646
107184	PROTEAM 4 GALLON ACCESSORY KIT	9675225
107185	PROTEAM PROGUARD 28" FRONT MOUNT SQUEEGEE	8756756
107303	SUPER COACH PRO 10 VAC W/KIT 107100	D726978; 9456722; 9861242
107304	SUPER COACH PRO 10 VAC W/KIT 107098	D726978; 9456722; 9861242
107305	SUPER COACH PRO 10 VAC W/KIT 107099	D726978; 9456722; 9861242
107306	SUPER COACH PRO 10 VAC W/KIT 101829	D726978; 9456722; 9861242
107307	SUPER COACH PRO 6 VAC W/KIT 107099	D726978; 9456722; 9861242
107308	SUPER COACH PRO 6 VAC W/KIT 107098	D726978; 9456722; 9861242
107309	SUPER COACH PRO 6 VAC W/KIT 101829	D726978; 9456722; 9861242
107310	SUPER COACH PRO 6 VAC W/KIT 107100	D726978; 9456722; 9861242
107320	GOFREE BP BATTERY PACK	D697024
107324	VAC SUPER HALFVAC PRO 120V NTK	10085606
107325	VAC SUPER HALFVAC PRO 120V W/107100	10085606
107326	VAC SUPER HALFVAC PRO 120V W/107097	10085606
107327	VAC SUPER HALFVAC PRO 120V W/107098	10085606
107328	VAC SUPER HALFVAC PRO 120V W/107099	10085606
107329	VAC; UPRIGHT; PROGEN12; 120 V	9173533B1; 9173533; 9113764; D737007
107330	VAC, UPRIGHT, PROGEN15, 120 V	9173533B1; 9173533; 9113764; D737007
107332	PROGUARD 15 W/GFCI	D670046; D676205; D1021303
107338	SUPER COACH PRO 10 VAC W/KIT 107336	D726978; 9456722; 9861242
107339	SUPER COACH PRO 10 VAC W/KIT 105889	D726978; 9456722; 9861242
107340	SUPER COACH PRO 10 VAC W/KIT 106820	D726978; 9456722; 9861242
107341	SUPER COACH PRO 10 VAC W/KIT 106841	D726978; 9456722; 9861242

107342	SUPER COACH PRO 10 VAC W/KIT 105891	D726978; 9456722; 9861242
107343	SUPER COACH PRO 6 VAC W/KIT 106820	D726978; 9456722; 9861242
107344	SUPER COACH PRO 6 VAC W/KIT 106841	D726978; 9456722; 9861242
107346	PAD MICROFIBER 170	D726978
107359	PROGUARD 15 W/SQUEEGEE	D670046; D676205; 8756756; D1021303
107363	PROVAC FS W/ KIT 100727	D726978; 9456722; 9861242
107371	SUPER COACH PRO BACKPACK 6QT VAC W/1-1/4" HOSE AND KIT 103439	D726978; 9456722; 9861242
107373	GOFREE BATTERY BACKPACK 6QT VAC W/1-1/4" HOSE AND KIT 103439	D726978; 9456722; 9861242
107375	PROVAC FS 6 W/KIT 107099	D726978; 9456722; 9861242
107376	PROVAC FS 6 W/KIT 107100	D726978; 9456722; 9861242
107384	GOFREE PRO W/KIT 106263	D697024; D719911
107385	SUPER HALFVAC PRO 120V W / KIT 100727	10085606
107391	PROTEAM SUPER COACH PRO 6 VAC FOR ISS W/107098 KIT	D726978; 9456722; 9861242
107392	PROTEAM SUPER COACH PRO 6 VAC FOR ISS W/107100 KIT	D726978; 9456722; 9861242
107394	PROTEAM SUPER COACH PRO 10 VAC FOR ISS W/107098 KIT	D726978; 9456722; 9861242
107395	PROTEAM SUPER COACH PRO 10 VAC FOR ISS W/107100 KIT	D726978; 9456722; 9861242
107397	GOFREE FLEX PRO W/KIT 107100	D697024; D719911
107398	GOFREE FLEX PRO W/KIT 107099	D697024; D719911
107399	GOFREE FLEX PRO W/KIT 107098	D697024; D719911
107401	GOFREE FLEX PRO W/6AH BATTERY AND KIT 107100	D697024; D719911
107402	GOFREE FLEX PRO W/6AH BATTERY AND KIT 107098	D719911
107404	GOFREE FLEX PRO W/1-1/4"HOSE, 6AH BATTERY & IPM KIT 103439	D719911
107405	BATTERY PACK, 6AH, FOR GOFREE FLEX PRO	D697024
107408	GOFREE FLEX PRO W/1-1/4"HOSE, 12AH BATTERY & IPM KIT 103439	D697024; D719911
107426	PROVAC FS 6 W/COMMERCIAL HOME KIT 107420	D726978
107427	PROVAC FS 6 W/SMALL BUSINESS KIT 107421	D726978
107428	SUPER HALF VAC PRO W/COMMERCIAL HOME KIT 107420	10085606
107429	SUPER HALF VAC PRO W/SMALL BUSINESS KIT 107421	10085606
107433	GOFREE PRO W/KIT 106263	D726978; 9456722; 9861242
107457	GOFREE FLEX PRO BATTERY, 12AH F/GRAINGER	D697024
107459	GOFREE FLEX PRO CHARGER, F/GRAINGER	D697024; D719911
107461	PROVAC 6 W/ELECTRIFIED HOSE OUTLET AND KIT 103224	D726978; 9456722; 9861242
107464	SUPER COACH PRO 6 W/107463 KIT	D726978; 9456722; 9861242
107465	SUPER COACH PRO 10 W/107463 KIT	D726978; 9456722; 9861242
107467	SUPER COACH PRO6 W/107466 KIT	D726978; 9456722; 9861242
107468	SUPER COACH PRO 10 W/107466 KIT	D726978; 9456722; 9861242
107473	PROTEAM SUPER COACH PRO 10 FOR STRATUS W/107250 KIT	D726978; 9456722; 9861242
107474	SUPER COACH PRO 6 VAC W/ PACKAGE OS1	D726978; 9456722; 9861242
107475	SUPER COACH PRO 10 VAC W/ PACKAGE OS1	D726978; 9456722; 9861242
107484	GOFREE FLEX PRO UK W/KIT 107098	D726978; 9456722; 9861242
107485	GOFREE FLEX PRO SWISS W/KIT 107098	D726978; 9456722; 9861242
107486	GOFREE FLEX PRO UK W/KIT 106820	D726978; 9456722; 9861242
107487	GOFREE FLEX PRO SWISS W/KIT 106820	D726978; 9456722; 9861242
107497	SUPER COACH PRO 6 W/107100 KIT 20" FLOOR TOOL & VAC STATION	D726978; 9456722; 9861242
107498	USPS SIDEWINDER PACKAGE (2 BOXES)	D726978; 9456722; 9861242
107499	FREEFLEX CORDLESS / CORDED UPRIGHT VACUUM	10258213; 11464376; D943225; 11185202; 11471018; 10709305; 10660497; 11864720
107499	PROTEAM FREEFLEX UPRIGHT VACUUM CORDED / CORDLESS	10413146; D836863; 11510540; 10682030; 10575691; 10758101; 10687678
107503	FREEFLEX CORDED UPRIGHT VACUUM	10258213; 11464376; D943225; 11185202; 11471018; 10709305; 10660497
107503	PROTEAM FREEFLEX UPRIGHT VACUUM CORDED	10413146; D836863; 11510540; 10682030; 10575691; 10758101
107504	SUPER COACH PRO6 W/107100 KIT AND 101613	D726978; 9456722; 9861242
107507	GOFREE FLEX PRO W/ 107100	D726978; 9456722; 9861242
107508	GOFREE FLEX PRO W/ 107099	D726978; 9456722; 9861242
107509	GOFREE FLEX PRO W/KIT 107098	D726978; 9456722; 9861242
107527	PROBLACE CARPET FLOOR TOOL	10258213; D812831
107528	PROBLADE HARD SURFACE FLOOR TOOL	10258213; D812831
107529	Telescoping Straight Wand	D803493
107533	SUPER COACH PRO 6 W/ 107530 KIT	D726978; 9456722; 9861242
107534	SUPER COACH PRO 6 W/ 107531 KIT	D726978; 9456722; 9861242
107535	SUPER COACH PRO 6 W/ 107532 KIT	D726978; 9456722; 9861242
107536	SUPER COACH PRO 10 W/ 107530 KIT	D726978; 9456722; 9861242
107537	SUPER COACH PRO 10 W/ 107531 KIT	D726978; 9456722; 9861242
107538	SUPER COACH PRO 10 W/ 107532 KIT	D726978; 9456722; 9861242
107539	GOFREE FLEX PRO 12AH W/107530 KIT	D726978; 9456722; 9861242

107540	GOFREE FLEX PRO 12AH W/107531 KIT	D726978; 9456722; 9861242
107541	GOFREE FLEX PRO 12AH W/107532 KIT	D726978; 9456722; 9861242
107543	PROVAC 6 W/ELECTRIFIED HOSE	D726978; 9456722; 9861242
107544	PROVAC 6 W / 107546 KIT	D726978; 9456722; 9861242
107567	PROVAC 6 W/107378 KIT	D726978; 9456722; 9861242
107569	PROVAC 6 W/107378 KIT	D726978; 9456722; 9861242
107571	PROVAC 6 W/ 107378 KIT	D726978; 9456722; 9861242
107582	PROVAC 6 W/107580 KIT	D726978; 9456722; 9861242
107583	PROVAC 6 W/107581 KIT	D726978; 9456722; 9861242
107587	SCP 10 W/1.25" HOSE & 107585 KIT	D726978; 9456722; 9861242
107588	SCP 6 W/1.25" HOSE & 107585 KIT	D726978; 9456722; 9861242
107592	PROVAC FS 6 WITH 107378 ACCESSORY KIT	D726978; 9456722; 9861242
107593	PROVAC 6 W/107594 ACCESSORY KIT	D726978; 9456722; 9861242
107608	SUPER HALFVAC HEPA W/107532 KIT	10085606
107613	PROVAC FS6 W/107532 KIT	D726978; 9456722; 9861242
107615	SUPER COACH PRO 10 W/KIT 107098	D726978; 9456722; 9861242
107616	SUPER COACH PRO 10 W/KIT 107532	D726978; 9456722; 9861242
107618	SUPER COACH PRO 6 W/KIT 107098	D726978; 9456722; 9861242
107619	SUPER COACH PRO 6 W/KIT 107532	D726978; 9456722; 9861242
107627	SUPER COACH PRO 6 VAC ASM	D726978; 9456722; 9861242
107628	Telescoping S-Bend Wand	D803494
107629	SUPER COACH PRO 6 VAC ASM	D726978; 9456722; 9861242
107630	SUPER COACH PRO 10 VAC ASM	D726978; 9456722; 9861242
107642	GOFREE FLEX PRO II W/12 AH BATTERY VAC	D726978; 9456722; 9861242; 11647878
107643	GOFREE FLEX PRO II W/6 AH BATTERY VAC	D726978; 9456722; 9861242; 11647878
107652	GOFREE FLEX PRO II W/12 AH BATTERY VAC	D726978; 9456722; 9861242; 11647878
107653	GOFREE FLEX PRO II W/6 AH BATTERY VAC	D726978; 9456722; 9861242; 11647878
107662	PROTEAM GOFIT 3 BACKPACK VAC	11594837; D1047325
107663	PROTEAM GOFIT 6 BACKPACK VAC	11594837; D1047325
107664	PROTEAM GOFIT 10 BACKPACK VAC	11594837; 11647878; D1047325
107665	PROTEAM GOFIT 6 PLUS BACKPACK VAC	11594837; D1047325
107668	PROTEAM GOFIT 3 CORDLESS BASE VAC W/ 4AH BATTERY	D1047325
107668	GOFIT 3 CORDLESS BASE VAC W/ 4AH BATTERY	11978869; 11901533; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107669	GOFIT 3 CORDLESS BASE VAC W/ 8AH BATTERY	11978869; 11901532; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107676	GOFIT BLOWER ACCESSORY KIT	D1046350
107677	PROTEAM GOFIT 3 PH BASE VAC	11594837; D1047325; 12156584
107678	PROTEAM GOFIT 6 PH BASE VAC	11594837; D1047325; 12156584
107688	PROTEAM GOFIT 10, 10 QT BACKPACK VAC W/ XOVER MULTI SURFACE TELESCOPING WAND KIT	11594837; D1047325; 12156584
107689	PROTEAM GOFIT 10, 10 QT BACKPACK VAC W/ XOVER MULTI SURFACE 2-PCS WAND KIT	11594837; D1047325; 12156584
107696	PROTEAM GOFIT 6, 6 QT BACKPACK VAC W/ XOVER MULTI SURFACE TELESCOPING WAND KIT	11594837; D1047325; 12156584
107697	PROTEAM GOFIT 6, 6 QT BACKPACK VAC W/ XOVER MULTI SURFACE 2-PCS WAND KIT	11594837; D1047325; 12156584
107706	PROTEAM GOFIT 6 PLUS, 6 QT BACKPACK VAC W/ XOVER MULTI SURFACE 2-PCS WAND KIT	11594837; D1047325; 12156584
107713	PROTEAM GOFIT 3, 3 QT BACKPACK VAC W/ XOVER MULTI SURFACE TELESCOPING WAND KIT	11594837; D1047325; 12156584
107772	GOFIT 6 CORDLESS BASE VAC W/ 4AH BATTERY	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107775	GOFIT 3 CORDLESS 4AH W/ 107098 XOVER 2-PIECE WAND KIT	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107777	GOFIT 3 CORDLESS 8AH W/ 106502 1.5" AVIATION KIT	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107778	GOFIT 3 CORDLESS 8AH W/ 107100 XOVER TELESCOPING WAND KIT	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107779	GOFIT 3 CORDLESS 8AH W/ 107098 XOVER 2-PIECE WAND KIT	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107780	GOFIT 3 CORDLESS 8AH W/ 107532 PROBLADES COMBO KIT	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107782	GOFIT 6 CORDLESS 4AH W/ 107100 XOVER TELESCOPING WAND KIT	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107783	GOFIT 6 CORDLESS 4AH W/ 107098 XOVER 2-PIECE WAND KIT	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107784	GOFIT 6 CORDLESS 4AH W/ 107532 PROBLADES COMBO KIT	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107787	GOFIT 6 CORDLESS 8AH W/107098 XOVER 2-PIECE WAND KIT	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107795	GOFIT 6 CORDLESS 8AH W/ 107099 XOVER PERFORMANCE TELESCOPING WAND KIT	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107801	GOFIT 3 CORDLESS 4AH W/107532 KIT & EXTRA 4AH BATTERY	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107802	GOFIT 3 CORDLESS 4AH W/107100 KIT & EXTRA 4AH BATTERY	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107803	GOFIT 6 CORDLESS 8AH W/107532 KIT & EXTRA 8AH BATTERY	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
107804	GOFIT 6 CORDLESS 8AH W/107100 KIT & EXTRA 8AH BATTERY	11978869; 11901538; 11864720; D1051036; 11978869; 11901527; 12156584; D1048619; D1095405
1071290	PROTEAM PROGUARD 10 WET/DRY VAC	D669646; 9675225
1073600	PROGUARD 20 W/SQUEEGEE	D670046; D676205; D1021303
PROTEAM Wet/Dry Vacuum	-	-
RRV0400	4 GAL WET/DRY VAC	D537992; 9675225; D1021303
RRV0450	4.5 GAL WET/DRY VAC	D5584110; 9675225; D1021303

RRV0600	6 GAL WET/DRY VAC	9675225; D1021303
RRV0900	9 GAL WET/DRY VAC	9675225; D1021303
RRV1000	10 GAL WET/DRY VAC	9675225; D1021303
RRV1200	12 GAL WET/DRY VAC	9675225; D1021303
RRV1600	16 GAL WET/DRY VAC	9675225; D1021303
RRV1600	16 GAL WET/DRY VAC	9675225; D1021303
CRAFTSMAN Wet/Dry Vacuum	-	-
17292	FILTER ASM 7.47" WET	D691338; 9510718; D1021303
17611	2-1/2 GAL WET/DRY VAC	D1021303
17612	4 GAL WET/DRY VAC	8695161; 8631539; D1021303
17761	16 GAL WET/DRY VAC	D1021303
17761	16 GAL WET/DRY VAC	D519251; D1021303
17762	20 GAL WET/DRY VAC	D519251; D1021303
17764	16 GAL WET/DRY VAC 80TH ANV	D519251; D1021303
17765	12 GAL WET/DRY VAC	D1021303
17765	12 GAL WET/DRY VAC	D519251; D1021303
17766	16 GAL WET/DRY VAC (CLASS 1)	D519251; D1021303
17768	16 GAL WET/DRY VAC (CLASS 1)	D519251; D1021303
17769	SUPPLIED DETACHED	D519251; D1021303
17789	11 GAL WET/DRY VAC CART - ADVANCED CLEANING	8973196; 9572465; 9675225:9510718; D1021303
17925	5 GAL WET/DRY CLEAN N CARRY VAC	D520689; D1021303
17965	6 GAL WET/DRY VAC	D1021303
17967	9 GAL WET/DRY VAC	D1021303
17971	20 GAL WET/DRY VAC	6035485; D1021303
29602	5 GAL 19L WET/DRY CLEAN N CARRY VAC	D520689; D1021303
29604	5 GAL 19L WET/DRY CLEAN N CARRY VAC	D520689; D1021303
29615	12 GAL 45L WET/DRY VAC	D1021303
29621	16 GAL 60L WET/DRY VAC COMBO	D519251
29623	SUPPLIED DETACHED	D519251
29711	SUPPLIED DETACHED	D519251
29901	4 GAL WET/DRY VAC	8695161; 8631539; D1021303
38773	FILTER ASM 7.47" WET	D691338; 9510718
97315	FILTER ASM 7.47" WET- CANADA	D691338; 9510718
29611C	9 GAL 34L WET/DRY VAC	D1021303
CMXEVB17612	4 GAL WET/DRY VAC	8695161; 8631539; D1021303
CMXZVB38773	FILTER ASM 7.47" WET	D691338; 9510718
SINGLE LATCH VACS	-	-
ALL SINGLE PIECE LATCH VACS	ALL SINGLE LATCH VACS	6321410
STINGER	-	-
WD20250	2 1/2 GAL WET/DRY VAC STINGER	6101669
ACCESSORIES	-	-
16952	PUMP ACCESSORY SEARS	D551681
16989	DELUXE CAR CLEANING KIT	8533907
38336	LED LIGHTED 1-7/8 CAR NOZZLE 6 PACK	D725856; 9700187; 10238255
38337	LED LIGHTED 2-1/2 CAR NOZZLE 6 PACK	D725856; 9700187; 10238255
38619	PUMP ACCESSORY	D551681
38633	2 1/2" FLOOR BRUSH NOZZLE (BLACK)	5706550
38658	DELUXE CAR CLEANING KIT	8533907
38660	NOISE DIFFUSION MUFFLER	D544090
38666	1-7/8" X 10-1/2 FLOOR BRUSH	5706550
97186	2-1/2" FLOOR BRUSH NOZZLE	5706550
97901	1 7/8" FLOOR BRUSH	5706550
835987	FLEXIBLE CREVICE TOOL W/1-7/8" ADAPTER	8533907
ALL VAC WITH 1-7/8" HOSE	1 7/8" WET NOZZLE	7661175
ALL VAC WITH 1-7/8" HOSE	1 7/8" WET NOZZLE	7832049
CMXZVB38336	LED LIGHTED 1-7/8 CAR NOZZLE 6 PACK	D725856; 9700187; 10238255
CMXZVB38337	LED LIGHTED 2-1/2 CAR NOZZLE 6 PACK	D725856; 9700187; 10238255
CVS108	NOZZLE CREVICE TOOL	8533907
DA1701	DUAL ROTATING DUSTING BRUSH	10702111; 11882984; D1091991
DA1702	DUAL CREVICE TOOL	10702111; 11882984; D1091991
DA1703	DUAL CAR NOZZLE	10702111; 11882984; D1091991
DA1709	DUAL UTILITY NOZZLE	10702111; 11882984; D1091991
DA1712	DUAL FLOOR TOOL	10702111; 11882984; D1091991

DA1740	DUAL CLAW NOZZLE	10702111; 11882984; D1091991
LA2539	2-1/2 LOCKING LED CAR NOOZLE	D725856; 9700187; 10238255
LA2518	TELESCOPING WAND, 2-1/2"	12419476; D1085602
MA12552	1-1/4" PREMIUM AUTO CLEANING KIT	8533907
MA17839	1-7/8" LED LIGHTED CAR NOZZLE	D725856
MA17852	1-7/8" BASIC CAR CLEANING KIT	8533907
MA17854	1-7/8" BASIC HOMEOWNER'S KIT	8533907
MA25052	2-1/2" BASIC CAR CLEANING KIT	8533907
MA25054	2-1/2" BASIC HOMEOWNER'S KIT	8533907
MAX2501	MAX ROTATING DUSTING BRUSH W/ HARD BRISTLE SHOE	10702111
MAX2502	MAX CREVICE TOOL	10702111
MAX2503	MAX CAR NOZZLE	10702111
MAX2509	MAX UTILITY NOZZLE	10702111
MAX2510	MAX FLOOR TOOL W/ WET SHOE	10702111; D1081048; D1104385
MAX2512	MAX LOCKING FLOOR TOOL DISP	10702111; D1081048
MAX2514	MAX FLOOR TOOL W/ HARD AND SOFT BRISTLE SHOES	10702111; D1081048; D1102070
MAX2530	MAX CONTRACTOR KIT (UTILITY / DUSTING BRUSH / CREVICE TOOL / SHOES)	10702111; D1102071
MAX2531	MAX KIT (MAX DUSTING BRUSH / CREVICE TOOL / WITH SHOES)	10702111
PG0300	PRO GEAR ACCESSORY	D1056379
SK0100	SHOE KIT - DUSTING BRUSH (HARD / SOFT / OVERMOLDED)	PATENT PENDING
SK0101	SHOE KIT - DUSTING BRUSH (HARD - 2 PK)	PATENT PENDING
SK0200	SHOE KIT - CREVICE TOOL (HARD / SOFT)	PATENT PENDING
SK0300	SHOE KIT - CAR NOZZLE (HARD / SOFT / OVERMOLDED)	D1106626
SK0400	NXT CLAW NOZZLE SHOE KIT	D1106626
SK0900	SHOE KIT - UTILITY NOZZLE (HARD / SOFT / OVERMOLDED)	D1102071
SK1500	SHOE KIT - FLOOR TOOL (HARD / SOFT)	D1102070
SK1501	FLOOR TOOL SHOE - HARD	D1102070
SK1502	FLOOR TOOL SHOE - SOFT	D1102070
SK1503	FLOOR TOOL SHOE - WET	D1104385
VT1710	1 7/8" WET NOZZLE	7661175
VT1714	1-7/8" x 10-1/2 FLOOR BRUSH	5706550
VT1718	TELESCOPING WAND, 1-7/8"	12419476; D1085602
VT1736	1-7/8" RIDGID LED PASSTHROUGH	D1056381; D1091032
VT1739	1 7/8" CAR NOZZLE (BLACK) LED	D725856; 9700187; 10238255
VT2514	2-1/2"-14" FLOOR BRUSH	5706550
VT2525	NOISE MUFFLER	D544090; D729926
VT2525RT	72927 - NOISE MUFFLER	6035485
VT2532	FLEXIBLE CREVICE TOOL WITH 2 1/2 ADAPTER ASM	8533907
VT2534	CAR ACCESSORY KIT	8533907
WS12532A	FLEXIBLE CREVICE TOOL W/2.5" ADAPTER	8533907
WS17814A	1-7/8" FLOOR BRUSH	5706550
WS17839A	1 7/8" CAR NOZZLE (BLACK) LED	D725856; 9700187; 10238255
WS25014A	2-1/2" FLOOR BRUSH	5706550
AIRMOVER	-	-
107132	PROTEAM AIRMOVER	D698433
107333	AIRMOVER	D698433
107133	PROTEAM AIRMOVER XP	D698433
107334	AIRMOVER XP	D698433
571782	AIRMOVER	D698433
107596	PROTEAM AIRMOVER XP	D698433
107597	AIRMOVER XP	D698433
AM2560	Air Mover	D698433
AM2265	Air Mover	D849924; D835254; D810269
AM2286	Air Mover	D849924; D835254; D810269
AM2287	Air Mover	D849924; D835254; D810269
WS1625AM	WORKSHOP AIR MOVER WITH HANDLE & WHEELS	D698433
PROTEAM Wet/Dry Vacuum	-	-
107365	SCP 6 VAC W/KIT 106263	D726978; 9456722; 9861242
107367	SCP 10 VAC W/KIT 106263	D726978; 9456722; 9861242
107433	GOFREE PRO W/KIT 106263	D697024; D719911
107469	SCP6 W/107466 KIT	D726978; 9456722; 9861242
107470	SCP 10 W/107466 KIT	D726978; 9456722; 9861242
107512	GFFP W/107463 KIT	D726978; 9456722; 9861242

107622	SUPER COACH PRO 6 W/107532 KIT	D726978; 9456722; 9861242
107623	SUPER COACH PRO 10 W/107532 KIT	D726978; 9456722; 9861242
107624	GOFREE FLEX PRO W/107532 KIT	D726978; 9456722; 9861242
DIRT HOUND		
DH0500	5 GAL WET/DRY VAC	D520689; D1021303
VAC MODELS:		
17611	2-1/2 GAL WET/DRY VAC	8206482; 8557008; D1021303
17612	4 GAL WET/DRY VAC	8206482; 8557008; D1021303
29900	2.5 GAL WET/DRY VAC CANADA	8206482; 8557008; D1021303
29901	SUPPLIED DETACHED	8206482; 8557008; D1021303
WD0525	5 GAL WET/DRY VAC	8206482; 8557008; D1021303
WD2025	2 1/2 GAL WET/DRY VAC	8206482; 8557008; D1021303
CARTRIDGE FILTERS:		
17810	FILTER ASM	8206482; 8557008; D1021303; 9345372
38741	FILTER ASM	8206482; 8557008; D1021303; 9345372
38773	FILTER ASM WET	9510718; 8206482; D691338
97210	FILTER ASM	8206482; 8557008; D1021303; 9345372
97315	FILTER ASM WET	9510718; 8206482; D691338
107177	FILTER ASM WET	9510718; 8206482; D691338
9345372	FILTER ASM	8206482; 8557008; D1021303; 9345372
CMXZVBE38740	FILTER ASM	8206482; 8557008; D1021303; 9345372
CMXZVBE38741	FILTER ASM	8206482; 8557008; D1021303; 9345372
CMXZVBE38751	FILTER ASM	8206482; 8557008; D1021303; 9345372
CMXZVBE38753	FILTER ASM	8206482; 8557008; D1021303; 9345372
CMXZVBE38754	FILTER ASM	8206482; 8557008; D1021303; 9345372
CMXZVBE38773	FILTER ASM WET	9510718; 8206482; D691338
CMXZVBE43969	FILTER ASM	8206482; 8557008; D1021303; 9345372
RRF7000	FILTER ASM WET	9510718; 8206482; D691338
VF3400	FILTER ASM	8206482; 8557008; D1021303; 9345372
VF3500	FILTER ASM	8206482; 8557008; D1021303; 9345372
VF3600	FILTER ASM	8206482; 8557008; D1021303; 9345372
VF3700	FILTER ASM WET	9510718; 8206482; D691338
VF3800	FILTER ASM	8206482; 8557008; D1021303; 9345372
VF4000	FILTER ASM	8206482; 8557008; D1021303; 9345372
VF4700	FILTER ASM WET	9510718; 8206482; D691338
VF5000	FILTER ASM	8206482; 8557008; D1021303; 9345372
VF6000	FILTER ASM	8206482; 8557008; D1021303; 9345372
VF7000	FILTER ASM WET	9510718; 8206482; D691338
VF7000RT	FILTER ASM WET	9510718; 8206482; D691338
VF8000	FILTER ASM	8206482; 8557008; D1021303; 9345372
WS11045F	FILTER ASM	8206482; 8557008; D1021303; 9345372
WS12045F	FILTER ASM	8206482; 8557008; D1021303; 9345372
WS13045F	FILTER ASM	8206482; 8557008; D1021303; 9345372
WS14045F	FILTER ASM WET	9510718; 8206482; D691338
WS21200F	FILTER ASM	8206482; 8557008; D1021303; 9345372
WS22200F	FILTER ASM	8206482; 8557008; D1021303; 9345372
WS23200F	FILTER ASM	8206482; 8557008; D1021303; 9345372
WS24200F	FILTER ASM WET	9510718; 8206482; D691338
PROTEAM Wet/Dry Vacuum		
107354	SUPERCOACH PRO 6 VAC W/KIT 107098	D726978; 9456722; 9861242
107355	SUPERCOACH PRO 6 VAC W/KIT 107100	D726978; 9456722; 9861242
107387	SUPERCOACH PRO 6 VAC W/KIT 106820	D726978; 9456722; 9861242
107357	SUPERCOACH PRO 10 VAC W/KIT 107098	D726978; 9456722; 9861242
107358	SUPERCOACH PRO 10 VAC W/KIT 107100	D726978; 9456722; 9861242
107388	SUPERCOACH PRO 10 VAC W/KIT 106820	D726978; 9456722; 9861242
107620	SUPER COACH PRO 6 W/107532 KIT	D726978; 9456722; 9861242
107621	SUPER COACH PRO 10 W/107532 KIT	D726978; 9456722; 9861242
PROTEAM Wet/Dry Vacuum		
107410	PROTEAM PROGUARD LI 3 CORDLESS VAC	9675225
107416	PROVAC FS 6 W/100727 REST PKG	D726978; 9456722; 9861242
107437	SUPER COACH PRO 10 W/107100 KIT	D726978; 9456722; 9861242
107438	SUPER COACH PRO 6 W/107100 KIT	D726978; 9456722; 9861242
107441	GOFREE FLEX PRO W/12AH BATTERY; 107100 KIT	D697024; D719911

107442	GOFREE FLEX PRO W/6AH BATTERY, 107100 KIT	D697024; D719911
GO CLEAN	-	-
BV100	GOCLEAN BACK VAC	8533907
BV100Q	GOCLEAN BACK VAC	8533907
GC200	GOCLEAN VAC	8533907
TRANSPORTATION VACUUM	-	-
CV0100	TRANSPORTATION VACUUM ASSEMBLY	9751504; 10099659; 9775478; 10750915; 10791892
CV0200	TRANSPORTATION VACUUM ASSEMBLY	9751504; 10099659; 9775478; 10750915; 10791892
CV0300	TRANSPORTATION VACUUM ASSEMBLY	9751504; 10099659; 9775478; 10791892

Date: 1/9/2026

Rev.: 0