



Explore Emerson Australia & New Zealand Newsletter August Issue

Jump directly into the section below that interests you!

- [A Word from Boris Gabin](#)
- [Free Webinars](#)
- [Proven Results](#)
- [Product News](#)
- [Educational Services](#)

A Word from Boris Gabin

Emerson introduces groundbreaking synchronisation software for power and water control systems



At Emerson, we're committed to helping our customers operate more efficiently, reliably, and with greater confidence. That's why we're proud to introduce the [Ovation™ Curation Tool](#), the industry's first synchronisation solution designed to maintain alignment between Ovation control systems and their digital twin simulations.

Digital twins are powerful tools for testing, training, and optimising operations, but keeping them

synchronised with live plant systems can be challenging. As production environments evolve, manual updates can consume valuable engineering resources and increase the risk of configuration drift.

The Ovation Curation Tool addresses this challenge by automatically tracking system changes, maintaining detailed version histories, and streamlining deployment across control systems and simulations. By improving digital twin accuracy, reducing engineering effort, and simplifying troubleshooting and governance, the solution helps customers maximise the value of their operational technology investments.

As the industry continues to embrace digital transformation, innovations like the Ovation Curation Tool are making it easier for organisations to enhance performance, strengthen resilience, and prepare for the future.

Free Webinars

Smarter Tank Operations: Improving accuracy, safety and efficiency without the disruption



Title	Date/Time	Registration
Taking Control of Tank Inventory: Practical Ways to Improve Accuracy and Efficiency	Sep 17, 2026, 1:00 PM AEST 60 min	Register Here
Modernising Tank Gauging in Brownfield Sites: What Actually Works	Sep 24, 2026, 1:00 PM AEST 60 min	Register Here
Safer Tanks, Fewer Surprises: Practical Overfill & Floating Roof Monitoring Solutions	Oct 1, 2026, 1:00 PM AEST 60 min	Register Here
Right-Sizing Tank Monitoring Solutions for Smaller Tank Farms & Remote Sites	Oct 8, 2026, 1:00 PM AEST 60 min	Register Here

Proven Results

Case Study Video



Detecting the Invisible: Nitrous oxide leakage often goes undetected, but the impact on costs, operations, and sustainability can be significant.

At Children's Hospital at Westmead, Sydney, enhanced Medical Gas Pipeline System (MGPS) monitoring is providing the visibility needed to detect and quantify N₂O leakage. With actionable insights at their fingertips, stakeholders can improve operational performance, reduce waste, and advance sustainability initiatives.

[View Video >](#)

Case Study

LNG Site Solves Vibration Issues in Rich Amine Letdown Valve



Site able to run at full capacity within 3 days with no excessive vibration

[Learn More >](#)

Product News

Next-Generation Portable Ultrasonic Flow Meters Offer Greater Flexibility for Plant-Wide Transparency



- Flexim™ FLUXUS 631 series of portable non-intrusive clamp-on ultrasonic flow meters measures liquids, gases and steam.
- Enables quick, temporary, on-demand flow measurement without interrupting operations.
- Supports flow meter and equipment verification, condition monitoring, leak detection and energy performance analysis.

[Learn More >](#)

Emerson Expands Flame Detection Portfolio for Broader Application Flexibility



The Rosemount™ 965 Flame Detector uses four infrared sensors to help distinguish hydrocarbon fires from non-flame background radiation.

[Learn More >](#)

New Combustible Gas Detection to Core Wireless Sensor for Enhanced Safety Coverage in Hard-to-Reach Areas



The Rosemount™ 928 Wireless Gas Monitor now includes combustible gas detection for percent lower explosive limit (%LEL) monitoring over the WirelessHART platform, extending coverage to hard-to-reach areas.

[Learn More >](#)

Emerson Delivers First-of-its-Kind Synchronisation Software for Power and Water Control Systems




Emerson's Ovation™ Curation Tool uses intuitive automated synchronisation to enable fast and easy deployment of system changes to simulations and other control systems via an intuitive dashboard.

[Learn More >](#)

Educational Services



Course	Dates	Location
GC 700XA Operations and Maintenance Training Course R4213 	Sep 22-25, 2026 Oct 13-16, 2026 Nov 17-20, 2026 Nov 30-Dec 3, 2026	Bayswater, VIC
Rosemount 8700/ 8800 / Micro Motion Series 1000/2000 Course 2340, 2341, 2358   	Nov 11-13, 2026 Dec 8-9, 2026 Dec 10, 2026	Perth, WA
Rosemount Tank Gauging Training	Sep 8-9, 2026 Oct 6-7, 2026 Nov 10-11, 2026 Dec 8-9, 2026	VIC and QLD
Rosemount Tank Master Training	Sep 10, 2026 Oct 8, 2026 Nov 12, 2026 Dec 10, 2026	VIC and QLD
Pressure, Temperature, Multivariable DP Flow Customized Training Program	Oct 20-22, 2026 Nov 3-5, 2026 Dec 15-17, 2026	VIC, NSW, SA, QLD WA
DeltaV Continuous Operation 7012	Sep 21-22, 2026	Virtual
DeltaV Hardware and Troubleshooting 7018	Sep 1-3, 2026 Sept 23-25, 2026	Perth, WA Bayswater, VIC
DeltaV Implementation using Live 7409	Sept 14-18, 2026	Bayswater, VIC

Have a question or need more information? Complete our [Contact Us](#) form and a member of our team will be in touch shortly.