

Fisher™ ET, EAT and ETR

Sliding-Stem Control Valves



General Application

Fisher ET, EAT and ETR general-purpose control valves (Figures 3, 4 and 5) are used for throttling or on-off control of a wide variety of liquids and gases. All three valve designs have single ports, balanced valve plugs and cage guiding. Metal-to-PTFE seating for stringent shutoff requirements is standard in all valves except those with Cavitrol III cages. Metal-to-metal seating for higher temperatures is standard for valves with Cavitrol III cages and optional for all other valves.

The temperature limits of ET valves can be extended above 232°C / 450°F by using PEEK (PolyEtherEtherKetone) anti-extrusion rings in combination with a spring-loaded PTFE seal. The PEEK anti-extrusion rings expand to close off the clearance gap between the plug and the cage where the PTFE seal may extrude at high temperatures and pressures. The temperature limits are extended to 316°C / 600°F for non-oxidizing service and to 260°C / 500°F for oxidizing service.

The ET product line is available for a wide range of applications, including sulfide and chloride stress-cracking environments common to the oil and gas production industries. To discuss available constructions, contact your [Emerson sales office](#) and include the applicable codes and standards required for these environments.

The easy-e™ Valve Family

ET, EAT and ETR control valves are part of the versatile easy-e family of Fisher industrial control valves. Easy-e valves share the following characteristics:

- Multiple trim material choices
- Interchangeable, restricted-capacity trims and full-sized trims to match variable process flow demands
- Different cage/plug styles that provide particular flow characteristics for highly-specialized applications. The standard cage comes in three different flow characteristics: quick-opening, linear or equal percentage.

Figure 1. Fisher ET Valve With 667 Actuator and Fisher Fieldvue™ DVC7K



X1968

- Whisper Trim™ I, Whisper Trim III (Figure 8) and Whisper NXG Trim and WhisperFlo™ cages (Figures 6 and 7) attenuate aerodynamic noise in gaseous service.
- To help eliminate cavitation damage in a properly-sized valve, a standard-travel, Cavitrol III, one-stage cage (Figure 10) and a long-travel, Cavitrol III, two-stage cage are available in the NPS 1 through NPS 8 ET control valve.

Features

- Compliance with the Clean Air Act—ENVIRO-SEAL™ packing systems (Figures 11 and 12) that provide an improved stem seal to help prevent the loss of process fluid are available. These packing systems feature PTFE or Graphite ULF packing with live-loading for reduced packing maintenance.
- PTFE Seating for Long-Lasting Shutoff Capability—Controlled compression of standard seat construction protects PTFE disk between metal disk seat and disk retainer (Figure 3). Only the edge of the PTFE disk is contacted by the flowstream during normal operation. Excellent shutoff is maintained by a backup ring or spring-loading that forces the valve plug seal ring against the cage (Figure 3).
- Valve Plug Stability—Rugged cage guiding provides high valve plug stability, which reduces vibration and mechanical noise.
- Cost-Effective Operation and Maintenance Economy—Increased wear resistance of hardened stainless steel trim means longer-lasting service. When inspection or maintenance is necessary, the body can stay in the pipeline during removal of trim parts. Balanced valve plug construction permits use of smaller, lower-cost Fisher actuators. The ETR valve also permits easy body interior access without having to remove the bonnet or actuator (Figure 5). And, trim inventory costs are cut because dimensional standardization permits use of most standard easy-e trim parts.
- Compliance with European Standards—Valves are available with dimensions specified by EN/DIN standards. See Figure 16.
- Sour Service Capability—Unless otherwise noted, references are to NACE MR0175-2002. Optional materials are available to meet NACE MR0103 and NACE MR0175 / ISO 15156. Material requirements under these standards vary by edition and year of issue; the specific standard must be specified.

Table 1. Specifications

Available Configurations	Maximum Pressure Drops ⁽²⁾
ET: Single-port, globe-style control valve with cage guiding, balanced valve plug and push-down-to-close valve plug action (Figure 3) EAT: Angle version of ET control valve, used to facilitate piping or in applications where a self-draining valve is desired (Figure 4) ETR: Same as ET control valve except with push-down-to-open valve plug action (Figure 5)	Same as maximum inlet pressure for specific construction defined above, except where further limited as follows: All Valves Except Those with Cavitrol III, Whisper Trim III, Whisper NXG Trim and WhisperFlo Cages: See Figure 13. Valves with Cavitrol III Cages: See Figure 14. Valves with Whisper Trim III and Whisper NXG Trim Cages: 0.999 $\Delta P/P_1$ maximum for levels A1 through D3 Valves for NACE MR0175 / ISO 15156 and MR0103: See Figure 15
Valve Sizes and End Connection Styles	Shutoff Classifications Per ANSI/FCI 70-2 and IEC 60534-4
Flanged raised-face per EN 1092-1/B and see Table 3.	Class IV, V or VI. See Tables 4, 6 or 7
Maximum Inlet Pressures and Temperatures ^{(1), (2)}	Construction Materials
As listed below, unless limited by maximum pressure drop or material temperature capabilities Valves with Cast Iron Bodies Flanged: Consistent with CL125B or 250B per ASME B16.1 Valves with Steel and Stainless Steel Bodies Flanged: Consistent with CL150, 300 and 600 ⁽³⁾ per ASME B16.34 Screwed or Welding: Consistent with flanged CL600 per ASME B16.34	Body, Bonnet and Bonnet Spacer or Bottom Flange, if used: ■ Cast iron, ■ WCC carbon steel or ■ LCC carbon steel, ■ WC9 chrome moly steel, ■ CF8M (cast 316 stainless steel), ■ CF3M (cast 316L stainless steel) or ■ other materials upon request Valve Plug, Cage and Metal Seating Parts: All Valves Except Those with Cavitrol III, Whisper NXG Trim or Whisper Trim III Cages: See Table 8 Valves with Cavitrol III Cages: See Table 9 Valves with Whisper Trim III and Whisper NXG Trim Cages: See Table 12 Valves with WhisperFlo Cages: See Table 11 Bellows Seal Assembly: ■ 316L stainless steel or ■ N04400 All Other Parts: See Table 14

- continued -

Table 1. Specifications (continued)

Material Temperature Capabilities ⁽²⁾	Yoke Boss and Stem Diameters
Body/Trim Combinations: All Valves Except Those with Cavitrol III, Whisper NXG Trim or Whisper Trim III Cages: See Figure 13 Valves with Cavitrol III Cages: See Table 9 Valves with Whisper Trim III and Whisper NXG Trim Cages: See Table 12 Valves with WhisperFlo Cages: See Table 11 Bolting For NACE MR0175 / ISO 15156 and MR0103: See Table 24 Bonnets: See Table 16 All Other Parts: See Table 14	See Table 19
Flow Characteristics	Typical Bonnet Styles
Standard Cages: ■ Quick-opening, ■ linear or ■ equal percentage Whisper Trim, WhisperFlo and Cavitrol Cages: Linear	See Table 16
Flow Directions	Packing Arrangements
ET Standard Cage: Normally down Whisper Trim and WhisperFlo Cages: Always up Cavitrol Cage: Always down EAT Standard Cage with Liner for Metal Seat: Normally down Standard Cage without Liner: Flow up or down Whisper Trim and WhisperFlo Cages: Always up ETR Standard Cage: Normally up Whisper Trim Cage: Always down	Standard Material: Single PTFE V-ring Optional Materials: See Table 14 ENVIRO-SEAL Packing Systems: See Figures 11 and 12 ENVIRO-SEAL Packing Systems in vacuum service: Standard ENVIRO-SEAL packing systems can be used in vacuum service with packing rings in standard orientation. Do not reverse the ENVIRO-SEAL PTFE packing rings. Also, see Bulletin 59.1:061, ENVIRO-SEAL Packing Systems for Sliding-Stem Valves (D101633X012).
Flow Coefficients and Noise Level Prediction	Approximate Weights
See Table 11 and Catalog 12.	NPS 1: 14 kg / 30 lb NPS 1-1/2: 20 kg / 45 lb NPS 2: 39 kg / 85 lb NPS 2-1/2: 45 kg / 100 lb NPS 3: 57 kg / 125 lb NPS 4: 77 kg / 170 lb NPS 6: 159 kg / 350 lb NPS 8: 408 kg / 900 lb
Port Diameters and Maximum Valve Plug Travels	Optional Safety Instrumented System Classification
See Tables 18, 20 and 18	SIL3 capable — certified by exida Consulting LLC
	Additional Options
	■ Lubricator, ■ lubricator/isolating valve, ■ drilled and tapped connection in extension bonnet for leak-off service, ■ body drain plug, ■ style 3 fabricated extension bonnet made on order to a specific length for cryogenic service, ■ style NS bonnet for seismic service requirements, ■ packings suitable for nuclear service, ■ Class V shutoff for ET above 232°C / 450°F using PEEK anti-extrusion rings, ■ Trim Cartridge
1. EN (or other) ratings and end connections can usually be supplied; consult your Emerson sales office. 2. The pressure or temperature limits in this bulletin and any applicable code limitations, should not be exceeded. 3. Certain bonnet bolting material selections may require a CL600 easy-e valve assembly to be derated. Contact your Emerson Automation Solutions sales office for more information. 4. Limitation based on excessive noise increase if max ΔP/P₁ ratio for a given cage level is exceeded.	

Table 2. ENVIRO-SEAL Packing System Specifications

Applicable Stem Diameters	Construction Materials
■ 9.5 mm / 3/8 in., ■ 12.7 mm / 1/2 in., ■ 19.1 mm / 3/4 in., ■ 25.4 mm / 1 in. and ■ 31.8 mm / 1-1/4 in. diameter valve stems	PTFE Packing Systems Packing Ring and Lower Wiper: PTFE V-ring ⁽³⁾ Male and Female Adaptor Rings: Carbon-filled PTFE V-ring Graphite ULF Packing Systems: Graphite rings Duplex Packing Systems: Male and Female Adaptor Rings: Carbon-filled PTFE V-ring Guide Bushings: Carbon graphite Packing Rings: Graphite composite Packing Washer: PTFE Anti-Extrusion Washer: Filled PTFE (not required for Graphite ULF or duplex packing) Lantern Ring: S31600 (316 stainless steel) (not required for Graphite ULF packing) Packing Box Flange: S31600 Spring: ■ 17-7PH stainless steel or ■ N06600 Packing Follower: S31600 lined with carbon-filled PTFE Packing Box Studs: Strain-hardened 316 stainless steel Packing Box Nuts: 316 stainless steel SA194 Grade 8M
Maximum Pressure/Temperature Limits ⁽¹⁾	
To Meet the EPA Fugitive Emission Standard of 100 PPM ⁽²⁾ For ENVIRO-SEAL PTFE and ENVIRO-SEAL Duplex packing systems: full CL300 up to 232°C / 450°F For ENVIRO-SEAL Graphite ULF packing: 104 bar / 1500 psig at 316°C / 600°F	
1. Refer to the valve specifications in this bulletin for pressure/temperature limits of valve parts. Do not exceed the pressure/temperature rating of the valve. Do not exceed any applicable code or standard limitation. 2. The Environmental Protection Agency (EPA) has set a limit of 100 parts per million (ppm) for fugitive emissions from a valve in selected VOC (Volatile Organic Compound) services. 3. In vacuum service, it is not necessary to reverse the ENVIRO-SEAL PTFE packing rings.	

Table 3. Available Constructions

VALVE	VALVE SIZE, NPS	VALVE BODY MATERIAL AND END CONNECTION STYLE ⁽¹⁾							
		Cast Iron Valve Body		Carbon Steel, Alloy Steel or Stainless Steel Valve Body					
		CL125 FF Flanged	CL250 RF Flanged	Screwed	RF or RTJ Flanged			Butt Weld	Socket Weld
CL150	CL300				CL600				
ET	1, 1-1/2 or 2 2-1/2, 3, 4, 6 or 8	X X	X X	X ---	X X	X X	X X	X X	X X
EAT	1 or 2 3, 4 or 6	--- ---	--- ---	--- ---	X X	X X	X X	X X	X X
ETR	1, 1-1/2 or 2 2-1/2, 3 or 4	--- ---	--- ---	X ---	X ---	X ---	X ---	X ---	X ---
VALVE	VALVE SIZE, DN	STEEL VALVE BODY MATERIAL AND RAISED-FACE END CONNECTION STYLE ⁽²⁾							
		PN16	PN25	PN40	PN63	PN100			
ET	25, 40, 50, 65, 80, 100, 150 or 200	X	X	X	X	X			
EAT	25, 50, 80, 100 or 150	X	X	X	X	X			
ETR	25, 40, 50, 65, 80 or 100	X	X	X	X	X			
X = Available Construction. 1. End connection style abbreviations: FF - Flat Faced, RF - Raised Face, RTJ - Ring Type Joint. 2. End connection EN1092-1/B.									

Table 4. Shutoff Classifications Per ANSI/FCI 70-2 and IEC 60534-4

Valve Design	Seating	Shutoff Class
All except those with Cavitrol III cages	PTFE	V Air Test
		V (optional)
		VI (optional) ⁽³⁾
	Metal	IV (standard)
		V (optional) ⁽¹⁾
		VI (optional) ⁽³⁾
ET with Cavitrol III one-stage cage	Metal	IV (standard)
		V (optional)
ET with Cavitrol III two-stage cages	Metal	V
ET and EAT with TSO (Tight Shutoff) trim (CL125 through 600)	Replaceable, protected soft seat	TSO ⁽²⁾ TSO is not an ANSI/FCI leakage class. Valves with TSO trim are factory tested to a more stringent Emerson test requirement of no leakage at time of shipment. Test medium is water. Specify service P when ordering. Shutoff class V.
ET with TSO (Tight Shutoff) trim (CL125 through 600)	Std or Cavitrol III trim. Replaceable, protected soft seat	
1. Class V shutoff requires spring-loaded seal ring, radius-seat plug and wide-bevel seat ring (not available with 8-in. port, quick-opening cage). Not available with trims 4, 29 and 85. 2. For additional information, contact your Emerson sales office . 3. Refer to Table 6.		

Trim Cartridge

In addition to traditional trim selections outlined in this product bulletin, some configurations of Fisher ET control valves are also available with Trim Cartridge. Trim Cartridge combines all valve trim components plus the bonnet in a single, serialized cartridge. Trim Cartridge simplifies valve repair by streamlining valve repair procurement, inventory and execution and is available as both a trim option in new valve assemblies or as a repair solution.

In new valve assemblies, Trim Cartridge simplifies repair parts procurement, inventory and budgeting. Trim Cartridge provides complete trim and bonnet repair in a single part number reducing the amount of part numbers to order and a single box to inventory. It also increases maintenance budgeting accuracy as Trim Cartridge provides a more consistent trim repair cost due to its streamlined installation and complete trim repair design.

As a repair part, Trim Cartridge reduces a more than 20 part repair process to a single pre-assembled repair cartridge, seat ring gasket and body to bonnet gasket. Each Trim Cartridge comes seat leak tested to CL V shut off and has pre-set ENVIRO-SEAL packing. Its factory assembled and tested design greatly reduces complexity and allows for streamlined installation and decreased repair time. Trim Cartridge can be utilized as a complete trim and bonnet repair solution for control valves with existing traditional trim or Trim Cartridge.

Figure 2. Fisher Trim Cartridge



Trim Cartridge contains ENVIRO-SEAL PTFE packing as the standard packing offering. Other available packing options are ENVIRO-SEAL Graphite ULF and ENVIRO-SEAL duplex. PEEK high temperature anti-extrusion rings are also available.

Trim Cartridge is fully backward compatible and has the same flow characteristics as comparable traditional trim.

Table 5. Trim Cartridge Table⁽¹⁾

VALVE	BONNET MATERIAL	SIZES	CHARACTERISTIC	STEM SIZES, IN	TRIM NUMBER	PLUG MATERIAL	ET CAGE MATERIAL	SEAT MATERIAL	STEM MATERIAL
ET	WCC, LCC, CF8M	NPS 1 to 4 Full and Reduced Ports	Equal Percent, Linear	3/8 and 1/2 (NPS 1 and 1.5)	1TC	416 SST	17-4 SST	17-4 SST	316 SST
					27TC	316 SST HF Seat and Guide	316 Chrome Plate	316 SST with CoCr-A HF	
				1/2 (NPS 2, 3 and 4)	29TC	316 SST		316 SST	S20910
					85TC (NACE)	316 SST		316 SST with CoCr-A HF	
					87TC (NACE)	316 SST HF Seat and Guide			

1. If ordering a butt-weld or socket weld end valve that requires post-weld heat treatment after installation, Trim Cartridge should not be selected.

ENVIRO-SEAL, HIGH-SEAL Packing Systems

ENVIRO-SEAL and HIGH-SEAL packing systems offer exceptional sealing capabilities. These systems easily install in existing valves or can be purchased with new valves. These systems help seal the process to conserve valuable process fluid. The long-life and reliability of these systems also reduce maintenance costs and downtime.

For applications requiring compliance with environmental protection regulations, the unique ENVIRO-SEAL packing system (Figure 12) and a unique ENVIRO-SEAL bellows seal system (Figure 11) are offered. The emission control packing system keeps emission concentrations below the EPA 100 ppm requirement.

For an excellent stem seal in applications that are not environmentally-sensitive, the HIGH-SEAL Graphite ULF packing system (Figure 12) is offered. The HIGH-SEAL packing system provides improved sealing at pressure/temperature ratings beyond ENVIRO-SEAL limits.

ENVIRO-SEAL packing systems, available with PTFE, Graphite ULF or duplex packing and the HIGH-SEAL Graphite ULF packing system feature live-loading and unique packing-ring arrangements for long-term, consistent sealing performance.

ANSI/FCI Class VI Shutoff Capabilities

ET valves with soft seat and metal seat constructions can provide ANSI/FCI Class VI shut-off capabilities. See Tables 6 and 7.

Table 6. Class VI Shutoff Availability^(1, 2)

Valve	Port Size, In.	Seat	Minimum Seat Load
ET	≥3.4375 ≤7	Soft	See Catalog 14
ET	≥3.4375 ≤7	Metal	300 lbs/lineal inch

1. Limited retrofit capability. Consult your [Emerson sales office](#).


2. Not for use with NPS 8.

Table 7. Class VI Trim Materials

VALVE	CAGE/SEAT RING RETAINER	VALVE PLUG	SEAT RING	SEAL RING	TRIM TEMPERATURE LIMIT	
					°C	°F
ET	316 SST / ENC	S31600 with standard beveled seat	S31600/PTFE	UHMWPE ⁽¹⁾ R30003	-198 to 66	-325 to 150
	316 SST / ENC	S31600/CoCr-A seat with radiused seat (special design)	S31600 with wide beveled seat (special design)	UHMWPE R30003	-198 to 66	-325 to 150
	17-4 SST (17-4PH SST)	S41600 with standard beveled seat	S31600/PTFE	UHMWPE R30003	-29 to 66	-20 to 150
	17-4 SST	S41600 with radiused seat (special design)	S31600 with wide beveled seat (special design)	UHMWPE R30003	-29 to 66	-20 to 150

1. UHMWPE (Ultra High Molecular Weight Polyethylene)

Figure 3. Fisher ET Sectional with Standard Cages



SPRING-LOADED SEAL RING CONSTRUCTION FOR USE WITH CAVITROL CAGES AND FOR METAL SEAT WITH OPTIONAL CLASS V SHUTOFF




Figure 4. Fisher EAT Sectional




Figure 5. Fisher ETR Sectional




Figure 6. Typical Valve with WhisperFlo Aerodynamic or Whisper NXG Trim






Figure 7. Typical WhisperFlo Cage



W7065

W6851-1

Table 8. Typical Combinations of Metal Trim Parts for All Valves Except Those for NACE MR0175 / ISO 15156 and MR0103 Specifications⁽¹⁾, Cavitrol III⁽²⁾, Whisper NXG Trim, Whisper Trim III⁽³⁾ and 4, 6 and 8-In. WhisperFlo Cages⁽⁶⁾

Trim Designation	Valve Plug	Cage	Disk Seat and Retainer for Standard PTFE-Seat Construction	Seat Ring or Liner for Optional Metal-Seat Construction	Optional Liner (Metal Seat EAT Valve Only)
1 (typically used with optional metal-seat constructions in all designs and body materials except CF8M)	S41600 HT	17-4 SST HT	---	S41600 HT or CA15 HT ⁽⁴⁾	S41600 HT
	17-4 SST HT HT ⁽⁵⁾	17-4 SST HT ⁽⁵⁾			
3	S31600 with seat and guide hard faced with CoCr-A hardfacing alloy	R30006 or R30016 (alloy 6)	---	R30006 (alloy 6)	---
4 ⁽⁷⁾	S31600	17-4 SST HT	S31600	S31600	S31600
5 ⁽⁵⁾	S31600 with seat and guide hard faced with CoCr-A hardfacing alloy	R31233	R30006 Disk Seat and retainer	R30006 (alloy 6)	---
6 ⁽⁵⁾	S31600 with seat and guide hard faced with CoCr-A hardfacing alloy	S31603 CRPL	R30006 Disk Seat and retainer	R30006 (alloy 6)	---
27	S31600 with seat and guide hard faced with CoCr-A hardfacing alloy	316 SST with electroless nickel coating (ENC)	S31600 disk retainer with CoCr-A disk seat	R30006 (alloy 6)	---
28 ⁽⁸⁾	S31600 with seat hard faced with CoCr-A hardfacing alloy	316 SST with electroless nickel coating (ENC)	S31600 disk retainer with CoCr-A disk seat	R30006 (alloy 6)	---
29 (standard for CF8M bodies in all designs regardless of seat construction) ⁽⁸⁾	S31600	316 SST with electroless nickel coating (ENC)	S31600	S31600	S31600
37 and 37H (trim 37H has clearances for high-temperature service above 210°C / 410°F)	S31600 with seat and guide hard faced with CoCr-A	17-4 SST HT	S31600 disk retainer with CoCr-A disk seat	Seat Ring: R30006 (alloy 6)	---

- continued -

Table 8. Typical Combinations of Metal Trim Parts for All Valves Except Those for NACE MR0175 / ISO 15156 and MR0103 Specifications⁽¹⁾, Cavitrol III⁽²⁾, Whisper NXG Trim, Whisper Trim III⁽³⁾ and 4, 6 and 8-In. WhisperFlo Cages⁽⁶⁾ (continued)

Trim Designation	Valve Plug	Cage	Disk Seat and Retainer for Standard PTFE-Seat Construction	Seat Ring or Liner for Optional Metal-Seat Construction	Optional Liner (Metal Seat EAT Valve Only)
57 (standard for standard PTFE-seat ET, EAT, ETR in all body materials except CF8M)	S41600 HT	17-4 SST HT ⁽⁵⁾	S31600	---	---
	17-4 SST HT ⁽⁵⁾				
316L	S31603	316L SST with electroless nickel coating (ENC)	S31603	S31603	---
316L HF	S31603 with seat and guide hard faced with CoCr-A hardfacing alloy	316L SST with electroless nickel coating (ENC)	S31603 disk retainer with CoCr-A disk seat	R30006 (alloy 6)	---
1. For NACE MR0175 / ISO 15156 and MR0103 specification trims, see Table 23. 2. For Cavitrol III trims, see Table 9. 3. For Whisper Trim III and Whisper NXG trims, see Table 12. 4. CA15 is used for NPS 6 and 8 full-sized and restricted-trim valves. 5. For 8-in. Whisper Trim I. 6. For 4, 6 and 8-in. WhisperFlo trims, see Table 11. 7. Not for use with Whisper Trim I. 8. Not for use with Whisper Trim I with 136 mm / 5.375 in. and larger ports.					

Table 9. Cavitrol III⁽¹⁾ Metal Trim Part Materials and Body/Trim Temperature Capabilities

TRIM DESIGNATION	VALVE PLUG	CAGE	CAGE RETAINER	SEAT RING	BODY AND BONNET		MATERIAL TEMPERATURE CAPABILITY			
							°C		°F	
							Min	Max	Min	Max
76	Heat-treated S42000	17-4 SST H900 for Cavitrol III 1-stage or 17-4 SST H1075 for Cavitrol III 2-stage	S31600	S17400 with H900 heat-treat condition	WCC carbon steel, WC9 chrome moly steel or LCC carbon steel		-29	These materials not limiting factors	-20	These materials not limiting factors
					CF8M	NPS 1, 1-1/2 or 2 valve body size	-29	These materials and sizes not limiting factors	-20	These materials and sizes not limiting factors
						NPS 2-1/2 or 3 valve body size	-29	216	-20	420
						NPS 4, 6 or 8 valve body size	-29	177	-20	350
1. Available only in NPS 1 through 8 ET valves.										

Table 10. DST⁽¹⁾ Metal Trim Part Materials and Body/Trim Temperature Capabilities

TRIM DESIGNATION	VALVE PLUG	CAGE	SEAT RING	BODY AND BONNET		MATERIAL TEMPERATURE CAPABILITY ⁽²⁾			
						°C		°F	
						Min	Max	Min	Max
581	R31233 Alloy	R31233	R31233	WCC		-29	316	-20	600
				LCC		-46	316	-50	600
				CF8M	NPS 3 NPS 4 Angle NPS 4 Globe (2-stage) NPS 6 Angle (2-stage) NPS 6 Globe (2-stage)	-73	316	-100	600
					NPS 4 Globe (3-stage) NPS 6 Angle (3-stage)	-73	204	-100	400
					NPS 6 Globe (3-Stage)	-73	260	-100	500
					NPS 8 Globe (3-Stage)	-73	149	-100	300

1. Available only in NPS 3 through 8 ET valves and NPS 4 through 6 EAT valves. For other materials and custom designs, see Bulletin 80.2:021 Dirty Service Trim (D102310X012).

2. PTFE/carbon seal ring with PEEK anti-extrusion rings may be used in temperatures up to 316°C / 600°F for non-oxidizing service or up to 260°C / 500°F for oxidizing service.

**Table 11. WhisperFlo Metal Trim Part Materials and Valve Body/Trim Temperature Capabilities
(NPS 4, 6 and 8 Fisher ET only)**

TRIM DESIGNATION	VALVE BODY	VALVE PLUG	CAGE	CAGE RETAINER	SEAT	MATERIAL TEMPERATURE CAPABILITY			
						°C		°F	
						Min	Max	Min	Max
901	WCC	S41600	410 SST	WCC ENC	S41600	-29	316	-20	600
902	WCC	S31600/CoCrA Seat and Guide	410 SST	WCC ENC	S31600/CoCrA	-29	316	-20	600
926	WCC	S31600/CoCrA Seat and Guide	410 SST NACE	WCC/NACE/ENC	S31600/CoCrA	-29	316	-20	600
936	316 CF8M	S31600/CoCrA Seat and Guide	316 SST/R31233	S31600/ENC	S31600/CoCrA	-198	316	-325	600
901C	WCC	S41000	410 SST	WCC ENC	S31600/PTFE	-29	232	-20	450
904C	WCC	S31600	410 SST	WCC ENC	S31600/PTFE	-29	149	-20	300
984C	WCC	S31600	410 SST NACE	WCC/NACE/ENC	S31600/PTFE	-29	149	-20	300
985C	CF8M	S31600	316 SST/R31233	S31600/ENC	S31600/PTFE	-73	149	-100	300
990	CD3MN	S31803/CoCrA Seat and Guide	2205 Duplex ⁽²⁾ / R31233	S31800/Cr Plate	S31803/ CoCrA Seat	-51	316	-60	600
	LCC					-46	316	-51	600
	WCC					-29	316	-20	600
990C	CD3MN	S31803/CoCrA Seat and Guide	2205 Duplex ⁽²⁾ / R31233	S31800/Cr Plate	S31803/PTFE	-51	232	-60	450
	LCC					-46	232	-51	450
	WCC					-29	232	-20	450

1. Temperatures above 232°C / 450°F require PEEK anti-extrusion rings and spring-loaded seal ring. This option allows ET construction to be used up to 316°C / 600°F for non-oxidizing service and 260°C / 500°F for oxidizing service.

2. 22 Cr-5Ni duplex stainless steel.

Table 12. Whisper Trim III and Whisper NXG Trim Metal Trim Part Materials and Body/Trim Temperature Capabilities

TRIM DESIGNATION	VALVE PLUG	CAGE	CAGE RETAINER	BAFFLE (FOR LEVEL D3 CAGE ONLY)	SEAT RING FOR METAL SEAT CONSTRUCTION	DISK SEAT AND RETAINER FOR PTFE SEAT CONSTRUCTION	STEM	BODY, BONNET AND BONNET SPACER	MATERIAL TEMPERATURE CAPABILITY			
									°C		°F	
									Min	Max	Min	Max
19.1 through 111.1, 177.8 and 203.2 mm / 0.75 through 4.375, 7 and 8 in. Port Sizes with Whisper Trim III Cage												
301G	S41600	17-4 SST	---	Steel	S41600	---	S31600	WCC, WC9	-29	316 ⁽²⁾	-20	600 ⁽²⁾
								CF8M ⁽⁵⁾	-29	176	-20	350
301GC	S41600	17-4 SST	---	Steel	---	S31600	S31600	WCC, WC9	-29	204	-20	400
								CF8M	-29	176	-20	350
312G ⁽¹⁾	S31600/ CoCr-A Seat and Guide	316 SST/ENC Electroless Nickel Coated	---	S31600	R30006	---	S20910	WCC, WC9	-29	316 ⁽²⁾	-20	600 ⁽²⁾
								CF8M	-198	316 ⁽²⁾	-325	600 ⁽²⁾
312GC ⁽¹⁾	S31600/ CoCr-A Seat and Guide	316 SST/ENC Electroless Nickel Coated	---	S31600	---	R30006/ S31600 ⁽⁶⁾	S20910	WCC, WC9	-29	204	-20	400
								CF8M	-73	204	-100	400
315G ⁽¹⁾	S31600/ CoCr-A Seat and Guide	316 SST Chrome Plate	---	S31600	R30006	---	S20910	WCC, WC9	-29	316 ⁽²⁾	-20	600 ⁽²⁾
								CF8M	-198	316 ⁽²⁾	-325	600 ⁽²⁾
315GC ⁽¹⁾	S31600/ CoCr-A Seat and Guide	316 SST Chrome Plate	---	S31600	---	R30006/ S31600 ⁽⁶⁾	S20910	WCC, WC9	-29	204	-20	400
								CF8M	-73	204	-100	400
306	S31803/ CoCr-A Seat and Guide (< 3"Port), S31803/ Ultimet Seat and Guide (≥ 3"Port)	2205 Duplex ⁽⁴⁾ Chrome Plate	---	S31803	S31803/CoCr-A (< 3"Port), S31803/ Ultimet (≥ 3"Port)	---	S31803	WCC, WC9	-29	316 ⁽²⁾	-20	600 ⁽²⁾
								CF8M	-51	316	-60	600 ⁽²⁾
307G	S31600/ CoCr-A Seat and Guide	S17400	---	Steel	R30006	---	S31600	WCC, WC9	-29	210	-20	410
307GH ⁽³⁾	S31600/ CoCr-A Seat and Guide	S17400	---	Steel	R30006	---	S31600	WCC, WC9	210	316	410	600
33.3 through 136.5, 177.8 and 203.2 mm / 1.3125 through 5.375, 7 and 8 in. Port Sizes with Whisper NXG Trim Cage												
301GNXG	S41600	17-4 H1075	---	---	S41600	---	S31600	WCC, WC9	-29	316 ⁽²⁾	-20	600 ⁽²⁾
								CF8M ⁽⁸⁾	-29	176	-20	350
312GNXG ⁽¹⁾	S316/ CoCr-A Seat and Guide	S31603/ENC	---	---	R30006	---	S20910	WCC, WC9	-29	316 ⁽²⁾	-20	600 ⁽²⁾
								CF8M	-198	316 ⁽²⁾	-325	600 ⁽²⁾
307GNXG	S31600/ CoCr-A Seat and Guide	17-4 H1075	---	---	R30006	---	S31600	WCC, WC9	-29	210	-20	410
307GHNXG ⁽³⁾	S31600/ CoCr-A Seat and Guide	17-4 H1075	---	---	R30006	---	S31600	WCC, WC9	210	316 ⁽²⁾	410	600 ⁽²⁾
306NXG	S31803/ Ultimet seat and guide	R31233 (Ultimet)	---	---	S31803/Ultimet (>1-7/8" Port), R30006 (≤1-7/8" Port)	---	S31803	WCC, WC9	-29	316 ⁽²⁾	-20	600 ⁽²⁾
								CF8M	-51	316	-60	600 ⁽²⁾

- continued -

Table 12. Whisper Trim III and Whisper NXG Trim Metal Trim Part Materials and Body/Trim Temperature Capabilities (continued)

TRIM DESIGNATION	VALVE PLUG	CAGE	CAGE RETAINER	BAFFLE (FOR LEVEL D3 CAGE ONLY)	SEAT RING FOR METAL SEAT CONSTRUCTION	DISK SEAT AND RETAINER FOR PTFE SEAT CONSTRUCTION	STEM	BODY, BONNET AND BONNET SPACER	MATERIAL TEMPERATURE CAPABILITY			
									°C		°F	
									Min	Max	Min	Max
136.5 mm / 5.375 in. Port with Whisper III Trim Cage												
301	S17400	416 SST	WCC/ENC	Steel	S41600	---	S31600	WCC, WC9	-29	316 ⁽²⁾	-20	600 ⁽²⁾
								CF8M	-29	163	-20	325
301C	S17400	416 SST	WCC/ENC	Steel	---	S31600	S31600	WCC, WC9	-29	204	-20	400
								CF8M	-29	163	-20	325
304	S31600/ CoCr-A Seat and Guide	416 SST	WCC/ENC	Steel	S31600/ CoCr-A Seat	---	S31600	WCC, WC9	-29	316 ⁽²⁾	-20	600 ⁽²⁾
								CF8M	-29	177	-20	350
312 ⁽¹⁾	S31600/ CoCr-A Seat and Guide	316 SST/ENC Electroless Nickel Coated	316/ENC Electroless Nickel Coated	S31600	R30006	---	S20910	WCC, WC9	-29	260	-20	500
								CF8M	-198	316 ⁽²⁾	-325	600 ⁽²⁾
312C ⁽¹⁾	S31600/ CoCr-A Seat and Guide	316/ENC Electroless Nickel Coated	316/ENC Electroless Nickel Coated	S31600	---	R30006/ S31600	S20910	WCC, WC9	-29	204	-20	400
								CF8M	-198	204	-325	400
306	S31803/ Ultimet Seat and Guide	2205 Duplex ⁽⁵⁾ Chrome Plate	---	S31803	S31803/ Ultimet	---	S31803	WCC, WC9	-29	316 ⁽²⁾	-20	600 ⁽²⁾
								CF8M	-51	316	-60	600 ⁽²⁾
1. NACE compatible trims meets NACE MR0175 2002, MR0175/ISO15156, MR0103. 2. Temperatures above 202°C / 450°F require PEEK anti-extrusion rings and spring loaded. This option allows ET construction to be used up to 316°C / 600°F for non-oxidizing service and 260°C / 500°F for oxidizing service. 3. For high temperature service. 4. 22 Cr-5Ni duplex stainless steel. 5. Trim 301G and 301GNXG can be used up to 216°C / 420°F with NPS 2.5 and NPS 3 CF8M body, can be used up to 316°C / 600°F with NPS 1 and NPS 1.5 CF8M body. 6. For 8 in. port size, both disk seat and retainer use R30006.												


Table 13. Materials and Temperature Limits for R31233 DST Body-to-bonnet Bolting Material Combinations⁽¹⁾

MATERIAL			BODY TYPE, SIZE AND DESIGN	MATERIAL TEMPERATURE CAPABILITY			
				°C		°F	
Body	Bolting			Min	Max	Min	Max
WCC	Studs Nuts	SA193-B7/NCF2 SA194-2H/NCF2	All	-29	316	-20	600
LCC	Studs Nuts	SA193-B7/NCF2 SA194-2H/NCF2	All	-46	316	-50	600
CF8M	Studs Nuts	SA193-B7/NCF2 SA194-2H/NCF2	NPS 3 (Globe Long Neck) 3-Stage NPS 4 (Globe Long Neck) 2-Stage	-46	316	-50	600
			NPS 6 (Globe Short Neck) 2-Stage	-46	191	-50	375
			NPS 4 (Globe Long Neck) 3-Stage NPS 6 (Globe Short Neck) 3-Stage NPS 8 (Globe Short Neck) 3-Stage	-46	177	-50	350
			NPS 3 (Globe Short Neck) 2-Stage and 3-Stage NPS 4 (Globe Short Neck) 2-Stage and 3-Stage NPS 4 (Angle) 2-Stage and 3-Stage NPS 6 (Angle) 2-Stage and 3-Stage	-46	149	-50	300
	Studs Nuts	SA-193-B8M Class 2 (strain-hardened) SA-194-8M	NPS 3 (Globe Long Neck) 3-Stage NPS 4 (Globe Long Neck) 2-Stage	-73	316	-100	600
			NPS 4 (Globe Long Neck) 3-Stage	-73	177	-100	350
			NPS 3 (Globe Short Neck) 2-Stage NPS 4 (Globe Short Neck) 2-Stage and 3-Stage NPS 4 (Angle) 2-Stage NPS 6 (Angle) 2-Stage and 3-Stage	-73	149	-100	300
			NPS 3 (Globe Short Neck) 3-Stage NPS 4 (Angle) 3-Stage NPS 6 (Globe Short Neck) 2-Stage and 3-Stage	-73	121	-100	250
			NPS 8 (Globe Short Neck) 3-Stage	-73	93	-100	200
			NPS 3 (Globe Long Neck) 3-Stage NPS 4 (Globe Long Neck) 2-Stage	-73	316	-100	600
			NPS 6 (Globe Short Neck) 2-Stage	-73	218	-100	425
			NPS 4 (Globe Long Neck) 3-Stage	-73	204	-100	400
			NPS 6 (Globe Short Neck) 3-Stage	-73	191	-100	375
			NPS 3 (Globe Short Neck) 2-Stage NPS 4 (Globe Short Neck) 2-Stage NPS 4 (Angle) 2-Stage NPS 6 (Angle) 2-Stage	-73	177	-100	350
			NPS 3 (Globe Short Neck) 3-Stage NPS 4 (Globe Short Neck) 3-Stage NPS 4 (Angle) 3-Stage NPS 6 (Angle) 3-Stage	-73	149	-100	300

1. For the body/trim material combination temperature limits, please reference Table 10.


1. For the body/trim material combination temperature limits, please reference Table 10.

Figure 8. Metal Seat and Whisper Trim III Cage in Fisher ET Valve




W2670

Figure 10. Cavitrol III One-Stage Cage




W3746A-4

Figure 9. Typical Balanced TSO Trim



W7020-1

Figure 11. Typical ENVIRO-SEAL Bellows Seal Bonnet and Bellows Seal Assembly



W5821-1

Figure 12. ENVIRO-SEAL and HIGH-SEAL Packing Systems









Figure 13. Typical Trim for All Valves Except Those with Cavitrol III, Whisper Trim III, Whisper NXG Trim or WhisperFlo Cages




A6736-2

NOTES:

1. USE TRIM 27 INSTEAD OF TRIM 29 FOR NONLUBRICATING FLUIDS SUCH AS SUPERHEATED STEAM OR DRY GASES BETWEEN 149°C / 300°F AND 232°C / 450°F.
2. DO NOT EXCEED THE MAXIMUM PRESSURE AND TEMPERATURE FOR THE PRESSURE RATING OF THE BODY MATERIAL USED, EVEN THOUGH THE TRIMS SHOWN MAY HAVE HIGHER CAPABILITIES.
3. TRIMS 4 AND 29 MAY BE USED UP TO 99 BAR / 1440 PSI WITH CLEAN DRY GAS. FOR PROCESS FLUIDS OTHER THAN CLEAN DRY GAS, USE TRIMS 4 AND 29 ONLY UP TO 21 BAR / 300 PSI.
4. TRIMS 1, 27 AND 37H TEMPERATURE LIMITS CAN BE EXTENDED TO 316°C / 600°F FOR NON-OXIDIZING SERVICE OR 260°C / 500°F OXIDIZING SERVICE IF PEEK ANTI-EXTRUSION RINGS ARE USED WITH SPRING-LOADED SEAL RINGS.
5. USE TRIM 37H INSTEAD OF TRIM 37 FOR TEMPERATURES ABOVE 210°C / 410°F. REQUIRES ANTI-EXTRUSION RINGS AND SPRING-LOADED SEAL RINGS FOR TEMPERATURES ABOVE 232°C / 450°F.

Figure 14. Typical Trim for Cavitrol III Cage Constructions



A6737

NOTES:

- 1. DO NOT EXCEED THE MAXIMUM PRESSURE AND TEMPERATURE FOR THE PRESSURE RATING OF THE BODY MATERIAL USED, EVEN THOUGH THE TRIM SHOWN MAY HAVE HIGHER CAPABILITIES.
- 2. TRIM 76 TEMPERATURE LIMITS CAN BE EXTENDED TO 316°C / 600°F FOR NON-OXIDIZING SERVICE OR 260°C / 500°F FOR OXIDIZING SERVICE IF PEEK ANTI-EXTRUSION RINGS ARE USED WITH SPRING-LOADED SEAL RINGS.

Table 14. Materials and Temperature Limits for Other Parts

PART			MATERIAL		TEMPERATURE CAPABILITIES						
					°C		°F				
					Min	Max	Min	Max			
Body-to-bonnet bolting. See Table 24 for NACE bolting materials and temperature limits	Cast iron body	Cap screws	Steel SAE Grade 5		-29	232	-20	450			
	WCC body	Studs	Steel SA-193-B7		-29	-- (5)	-20	-- (5)			
		Nuts	Steel SA-194-2H								
	LCC body	Studs	Steel SA-193-B7		-46	-- (5)	-50	-- (5)			
		Nuts	Steel SA-194-2H								
	CF3M or CF8M (316 stainless steel) body	Studs	Steel SA-193-B7 (std) (NACE [non-exposed bolting])		-48	-- (5)	-55	-- (5)			
		Nuts	Steel SA-194-2H (std) (NACE [non-exposed bolting])		-46	-- (5)	-50	-- (5)			
		Studs	S30400 stainless steel SA-320-B8		-- (5)	38	-- (5)	100			
		Nuts	S30400 stainless steel SA-194-8								
		Studs	S31600 stainless steel SA-193-B8M (strain-hardened) or S31600 stainless steel SA-193-B8M		-- (5)	-- (5)	-- (5)	-- (5)			
Nuts		S31600 stainless steel SA-194-8M									
Disk			PTFE		-73	204	-100	400			
2-piece valve plug seal (standard for NPS 1 thru 6 valves except those with Cavitrol III cage)			Backup ring		Fluorocarbon ⁽¹⁾		-18	204	0	400	
					Ethylene-propylene ⁽²⁾		-40	232	-40	450	
					Nitrile ⁽³⁾	For use with air and hydrocarbons		-40	71	-40	160
			For use with other compatible fluids			-40	82	-40	180		
			Seal ring			Carbon-filled PTFE		-73	232	-100	450
Spring-loaded valve plug seal ⁽⁷⁾			Backup ring ⁽⁴⁾		S41600 stainless steel		-29	-- (5)	-20	-- (5)	
					S31600 stainless steel		-- (5)	-- (5)	-- (5)	-- (5)	
			Retaining ring ⁽⁴⁾		S30200 stainless steel (N07750, NACE Std)		-- (5)	-- (5)	-- (5)	-- (5)	
			Seal ring			PTFE with N10276 spring		-73	232	-100	450
For applications using PEEK Anti-Extrusion Rings: Spring-loaded valve plug seal			Backup ring ⁽⁴⁾		S41600 stainless steel		-29	-- (5)	-20	-- (5)	
					S31600 stainless steel		-- (5)	-- (5)	-- (5)	-- (5)	
			Retaining ring ⁽⁴⁾		S30200 stainless steel		-- (5)	-- (5)	-- (5)	-- (5)	
			Seal ring			PTFE/graphite with R30003spring		-73	316 ⁽⁶⁾	-100	600 ⁽⁶⁾
			Anti-extrusion rings			PEEK (PolyEtherEtherKetone)		-- (5)		-- (5)	
Valve plug stem			S31600 (S20910, NACE Std.) or S31603		-- (5)	-- (5)	-- (5)	-- (5)			
Load ring (NPS 8 ET valve only)			S17400 or optional N06600 or N05500								
Restricted trim adaptors			Cast iron		-73	232	-100	450			
			WCC steel		-29	-- (5)	-20	-- (5)			
			S31600 stainless steel		-- (5)		-- (5)				
Seat ring, bonnet and cage gaskets			FGM (standard)		-- (5)		-- (5)				
			PTFE-coated N04400		-- (5)	149	-- (5)	300			
Spiral wound gasket			N06600/graphite (FGM-standard)		-- (5)		-- (5)				
			N04400/PTFE		-73	149	-100	300			
Shim			S31600 stainless steel		-- (5)	-- (5)	-- (5)	-- (5)			
			N04400								
Packing	(temperatures shown are material temperature capabilities)	See Table 16 for proper bonnet selection	PTFE V-ring		-40	232	-40	450			
			PTFE/composition		-73	232	-100	450			
			Graphite ribbon/filament		-- (5)		-- (5)				

- continued -

Table 14. Materials and Temperature Limits for Other Parts (continued)

PART		MATERIAL	TEMPERATURE CAPABILITIES			
			°C		°F	
			Min	Max	Min	Max
Packing flange, studs and nuts when used with standard bonnet		S31600 stainless steel	-- (5)		-- (5)	
Metal packing box parts		S31600 or S17400 stainless steel depending on part	-- (5)		-- (5)	
Extension bonnet bushing	Trims 1 and 4	S41600 stainless steel	-29	-- (5)	-20	-- (5)
	Other trims	S31600 stainless steel	-- (5)		-- (5)	
1. For high-temperature air, hydrocarbons and certain other chemicals and solvents. Not for use with steam or ammonia. Not recommended for water above 82°C / 180°F.						
2. Has excellent moisture resistance to hot water and steam and may be used with most fire-resistant hydraulic oils, but cannot be used with petroleum-based fluids and other hydrocarbons.						
3. Cannot be used with fire-resistant hydraulic oils.						
4. These parts not used with 137 mm / 7 in. ports or larger.						
5. These materials not limiting factors.						
6. This material may be used in temperatures up to 260°C / 500°F for oxidizing service.						
7. Standard for NPS 8 valve regardless of cage and all NPS 1 thru 6 valves with Cavitrol III cages, optional in NPS 1 thru 6 valves with other than Cavitrol III cages.						

Table 15. Fisher ET Valve Body/Trim Temperature Capabilities For All Valves Except Cavitrol III, Whisper NXG Trim, Whisper Trim III Cage and NPS 4, 6 and 8 ET with WhisperFlo Cage

BODY/BONNET ⁽³⁾ MATERIALS	TRIM DESIGNATION	VALVE SIZE, NPS	MATERIAL TEMPERATURE CAPABILITY			
			°C		°F	
			Min	Max	Min	Max
Cast Iron	1,3,27, 29 or 57	All	-29	232	-20	450
	5 ⁽⁵⁾	8	-29	232	-20	450
	6 ⁽⁵⁾		-29	232	-20	450
	37	All	-29	210	-20	410
	37H		210	232	410	450
CF3M (316L stainless steel)	316L	All	-198 ⁽⁴⁾	149 ⁽²⁾	-325 ⁽⁴⁾	300 ⁽²⁾
	316L HF		-198 ⁽⁴⁾	316 ⁽¹⁾	-325 ⁽⁴⁾	600 ⁽¹⁾
CF8M (316 stainless steel)	5 ⁽⁵⁾	8	-198 ⁽⁴⁾	316 ⁽¹⁾	-325 ⁽⁴⁾	600 ⁽¹⁾
	6 ⁽⁵⁾		-198 ⁽⁴⁾	316 ⁽¹⁾	-325 ⁽⁴⁾	600 ⁽¹⁾
	27	All	-198 ⁽⁴⁾	316 ⁽¹⁾	-325 ⁽⁴⁾	600 ⁽¹⁾
	28		-198 ⁽⁴⁾	149 ⁽²⁾	-325 ⁽⁴⁾	300 ⁽²⁾
	29		-198 ⁽⁴⁾	149 ⁽²⁾	-325 ⁽⁴⁾	300 ⁽²⁾
LCC steel	1	All	-29	316 ⁽¹⁾	-20	600 ⁽¹⁾
	4		-46	210	-50	410
	5 ⁽⁵⁾	8	-46	316 ⁽¹⁾	-50	600 ⁽¹⁾
	6 ⁽⁵⁾		-46	316 ⁽¹⁾	-50	600 ⁽¹⁾
	27	All	-46	316 ⁽¹⁾	-50	600 ⁽¹⁾
	29		-46	149 ⁽²⁾	-50	300 ⁽²⁾
	37		-46	210	-50	410
	37H		210	316 ⁽¹⁾	410	600 ⁽¹⁾
	57		-29	232	-20	450

- continued -

Table 15. Fisher ET Valve Body/Trim Temperature Capabilities For All Valves Except Cavitrol III, Whisper NXG Trim, Whisper Trim III Cage and NPS 4, 6 and 8 ET with WhisperFlo Cage (continued)

BODY/BONNET ⁽³⁾ MATERIALS	TRIM DESIGNATION	VALVE SIZE, NPS	MATERIAL TEMPERATURE CAPABILITY			
			°C		°F	
			Min	Max	Min	Max
WCC steel	1	All	-29	316 ⁽¹⁾	-20	600 ⁽¹⁾
	5 ⁽⁵⁾	8	-29	316 ⁽¹⁾	-20	600 ⁽¹⁾
	6 ⁽⁵⁾		-29	316 ⁽¹⁾	-20	600 ⁽¹⁾
	27	All	-29	316 ⁽¹⁾	-20	600 ⁽¹⁾
	29		-29	149 ⁽²⁾	-20	300 ⁽²⁾
	37		-29	210	-20	410
	37H		210	316 ⁽¹⁾	410	600 ⁽¹⁾
	57		-29	232	-20	450
WC9 Chrome moly steel	1 or 3	All	-29	316 ⁽¹⁾	-20	600 ⁽¹⁾
	5 ⁽⁵⁾	8	-29	316 ⁽¹⁾	-20	600 ⁽¹⁾
	6 ⁽⁵⁾		-29	316 ⁽¹⁾	-20	600 ⁽¹⁾
	27	All	-29	316 ⁽¹⁾	-20	600 ⁽¹⁾
	29		-29	149 ⁽²⁾	-20	300 ⁽²⁾
	37		-29	210	-20	410
	37H		210	316 ⁽¹⁾	410	600 ⁽¹⁾
	57		-29	232	-20	450

1. Temperatures above 232°C / 450°F require PEEK anti-extrusion rings and spring-loaded seal ring. This option allows ET construction to be used up to 316°C / 600°F for non-oxidizing service and 260°C / 500°F for oxidizing service.
2. Lubricating service allows usage to 232°C / 450°F
3. Same material also used for bottom flange, if required. Restricted trim and full-sized limits are the same.
4. May be used down to -254°C / -425°F if manufacturing process includes Charpy impact test.
5. Only available for Whisper Trim I cages.

Table 16. Bonnet Selection Guidelines

BONNET STYLE	PACKING MATERIAL	IN-BODY PROCESS TEMPERATURE LIMITS ⁽¹⁾	
		°C	°F
Plain: ■ Standard for all valve sizes through NPS 6 with 2-13/16 yoke boss diameter ■ Standard for NPS 6 and 8 valves in cast iron and WCC steel bonnet material with 3-9/16 yoke boss diameter	PTFE V-ring	-18 to 232	0 to 450
	PTFE/Composition	-18 to 232	0 to 450
	Graphite ribbon/filament	-18 to 316 ⁽²⁾	0 to 600 ⁽²⁾
Style 1 Cast Extension: ■ Standard for NPS 8 valves in S31600 bonnet material with 3-9/16 yoke boss diameter	PTFE V-ring	-46 to 316 ⁽²⁾	-50 to 600 ⁽²⁾
	PTFE/Composition		
	Graphite ribbon/filament		
Style 2 Cast Extension: ■ Optional for NPS 2 through 4 valve sizes with 2-13/16 in. yoke boss diameter ■ Optional for NPS 6 and 8 valves with 3-9/16 yoke boss diameter	PTFE V-ring	-101 to 316 ⁽²⁾	-150 to 600 ⁽²⁾
	PTFE/Composition		
	Graphite ribbon/filament		
ENVIRO-SEAL bellows seal bonnet	PTFE	For exceptional stem sealing capabilities. See Bulletin 59.1:070, ENVIRO-SEAL Bellows Seal Bonnets (D101641X012), for pressure/temperature ratings.	
	Graphite ULF	For exceptional stem sealing capabilities. See Bulletin 59.1:070, ENVIRO-SEAL Bellows Seal Bonnets (D101641X012), for pressure/temperature ratings.	

1. These in-body process temperatures assume an outside, ambient temperature of 21°C / 70°F and no insulation on the bonnet. When using any packing at low process temperatures, a cast extension bonnet may have to be used to prevent packing damage which could result from the formation of valve stem frost. Material selection for trim and other components will also be limiting factors.

2. Temperatures above 232°C / 450°F require PEEK anti-extrusion rings and spring-loaded seal ring.

Table 17. Maximum Flow Coefficients for Full-Sized Trim with Equal Percentage Cage and Normal Flow Direction

Valve		Valve Size, NPS	C _V at Max Valve Plug Travel
ED		1	17.2
		1-1/2	35.8
		2	59.7
		2-1/2	99.4
		3	136
		4	224
		6	394
		8 ⁽¹⁾	567
		8 ⁽²⁾	819
		EAT	with liner
2	48.1		
3	149		
4	152		
6	336		
without liner	1		19.0
	2		47.2
	3		148
	4		156
	6		328
ETR		1	17.2
		1-1/2	35.8
		2	59.7
		2-1/2	99.4
		3	136
		4	224

1. With 51 mm / 2 in. travel.

2. With 76 mm / 3 in. travel.

1. With 51 mm / 2 in. travel.

2. With 76 mm / 3 in. travel.

Table 18. Port Diameters and Valve Plug Travel

VALVE SIZE, NPS				PORT DIAMETER ⁽¹⁾		MAXIMUM VALVE PLUG TRAVEL ⁽¹⁾	
ET or ETR		EAT					
Full-Sized Trim	Restricted-Capacity Trim	Full-Sized Trim	Restricted-Capacity Trim	mm	in.	mm	in.
1	1-1/2	1	2	33.3	1.3125	19.1	0.75
---	2	---	---	33.3	1.3125	19.1	0.75
1-1/2	---	2	---	46.7	1.875	19.1	0.75
---	2-1/2	---	---	46.7	1.875	19.1	0.75
2	3	---	4	58.7	2.3125	29	1.125
2-1/2	4	3	6	73.0	2.875	38	1.5
3	---	4	---	87.3	3.4375	38	1.5
4	---	6	---	111.1	4.375	51	2
6 ⁽²⁾	---	---	---	177.8 ⁽³⁾	7 ⁽³⁾	51 ⁽³⁾	2 ⁽³⁾
				---	---	---	---
8 ⁽²⁾	---	---	---	203.2	8	51	2
						76	3

1. For Cavitrol III trim, see Table 20.

2. Not available in ETR valves.

3. Standard-travel cages.

1. For Cavitrol III trim, see Table 20.

2. Not available in ETR valves.

3. Standard-travel cages.

Table 19. Stem and Yoke Boss Diameters

VALVE SIZE, NPS				STEM AND YOKE BOSS DIAMETERS							
ET or ETR		EAT		Standard				Optional			
Full-Sized Trim	Restricted-Capacity Trim	Full-Sized Trim	Restricted-Capacity Trim	Stem		Yoke Boss		Stem		Yoke Boss	
				mm	in.	mm	in.	mm	in.	mm	in.
1	1-1/2	1	2	9.5	3/8	54	2-1/8	12.7	1/2	71	2-13/16
---	2	---	---	12.7	1/2	71	2-13/16	---	---	---	---
1-1/2	---	2	---	9.5	3/8	54	2-1/8	12.7	1/2	71	2-13/16
---	2-1/2	---	---	1.7	1/2	71	2-13/16	---	---	---	---
2	3	---	4	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16
2-1/2	4	3	6	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16
3	---	4	---	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16
4	---	6	---	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16
								25.4	1	127	5
6 ⁽¹⁾	---	---	---	19.1	3/4	90	3-9/16	25.4 or 31.8	1 or 1-1/4	127	5
8 ⁽¹⁾	---	---	---								

1. Not available in ETR valves.

Table 20. Port Diameters and Valve Plug Travel for Cavitrol III Cage

ET VALVE SIZE, NPS	ONE-STAGE CAGE		TWO-STAGE CAGE	
	Port Diameters	Valve Plug Travel ⁽¹⁾	Port Diameters	Valve Plug Travel
mm				
1	33.3	25	25.4	25
1-1/2	47.6	22	33.3	38
2	58.7	29	47.6	51
2-1/2	73.0	38	58.7	64
3	87.3	41	7.30	76
4	111.1	54	73.0	102
6	177.8	57	136.5	102
8	203.2	86	177.8	152
in.				
1	1.3125	1	1	1
1-1/2	1.875	0.875	1.3125	1.5
2	2.3125	1.125	1.875	2
2-1/2	2.875	1.5	2.3125	2.5
3	3.4375	1.625	2.875	3
4	4.375	2.125	2.875	4
6	7	2.25	5.375	4
8	8	3.375	7	6

1. The travel listed is the maximum travel that can be obtained for the given size. In situations where increased valve capacity is not needed, standard ET valve travels should be utilized in selecting the actuator.

Table 21. Port Diameter, Valve Plug Travel and Stem and Yoke Boss Diameters for Whisper NXG Trim⁽²⁾ and Whisper III Trims⁽¹⁾

VALVE SIZE, NPS		PORT DIAMETER		MAX VALVE PLUG TRAVEL		STEM AND YOKE BOSS DIAMETERS								PERFORMANCE LEVEL
						Standard				Optional				
ET	EAT					mm	in.	mm	in.	Stem		Yoke Boss		
		mm	in.	mm	in.					mm	in.	mm	in.	
1	1	33.3	1-5/16	19	3/4	9.5	3/8	54	2-1/8	12.7	1/2	71	2-13/16	A1
1-1/2	2	47.6	1-7/8	19	3/4	9.5	3/8	54	2-1/8	12.7	1/2	71	2-13/16	A1
		33.3	1-5/16	19	3/4									A3, B1, B3, C1
2	---	58.7	2-5/16	35	1-3/8	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16	A1
2	---	33.3	1-5/16	29	1-1/8	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16	A3, B1, B3, C1, C3, D1, D3
2-1/2	3	73	2-7/8	38	1-1/2	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16	A1
		47.6	1-7/8											A3, B1, B3, C1, C3, D1, D3
3	4	87.3	3-7/16	38	1-1/2	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16	A1
		58.7	2-5/16											A3, B1, B3, C1, C3, D1, D3
4	6	111.1	4-3/8	51	2	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16	A1
		87.3	3-7/16							25.4	1	127	5	A3, B1, B3, C1, C3, D1, D3
6	---	177.8	7	51	2	19.1	3/4	90	3.5625	25.4 or 31.8	1 or 1-1/4	127	5	A1
		136.5	5-3/8	76	3									A3, B1, B3, C1, C3, D1, D3
8	---	203.2	8	76	3	19.1	3/4	90	3.5625	25.4 or 31.8	1 or 1-1/4	127	5	A1
				102	4									A3, B1, B3, C1, C1, C3

1. Refer Fisher Bulletin 80.1:010 Whisper Trim III (D100191X012) for more information.


2. Currently, Whisper NXG is only available to level A1, B1 and C1.

Table 22. Port Diameters, Valve Plug Travel, Yoke Boss Diameters for TSO (Tight Shutoff) Trim

VALVE	TRIM	MAX TRAVEL		YOKE BOSS SIZE		PORT DIAMETER				C _V REDUCTION AT 100% TRAVEL ⁽¹⁾	UNBALANCE AREA
						Nominal		Actual TSO			in ²
		mm	in.	mm	in.	mm	in.	mm	in.		
ET NPS 3	CAV III 2-Stage	76.2	3	90 127	3-9/16 5	73.0	2.875	68.3	2.6875	0%	0.098
ET NPS 4	CAV III 2-Stage	102	4	90 127	3-9/16 5	73.0	2.875	68.3	2.6875	5%	0.098
EAT NPS 4	Std	38.1	1.5	71.4 90	2-13/16 3-9/16	87.3	3.4375	82.6	3.25	6% 4%	0.118
EAT NPS 6	Std	50.8	2	90	3-9/16	111	4.375	106	4.1875	4% (linear) 3% (equal percent)	0.154

1. This column lists the percent reduction of published maximum C_v of the trim listed in the TRIM column.

Figure 15. Typical Trim for NACE MR0175 / ISO 15156 and MR0103 (Sour Service)



A6739-1

NOTES:

1. USE TRIM 87 INSTEAD OF TRIM 85 FOR NONLUBRICATING FLUIDS SUCH AS SUPER-HEATED STEAM OR DRY GASES BETWEEN 149°C / 300°F AND 232°C / 450°F.
2. DO NOT EXCEED THE MAXIMUM PRESSURE AND TEMPERATURE FOR THE PRESSURE RATING OF THE BODY MATERIAL USED, EVEN THOUGH THE TRIMS SHOWN MAY HAVE HIGHER CAPABILITIES.
3. TRIM 85 MAY BE USED UP TO 99 BAR / 1440 PSI WITH CLEAN DRY GAS. FOR PROCESS FLUIDS OTHER THAN CLEAN DRY GAS, USE TRIM 85 ONLY UP TO 21 BAR / 300 PSI.
4. TRIM 87 TEMPERATURE LIMITS CAN BE EXTENDED TO 316°C / 600°F FOR NON-OXIDIZING SERVICE OR 260°C / 500°F FOR OXIDIZING SERVICE IF PEEK ANTI-EXTRUSION RINGS ARE USED WITH SPRING-LOADED SEAL RINGS.

Table 23. Metal Trim Part Materials for Compatibility with NACE MR0175 / ISO 15156 and MR0103 (Sour Service) Specifications. Environmental Restrictions Apply, Refer to Standard

Trim Designation ⁽⁴⁾	Valve Plug	Cage	Seat Ring for Standard Metal Seat Construction	Optional Liner for Metal Seat (EAT only)	Disk Seat and Retainer for Optional PTFE-Seat Construction	Valve Stem, Packing Follower, Lantern Ring, Packing Box Ring and Pin	Load Ring ⁽¹⁾
85 ⁽⁵⁾	S31600	316 SST with electroless nickel coating (ENC)	S31600	S31600	---	S20910 (Valve Stem) S31600 (All Other Parts)	N05500
85C ^(2, 5)	S31600	316 SST with electroless nickel coating (ENC)	---	---	S31600		
86 ⁽⁵⁾	S31600 with seat hard faced with CoCr-A hardfacing alloy	316 SST with electroless nickel coating (ENC)	R30006 (alloy 6)	---	---		
87 (Also used for 8-in. Whisper Trim I)	S31600 with seat and guide hard faced with CoCr-A hardfacing alloy	316 SST with electroless nickel coating (ENC) ⁽³⁾	R30006 (alloy 6)	---	---		
87C ⁽²⁾ (Also used for 8-in. Whisper Trim I)	S31600 with seat and guide hard faced with CoCr-A hardfacing alloy	316 SST with electroless nickel coating (ENC) ⁽³⁾	---	---	S31600		
1. NPS 8 valve body only. 2. 85C and 87C are trims for PTFE-seat construction. 3. 8-in. Whisper Trim I cage is 17-4 SST, double H1150 (NACE) / ENC. 4. N07750 retaining ring is standard for spring-loaded seal ring construction. 5. Not for use with Whisper Trim I with 136 mm / 5.375 in. and larger ports.							


Table 24. Bolting Materials and Temperature Limits for Bolting Compliance with NACE MR0175-2002, NACE MR0175/ISO 15156 and NACE MR0103. Environmental Restrictions May Apply

VALVE BODY MATERIAL		BOLTING MATERIAL	TEMPERATURE CAPABILITIES			
			°C		°F	
			Min	Max	Min	Max
Non-exposed bolting (Standard)						
WCC and CF8M (316 SST)	Studs	Steel SA-193-B7	-48 ⁽²⁾	427	-55 ⁽²⁾	800
	Nuts	Steel SA-194-2H				
Exposed bolting (Optional) Requires Derating of Valve ⁽¹⁾ When These Body-to-Bonnet Bolting Materials are Used						
WCC and CF8M	Studs	Steel SA-193-B7M	-48 ⁽²⁾	427	-55 ⁽²⁾	800
	Nuts	Steel SA-194-2HM				
1. Derating is not required for CL150 and 300 valves. Derating may be required for valves rated at CL600. Contact your Emerson sales office for assistance in determining the derating of valves when these body-to-bonnet bolting materials are used. 2. -29°C / -20°F with WCC body material.						


Table 25. Fisher ET and ETR Dimensions

VALVE SIZE, NPS	A									G (MAX)	
	Pressure Rating, End Connection Style ⁽¹⁾										
	Scrd or SW	CL125 FF or CL150 RF	CL150 RTJ	CL250 RF or CL300 RF	CL300 RTJ	BW or CL600 RF	CL600 RTJ	PN16 to 40 ⁽²⁾	PN63 to 100 ⁽²⁾	ET	ETR
mm											
1	210	184	197	197	210	210	210	160	230	60	119
1-1/2	251	222	235	235	248	251	251	200	260	71	116
2	286	254	267	267	282	286	289	230	300	78	133
2-1/2	---	276	292	292	308	311	314	290	340	90	159
3	---	298	311	317	333	337	340	310	380	97	168
4	---	353	365	368	384	394	397	350	430	129	192
6	---	451	464	473	489	508	511	480	550	140	---
8	---	543	556	568	584	610	613	600	650	191	---
in.											
1	8.25	7.25	7.75	7.75	8.25	8.25	8.25	See mm below	See mm below	2.38	4.69
1-1/2	9.88	8.75	9.25	9.25	9.75	9.88	9.88			2.81	4.56
2	11.25	10.00	10.50	10.50	11.12	11.25	11.38			3.06	5.25
2-1/2	---	10.88	11.38	11.50	12.12	12.25	12.38	See mm below	See mm below	3.56	6.25
3	---	11.75	12.25	12.50	13.12	13.25	13.38			3.81	6.62
4	---	13.88	14.38	14.50	15.12	15.50	15.62			5.06	7.56
6	---	17.75	18.25	18.62	19.25	20.00	20.12			5.51	---
8	---	21.38	21.88	22.38	23.00	24.00	24.12			7.50	---
1. End connection style abbreviations: BW - Butt welding, FF - Flat Faced, Scrd - Screwed, SW - Socket weld, RF - Raised Face, RTJ - Ring Type Joint. 2. Valves which meet EN 1092 flange standards and have EN face-to-face dimensions are available only from Europe (EN 558-1). Valves which meet EN 1092 flange standards but not EN face-to-face standards are available in the US. Consult your Emerson sales office .											

Figure 16. Fisher ET and ETR Dimensions (Also See Tables 25, 26 and 27)



AR4967-A
A0925-3



10A7397-B
A0926-2

NOTES:

1. $B = \frac{A}{2}$

2. FOR DIMENSIONS OF VALVES WITH OTHER END CONNECTIONS, CONSULT YOUR [EMERSON SALES OFFICE](#).

Table 26. Fisher ET and ETR Dimensions

VALVE SIZE, NPS	D FOR PLAIN BONNET										
	ET Except with Cavitrol III Two-Stage Cage				ET with Cavitrol III Two-Stage Cage				ETR		
	Stem Diameter, mm										
	9.5	12.7	19.1	25.4 or 31.8	9.5	12.7	19.1	25.4 or 31.8	9.5	12.7	19.1
1	127	149	---	---	---	184	---	---	113	124	---
1-1/2	124	146	---	---	155	177	---	---	122	133	---
2	---	165	162	---	---	201	198	---	---	148	140
2-1/2	---	187	184	---	---	229	226	---	---	157	152
3	---	191	187	---	---	260	256	---	---	167	159
4	---	221	217	264	---	311	308	354	---	198	191
6 ⁽¹⁾	---	---	251	270	---	---	336	380	---	---	---
6 ⁽²⁾	---	---	312	330	---	---	---	---	---	---	---
8	---	---	375 ⁽³⁾	426	---	---	511	560	---	---	---
VALVE SIZE, NPS	Stem Diameter, in.										
	3/8	1/2	3/4	1 or 1-1/4	3/8	1/2	3/4	1 or 1-1/4	3/8	1/2	3/4
1	5.00	5.88	---	---	---	7.25	---	---	4.44	4.88	---
1-1/2	4.88	5.75	---	---	6.09	6.97	---	---	4.81	5.25	---
2	---	6.50	6.38	---	---	7.91	7.78	---	---	5.81	5.50
2-1/2	---	7.38	7.25	---	---	9.03	8.91	---	---	6.31	6.00
3	---	7.50	7.38	---	---	10.22	10.09	---	---	6.56	6.25
4	---	8.69	8.56	10.38	---	12.25	12.12	13.94	---	7.81	7.50
6 ⁽¹⁾	---	---	9.88	10.62	---	---	13.22	14.97	---	---	---
6 ⁽²⁾	---	---	12.26	13.00	---	---	---	---	---	---	---
8	---	---	14.75 ⁽³⁾	16.75	---	---	20.12	22.06	---	---	---

1. For all NPS 6 valves except with Whisper III, Whisper NXG trims and WhisperFlo cages.

2. For NPS 6 valves with Whisper III, Whisper NXG trims and WhisperFlo cages.

3. Available only in cast iron or WCC steel for the stem diameter with plain bonnet.

Table 27. Fisher ET and ETR Dimensions

VALVE SIZE, NPS	D FOR EXTENSION AND ENVIRO-SEAL BELLOWS SEAL BONNETS (ET ONLY, EXCEPT WITH CAVITROL III CAGE)									
	Style 1 Ext. Bonnet				Style 2 Ext. Bonnet			ENVIRO-SEAL Bellows Seal Bonnet		
	Stem Diameter									
	mm									
	9.5	12.7	19.1	25.4 or 31.8	9.5	12.7	19.1	9.5	12.7	19.1
1	213	251	---	---	303	319	---	320	---	---
1-1/2	210	248	---	---	300	316	---	317	---	---
2	---	267	272	---	---	465	---	---	384	---
2-1/2	---	289	294	---	---	492	---	---	---	---
3	---	292	297	---	---	495	487	---	517	517
4	---	322	327	370	---	526	518	---	541	---
6 ⁽¹⁾	---	---	357	402	---	---	543	---	---	573
6 ⁽²⁾	---	---	418	462	---	---	604	---	---	---
8	---	---	421	450	---	---	621	---	---	703
VALVE SIZE, NPS	in.									
	3/8	1/2	3/4	1 or 1-1/4	3/8	1/2	3/4	3/8	1/2	3/4
1	8.38	9.88	---	---	11.94	12.56	---	12.62	---	---
1-1/2	8.25	9.75	---	---	11.81	12.44	---	12.50	---	---
2	---	10.50	10.69	---	---	18.31	---	---	15.12	---
2-1/2	---	11.38	11.56	---	---	19.38	---	---	---	---
3	---	11.50	11.69	---	---	19.50	19.19	---	20.38	20.38
4	---	12.69	12.88	14.56	---	20.69	20.38	---	21.31	---
6 ⁽¹⁾	---	---	14.06	15.81	---	---	21.38	---	---	22.56
6 ⁽²⁾	---	---	16.44	18.19	---	---	23.76	---	---	---
8	---	---	16.56	17.75	---	---	24.44	---	---	27.69

1. Standard-travel cages.


2. For NPS 6 valves with Whisper III, Whisper NXG trims and WhisperFlo cages.

Table 28. Fisher EAT Dimensions⁽¹⁾

VALVE SIZE, NPS	AA					
	CL150		CL300		CL600	
	RF	RTJ	RF	RTJ	BW, SW or RF	RTJ
	mm					
1	92	98	98	105	105	105
2	127	133	133	141	143	144
3	149	156	159	167	168	170
4	176	183	184	197	197	198
6	225	232	237	244	254	256
	in.					
1	3.62	3.88	3.88	4.12	4.12	4.12
2	5.00	5.25	5.25	5.56	5.62	5.69
3	5.88	6.12	6.25	6.56	6.62	6.69
4	6.94	7.19	7.25	7.56	7.75	7.81
6	8.88	9.12	9.31	9.62	10.00	10.06

1. End connection style abbreviations: BW - Butt welding, FF - Flat Faced, Scrd - Screwed, SW - Socket weld, RF - Raised Face, RTJ - Ring Type Joint.

Figure 17. Fisher EAT Dimensions (Also See Tables 28, 29 and 30)



A0927-2

NOTE: FOR DIMENSIONS OF VALVES WITH PN (OR OTHER) END CONNECTIONS, CONSULT YOUR [EMERSON SALES OFFICE](#).

Table 29. Fisher EAT Dimensions

VALVE SIZE, NPS	DD						
	Plain Bonnet				Style 1 Extension Bonnet		
	Stem Diameter, mm						
	9.5	12.7	19.1	25.4 or 31.8	9.5	12.7	19.1
1	111	133	---	---	197	253	---
2	98	121	---	---	184	223	---
3	---	149	146	---	---	251	256
4	---	140	137	---	---	241	246
6	---	144	141	187	---	246	251
VALVE SIZE, NPS	Stem Diameter, in.						
	3/8	1/2	3/4	1 or 1-1/4	3/8	1/2	3/4
1	4.38	5.25	---	---	7.75	9.25	---
2	3.88	4.75	---	---	7.25	8.75	---
3	---	5.88	5.75	---	---	9.88	10.06
4	---	5.50	5.38	---	---	9.50	9.69
6	---	5.69	5.56	7.38	---	9.69	9.88

Table 30. Fisher EAT Dimensions

VALVE SIZE, NPS	DD					
	Style 2 Extension Bonnet			ENVIRO-SEAL Bellows Seal Bonnet		
	Stem Diameter, mm					
	9.5	12.7	19.1	9.5	12.7	19.1
1	291	305	---	305	---	---
2	278	291	---	292	---	---
3	---	454	---	---	---	---
4	---	445	437	---	467	---
6	---	449	441	---	465	---
VALVE SIZE, NPS	Stem Diameter, in.					
	3/8	1/2	3/4	3/8	1/2	3/4
1	11.44	12.00	---	12.00	---	---
2	10.94	11.44	---	11.50	---	---
3	---	17.88	---	---	---	---
4	---	17.50	17.19	---	18.38	---
6	---	17.69	17.38	---	18.31	---

Ordering Information

Inlet pressure and temperature must always be limited by the applicable ASME pressure/temperature rating. Pressure drop information for various trim material combinations is provided in Figures 13, 14 and 15. The maximum allowable pressure drop for the application must not exceed the lowest value indicated for the combination of materials selected.

When ordering, specify:

Application Information

1. Type of application:
 - a. Throttling or on-off
 - b. Reducing or relief
2. Controlled fluid (include chemical analysis of fluid if possible)
3. Specific gravity of controlled fluid
4. Fluid temperature
5. Inlet pressures:
 - a. Minimum
 - b. Normal
 - c. Maximum
6. Pressure drops:
 - a. Minimum flowing drop
 - b. Normal flowing drop
 - c. Maximum flowing drop
 - d. Maximum at shutoff

7. Flow rates:
 - a. Minimum controlled flow
 - b. Normal flow
 - c. Maximum flow
8. Maximum permissible noise level, if critical
9. Shutoff classification required
10. Valve stem diameter and bonnet type (plain, extension or ENVIRO-SEAL bellows seal bonnet)
11. Line size and schedule

Valve Information

To determine what valve ordering information is needed, refer to the specifications. Review the description for each specification and in the referenced tables; write down your choice whenever there is a selection to be made. Always specify the valve design letter designation.

Actuator and Accessory Information

Refer to the specific actuator and accessory bulletins for required ordering information.

 [LinkedIn.com/groups/3941826](https://www.linkedin.com/groups/3941826)
 [Fisher.com](https://www.fisher.com)

 [Facebook.com/FisherValves](https://www.facebook.com/FisherValves)
 [X.com/FisherValves](https://www.x.com/FisherValves)

D100022X012 © 2012, 2025 Fisher Controls International LLC. All rights reserved.

Neither Emerson, nor any of its affiliated entities assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

Fisher, Cavitrol, easy-e, ENVIRO-SEAL, FIEDLVUE, Whisper Trim, and WhisperFlo are marks owned by one of the companies in the Emerson business unit of Emerson Electric Co. Emerson and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson
Marshalltown, Iowa 50158 USA
Sorocaba, 18087 Brazil
Cernay, 68700 France
Dubai, United Arab Emirates
Singapore 128461 Singapore

www.fisher.com

FISHER™

