

Fisher™ ES and EAS Sliding-Stem Control Valves



Fisher™ ES and EAS Sliding-Stem Control Valves

Fisher ES and EAS general-purpose control valves (Figures 1 and 2) are used for throttling or on-off control of a wide variety of liquids and gases. Both valve designs have single ports, unbalanced valve plugs and cage guiding.

In both designs, metal-to-metal seating is standard for all general applications over a wide range of pressure drops and temperatures. Metal-to-PTFE seating is optional for more stringent shutoff requirements.

The Fisher ES product line is available for a wide range of applications, including sulfide and chloride stress-cracking environments common to the oil and gas production industries. To discuss available constructions, contact your [Emerson sales office](#) and include the applicable codes and standards required for these environments.

The easy-e™ Valve Family

ES and EAS valves are part of the versatile easy-e family of Fisher industrial control valves. easy-e valves share the following characteristics:

- Multiple trim material choices
 - Trim temperature capability with standard metal seats to 427°C / 800°F
 - Flexible graphite gaskets
 - Interchangeable, restricted-capacity trims and full-flow trims to match variable process flow demands
 - Trim part interchangeability that permits reconfiguring the valve to a different design variation
- Different cage/plug styles provide particular flow characteristics for highly-specialized applications. The standard cage comes in three different flow characteristics:
 - quick-opening
 - linear
 - equal percentage
 - Whisper Trim™ I cages (Figure 1) that attenuate aerodynamic noise in gaseous service are available for all sizes except the NPS 8 ES valve.
 - Optional constructions provide material compatibility with NACE MR0175-2002.
 - 316 stainless steel packing box parts are standard (including packing flange, studs and nuts).



X1968

**FISHER ES VALVE WITH 667 ACTUATOR
AND FISHER FIELDVUE™ DVC7K**

Features

- Compliance with the Clean Air Act — Optional ENVIRO-SEAL™ packing systems (Figure 3) provide an improved stem seal to help prevent the loss of process fluid. The ENVIRO-SEAL packing systems feature PTFE, Graphite ULF or Duplex packing with live-loading for reduced packing maintenance.
- Valve Plug Stability — Rugged cage guiding provides increased valve plug stability, which reduces vibration and mechanical noise.
- Economy — Streamlined flow passages provide higher efficiency and greater capacities per initial investment.
- Cost-Effective Operation — Increased wear resistance of the standard hardened stainless steel trim means long-lasting service. Also, trim inventory costs are cut because dimensional standardization permits use of most standard easy-e trim parts.
- Easy Maintenance — The valve can stay in the pipeline during removal of trim parts for inspection or maintenance.
- Long-Lasting Shutoff Capability with PTFE Seating — Controlled compression of optional seat construction protects PTFE disk between metal disk seat and disk retainer (Figure 1). The flowstream contacts only the edge of the disk during normal operation.
- Compliance with European Standards — Valves are available with dimensions specified by EN/DIN standards. See Figure 7 and the note in Figure 8.
- Sour Service Capability — Unless otherwise noted, references are to NACE MR0175-2002. Optional materials are available to meet NACE MR0103 and NACE MR0175/ISO15156. Material requirements under these standards vary by edition and year of issue; the specific standard must be specified.

Specifications

Available Configurations	Flow Characteristics
ES: Single-port, globe-style control valve with cage guiding, unbalanced valve plug and push-down-to-close valve plug action (Figure 1) EAS: Angle version of ES control valve, used to facilitate piping or in applications where a self-draining valve is desired (Figure 2)	Standard Cages: ■ Quick-opening, ■ linear or ■ equal percentage Whisper Trim: Linear
Valve Sizes	Flow Directions
See Table 3	ES <i>Standard Cage</i> : Normally up <i>Whisper Trim Cages</i> : Always up
End Connection Styles ⁽¹⁾⁽²⁾	EAS <i>Standard Cage</i> : Without liner, flow up or down; with liner, normally down <i>Whisper Trim Cages</i> : Always up
Cast Iron Valves <i>Flanged</i> : ES, NPS 1 through 8, including NPS 1-1/2 and 2-1/2 (except NPS 1 to 1/4), ■ CL125 flat-face or ■ CL250 raised-face flanges per ASME B16.1 Steel and Stainless Steel Valves Flanged: ■ CL150, 300 or 600 raised-face (RF) or ring-type joint (RTJ) flanges per ASME B16.5, ■ Raised-face (RF) flanges per EN1092-1/B <i>Screwed or Socket Welding</i> : NPS 1/2 through 2, consistent with ASME B16.11 <i>Buttwelding</i> : NPS 1 through 8 (except NPS 1-1/4). Schedules 40 or 80 consistent with ASME B16.25	
Maximum Inlet Pressures and Temperatures ⁽¹⁾⁽²⁾	Flow Coefficients and Noise Level Prediction
As listed below, unless limited by maximum pressure drop or material temperature capabilities Cast Iron Valves <i>Flanged</i> : Consistent with CL125B or 250B per ASME B16.1 Steel and Stainless Steel Valves <i>Flanged</i> : Consistent with CL150, 300 and 600 ⁽³⁾ per ASME B16.34 <i>Screwed or Welding</i> : Consistent with flanged CL600 ⁽³⁾ per ASME B16.34	See Table 8 and Catalog 12
	Port Diameters and Maximum Valve Plug Travels
	See Table 12 for trims except Whisper III and Whisper NXG trims See Table 13 for Whisper III and Whisper NXG trims

- continued -

Specifications

Maximum Pressure Drop ⁽²⁾	Approximate Weights
Same as maximum inlet pressure for specific construction defined on the previous page, except where further limited as shown in Figures 5 and 6 Valves for NACE MR0175-2002: See Figure 5	NPS 1/2 and 3/4: 9 kg / 20 lb NPS 1 and 1-1/4: 14 kg / 30 lb NPS 1-1/2: 20 kg / 45 lb NPS 2: 39 kg / 85 lb NPS 2-1/2: 45 kg / 100 lb NPS 3: 57 kg / 125 lb NPS 4: 77 kg / 170 lb NPS 6: 159 kg / 350 lb NPS 8: 408 kg / 900 lb
Shutoff Classifications per ANSI/FCI 70-2 and IEC 60534-4	Yoke Boss and Stem Diameters
Metal Seating: Class IV is standard. Class V is optional PTFE Composition Seating: Class VI	See Tables 12 and 13
Construction Materials	Typical Bonnet Styles
Body, Bonnet and Bonnet Spacer or Bottom Flange, if used: ■ WCC carbon steel, ■ CF8M stainless steel, ■ LCC carbon steel, ■ WC9 chrome moly steel, ■ Cast iron body with steel bonnet construction, ■ CF3M stainless steel or Other material constructions upon request Valve Plug, Cage and Metal Seating Parts: See Table 4 All Other Parts: See Table 9	■ Plain or ■ extension. See Figures 7 and 8 for standard dimensions. See Table 7 for selection guidelines ■ ENVIRO-SEAL bellows seal bonnet. See Figure 4 for view of ENVIRO-SEAL bellows seal bonnet. Also, see Bulletin 59.1:070, ENVIRO-SEAL Bellows Seal Bonnets, (D101641X012) for further information.
Material Temperature Capabilities ⁽²⁾	Optional Safety Instrumented System Classification
Body/Trim Combinations: See Tables 4 and 6 Those For NACE Specification: See Tables 10 and 11 Whisper III and Whisper NXG Trims: See Table 5 All Other Parts: See Table 9	SIL3 capable — certified by exida Consulting LLC
Packing Arrangements	Additional Options
Standard Material: Single PTFE V-ring ENVIRO-SEAL Packing: See Figure 3 <i>ENVIRO-SEAL Packing Systems in vacuum service:</i> Standard ENVIRO-SEAL packing systems can be used in vacuum service with packing rings in standard orientation. Do not reverse the ENVIRO-SEAL PTFE packing rings. Also see Bulletin 59.1:061, ENVIRO-SEAL Packing Systems for Sliding-Stem Valves, (D101633X012) for more information.	■ Lubricator, ■ lubricator/isolating valve, ■ drilled and tapped connection in extension bonnet for leakoff service, ■ body drain plug, ■ style 3 fabricated extension bonnet made on order to a specific length for cryogenic service and ■ Whisper Trim III and Whisper NXG Trim cages
1. EN (or other) ratings and end connections can usually be supplied; consult your Emerson sales office. 2. The pressure/temperature limits in this bulletin and any applicable standard limitations should not be exceeded. 3. Certain bonnet bolting material selections may require a CL600 easy-e valve assembly to be derated. Contact your Emerson sales office for more information.	

ENVIRO-SEAL Packing System Specifications

Applicable Stem Diameters	Construction Materials
■ 9.5 mm / 3/8 in. ■ 12.7 mm / 1/2 in. ■ 19.1 mm / 3/4 in. ■ 25.4 mm / 1 in. and ■ 31.8 mm / 1-1/4 in. diameter valve stems	PTFE Packing Systems: <i>Packing Ring and Lower Wiper:</i> PTFE V-ring ⁽³⁾ <i>Male and Female Adaptor Rings:</i> Carbon-filled PTFE V-ring Graphite ULF Packing Systems: Graphite rings Duplex Packing Systems: <i>Male and Female Adaptor Rings:</i> Carbon-filled PTFE V-ring <i>Guide Bushings:</i> Carbon graphite <i>Packing Rings:</i> Graphite composite <i>Packing Washer:</i> PTFE <i>Anti-Extrusion Washer:</i> Filled PTFE (not required for graphite or duplex packing) <i>Lantern Ring:</i> S31600 (316 stainless steel) (not required for graphite packing) <i>Packing Box Flange:</i> S31600 <i>Spring:</i> ■ 17-7PH stainless steel or ■ N06600 <i>Packing Follower:</i> S31600 lined with carbon-filled PTFE <i>Packing Box Studs:</i> Strain-hardened 316 stainless steel <i>Packing Box Nuts:</i> 316 stainless steel
Maximum Pressure/Temperature Limits ⁽¹⁾	
To Meet the EPA Fugitive Emission Standard of 100 PPM ⁽²⁾ For ENVIRO-SEAL PTFE and ENVIRO-SEAL <i>Duplex packing systems</i> ; full CL300 up to 232°C / 450°F For ENVIRO-SEAL <i>Graphite packing</i> ; 104 bar / 1500 psig at 316°C / 600°F	
1. Refer to the valve specifications in this bulletin for pressure/temperature limits of valve parts. Do not exceed the pressure/temperature rating of the valve. Do not exceed any applicable code or standard limitation. 2. The Environmental Protection Agency (EPA) has set a limit of 100 parts per million (ppm) for fugitive emissions from a valve in selected VOC (Volatile Organic Compound) services. 3. In vacuum service, it is not necessary to reverse the ENVIRO-SEAL PTFE packing rings.	

Table 1. Class VI Shutoff Availability

VALVE	PORT SIZE, INCHES	SEAT	MINIMUM SEAT LOAD
ES	≤ 7	Metal	300 lbs/lineal inch

Table 2. Class VI Trim Materials

VALVE	CAGE/SEAT RING RETAINER	VALVE PLUG	SEAT RING	TRIM TEMPERATURE LIMIT	
				°C	°F
ES	S31600 (316 SST) / ENC	S31600/CoCr-A (alloy 6) seat	S31600	Not a limiting factor	Not a limiting factor

ENVIRO-SEAL, HIGH-SEAL Packing Systems

ENVIRO-SEAL and HIGH-SEAL packing systems offer excellent sealing capabilities. They easily install in your existing valves or can be purchased with new valves. These systems may help prevent the loss of process fluid. The long operational life and reliability of these systems also helps to reduce your maintenance costs and downtime.

For applications requiring compliance with environmental protection regulations, the unique Fisher ENVIRO-SEAL packing system (Figure 3) and a unique ENVIRO-SEAL bellows seal system (Figure 4) are offered. The emission control packing system helps to keep emission concentrations below the EPA 100 ppm requirement.

For an excellent stem seal in applications that are not environmentally-sensitive, the Fisher HIGH-SEAL Graphite ULF packing system is offered. The HIGH-SEAL packing system provides excellent sealing at pressure/temperature ratings beyond ENVIRO-SEAL limits.

ENVIRO-SEAL packing systems, available with PTFE, Graphite ULF or Duplex packing and the HIGH-SEAL packing systems, Graphite ULF and graphite composite, feature live-loading and unique packing-ring arrangements for long-term, consistent sealing performance.

Class VI Shutoff Capabilities

ES valves with metal seat constructions can provide ANSI/FCI Class VI shutoff capabilities. See Tables 1 and 2.

Table 3. Available Valve Body Constructions

VALVE	VALVE SIZE, NPS	BODY MATERIAL AND END CONNECTION STYLE ⁽¹⁾							
		Carbon Steel, Alloy Steel or Stainless Steel Valve Body						Cast Iron Valve Body	
		Screwed	RF or RTJ Flanged			Butt-welding	Socket Weld	CL125 FF Flanged	CL250 RF Flanged
			CL150	CL300	CL600				
ES	1/2 or 3/4	X	---	---	---	---	X	---	---
	1, 1-1/2 or 2	X	X	X	X	X	X	X	X
	1-1/4	X	---	---	---	---	---	---	---
	2-1/2, 3, 4, 6 or 8	---	X	X	X	X	---	X	X
EAS	1 or 2	---	X	X	X	X	---	---	---
	3, 4 or 6	---	X	X	X	X	---	---	---
X = Available Construction. 1. End connection style abbreviations: FF - Flat Faced, RF - Raised Face, RTJ - Ring Type Joint.									

Figure 1. Fisher ES Sectional




Table 4. Typical Combinations of Metal Trim Parts⁽¹⁾ for all Valves Except Those for NACE Specification and Whisper Trim III and Whisper NXG Trim Cages

TRIM DESIGNATION	VALVE PLUG	CAGE	SEAT RING FOR STANDARD METAL-SEAT CONSTRUCTION	OPTIONAL LINER (METAL-SEAT EAS VALVE BODY ONLY)	DISK SEAT AND RETAINER FOR OPTIONAL PTFE-SEAT CONSTRUCTION
1 (standard for metal-seat ES and EAS in all valve body materials except CF8M)	S41600 HT	17-4 SST HT ⁽⁶⁾	S41600 HT or CA15 HT ⁽¹⁾ (410 stainless steel)	S41600 HT	---
	17-4 SST HT ⁽⁶⁾				
3 ⁽⁵⁾ and 3H ⁽⁴⁾	S31600 with seat and guide hard faced with CoCr-A hardfacing alloy	R30006 or R30016 (alloy 6)	R30006 (alloy 6)	---	---
4 ⁽²⁾	S31600	17-4 SST HT	S31600	S31600	S31600
27	S31600 with seat and guide hard faced with CoCr-A hardfacing alloy	316 SST with electroless nickel coating (ENC)	R30006 (alloy 6)	---	---
28 ⁽³⁾	S31600 with seat hard faced with CoCr-A hardfacing alloy				
29 ⁽³⁾ (standard for CF8M valve bodies in all designs regardless of seat construction)	S31600	316 SST with ENC	S31600	S31600	S31600
37 and 37H ⁽⁴⁾	S31600 with seat and guide hard faced with CoCr-A hardfacing alloy	17-4 SST HT	R30006 (alloy 6)	---	---
57 (standard for PTFE-seat constructions in all designs and valve body materials except CF8M)	S41600 alloy HT	17-4 SST HT ⁽⁶⁾	---	---	S31600
	17-4 SST HT ⁽⁶⁾				
316L	S31603	316L SST with electroless nickel coating (ENC)	S31603	---	S31603
316L HF	S31603 with seat and guide hard faced with CoCr-A hardfacing alloy	316L SST with electroless nickel coating (ENC)	R30006 (alloy 6)	---	S31603 disk retainer with CoCr-A disk seat
1. CA15 is used for NPS 6 and 8 full-size and restricted-trim valves. 2. Not for use with Whisper Trim I. 3. Not for use with Whisper Trim I with 136.5 mm / 5.375 in. and larger ports. 4. Trims 3H and 37H have clearance for high-temperature service. 5. For trim 3, upper temperature limited to 316°C / 600°F when used for Whisper Trim I. 6. For NPS 8 Whisper Trim I.					

Table 5. Whisper Trim III and Whisper NXG Trim Metal Trim Part Materials and Body/Trim Temperature Capabilities

TRIM DESIGNATION	VALVE PLUG	CAGE	CAGE RETAINER	BAFFLE (FOR LEVEL D3 CAGE ONLY)	SEAT RING FOR METAL-SEAT CONSTRUCTION	DISK SEAT AND RETAINER FOR PTFE-SEAT CONSTRUCTION	STEM	BODY, BONNET AND BONNET SPACER	MATERIAL TEMPERATURE CAPABILITY			
									°C		°F	
									Min.	Max.	Min.	Max.
19.1 through 111.1 and 177.8 mm / 0.75 through 4.375 and 7 in. Port Sizes with Whisper III Trim Cage												
301G	S41600	17-4 SST	---	Steel	S41600	---	S31600	WCC, WC9	-29	427	-20	800
								CF8M ⁽⁷⁾	-29	176	-20	350
301GC	S41600	17-4 SST	---	Steel	---	S31600	S31600	WCC, WC9	-29	204	-20	400
								CF8M	-29	176	-20	350
312G ⁽¹⁾	S31600/ CoCr-A Seat and Guide	316 SST/ ENC Electroless Nickel Coated	---	S31600	R30006	---	S20910	WCC, WC9,	-29	343	-20	650
								CF8M	-198	343	-325	650
312GC ⁽¹⁾	S31600/ CoCr-A Seat and Guide	316 SST/ ENC Electroless Nickel Coated	---	S31600	---	R30006/ S31600	S20910	WCC, WC9,	-29	204	-20	400
								CF8M	-73	204	-100	400
315G ⁽¹⁾	S31600/ CoCr-A Seat and Guide	316 SST Chrome Plate	---	S31600	R30006	---	S20910	WCC, WC9	-29	316	-20	600
								CF8M	-198	316	325	600
315GC ⁽¹⁾	S31600/ CoCr-A Seat and Guide	316 SST Chrome Plate	---	S31600	---	R30006/ S31600	S20910	WCC, WC9	-29	204	-20	400
								CF8M	-73	204	-100	400
318G	F22/ CoCr-A Seat and Guide	2.25 Cr-1Mo Nitrided	---	WC9	R30006	---	S41000/ S42200 ⁽⁴⁾	WCC	-29	427	-20	800
								WC9	-29	593	-20	1100
306	S31803/ CoCr-A Seat and Guide (< 3" Port), S31803/ Ultimet Seat and Guide (≥ 3" Port)	2205 Duplex ⁽⁵⁾ Chrome Plate	---	S31803	S31803/ CoCr-A (< 3"Port), S31803/ Ultimet (≥ 3"Port)	---	S31803	WCC, WC9,	-29	316	-20	600
								CF8M	-51	316	-60	600
307G	S31600/ CoCr-A Seat and Guide	17-4 SST	---	Steel	R30006	---	S31600	WCC, WC9	-29	210	-20	410
307GH ⁽³⁾	S31600/ CoCr-A Seat and Guide	17-4 SST	---	Steel	R30006	---	S31600	WCC, WC9	210	427	410	800

- continued -

**Table 5. Whisper Trim III and Whisper NXG Trim Metal Trim Part Materials and Body/Trim
Temperature Capabilities (continued)**

TRIM DESIGNATION	VALVE PLUG	CAGE	CAGE RETAINER	BAFFLE (FOR LEVEL D3 CAGE ONLY)	SEAT RING FOR METAL-SEAT CONSTRUCTION	DISK SEAT AND RETAINER FOR PTFE-SEAT CONSTRUCTION	STEM	BODY, BONNET AND BONNET SPACER	MATERIAL TEMPERATURE CAPABILITY			
									°C		°F	
									Min.	Max.	Min.	Max.
19.1 through 111.1 and 177.8 mm / 0.75 through 4.375 and 7 in. Port Sizes with Whisper III Trim Cage												
301GNXG	S41600	17-4 H1075	---	---	S41600	---	S31600	WCC, WC9	-29	427	-20	800
								CF8M ⁽⁵⁾	-29	176	-20	350
312GNXG ⁽¹⁾	S31600/ CoCr-A Seat and Guide	S31603/ ENC	---	---	R30006	---	S20910	WCC, WC9	-29	343	-20	650
								CF8M	-198	343	-325	650
307GNXG	S31600/ CoCr-A Seat and Guide	17-4 H1075	---	---	R30006	---	S31600	WCC, WC9	-29	210	-20	410
307GHNXG ⁽³⁾	S31600/ CoCr-A Seat and Guide	17-4 H1075	---	---	R30006	---	S31600	WCC, WC9	210	427	410	800
306NXG	S31803/ Ultimet Seat and Guide	R31233 (Ultimet)	---	---	S31803/ Ultimet (>1-7/8" Port), R30006 (≤1-7/8" Port)	---	S31803	WCC, WC9, CF8M	-29	316	-20	600
								CF8M	-51	316	-60	600
136.5 mm / 5.375 in. Port with Whisper III Trim Cage												
301	S17400	416 SST	WCC/ENC	Steel	S41600	---	S31600	WCC, WC9	-29	343	-20	650
								CF8M	-29	163	-20	325
301 A	S17400	416 SST	WCC/ Nitrided	Steel	S41600	---	S31600	WCC, WC9	-29	427	-20	800
301 C	S17400	416 SST	WCC/ENC	Steel	---	S31600	S31600	WCC, WC9	-29	204	-20	400
								CF8M	-29	163	-20	325
304	S31600/ CoCr-A Seat and Guide	416 SST	WCC/ENC	Steel	S31600/ CoCr-A Seat	---	S31600	WCC, WC9	-29	343	-20	650
								CF8M	-29	177	-20	350
312 ⁽¹⁾	S31600/ CoCr-A Seat and Guide	316 SST/ ENC Electroless Nickel Coated	316/ENC Electroless Nickel Coated	S31600	R30006	---	S20910	WCC, WC9, CF8M	-29	343	-20	650
312C ⁽¹⁾	S31600/ CoCr-A Seat and Guide	316 SST/ ENC Electroless Nickel Coated	316/ENC Electroless Nickel Coated	S31600	---	R30006/ S31600	S20910	WCC, WC9	-29	204	-20	400
								CF8M	-29	204	-325	400
315	S31600/ CoCr-A Seat and Guide	316 SST/ Electro- lyzed Chrome Coat	S31600/ Electrolyzed Chrome Coat	S31600	S31600/ CoCr-A	---	S31600/ S20910 ⁽⁶⁾	WCC, WC9	-29	260	-20	500
								CF8M	-198	537 ⁽²⁾	-325	1000 ⁽²⁾

- continued -

Table 5. Whisper Trim III and Whisper NXG Trim Metal Trim Part Materials and Body/Trim Temperature Capabilities (continued)

TRIM DESIGNATION	VALVE PLUG	CAGE	CAGE RETAINER	BAFFLE (FOR LEVEL D3 CAGE ONLY)	SEAT RING FOR METAL-SEAT CONSTRUCTION	DISK SEAT AND RETAINER FOR PTFE-SEAT CONSTRUCTION	STEM	BODY, BONNET AND BONNET SPACER	MATERIAL TEMPERATURE CAPABILITY			
									°C		°F	
									Min.	Max.	Min.	Max.
318	S31600/ CoCr-A Seat and Guide	2.25 Cr-1Mo Nitrided	WC9 Nitrided	WC9	S31600/ CoCr-A Seat	---	S20910	WCC	-29	427	-20	800
								WC9	-29	593	-20	1100
306	S31803/ Ultimet Seat and Guide	2205 Duplex ⁽⁵⁾ Chrome Plate	---	S31803	S31803/ Ultimet	---	S31803	WCC, WC9,	-29	316	-20	600
								CF8M	-51	316	-60	600

1. NACE compatible trims meets NACE MR0175 2002, MR0175/ISO15156, MR0103.
2. May be used up to 593°C / 1100°F. If manufacturing process controls carbon content to 0.04% minimum or 0.08% maximum.
Not applicable to NXG trim.
3. For high temperature service.
4. Trim 318G uses S41000 stem up to 538°C / 1000°F and S42200 stem above 538°C / 1000°F.
5. 22 Cr-S Ni duplex stainless steel.
6. Trim 315 uses S31600 stem up to 427°C / 800°F and S20910 stem above 427°C / 800°F.
7. Trim 301G and 301GNXG can be used up to 216°C / 420°F with NPS 2.5 and NPS 3 CF8M body, can be used up to 354°C / 670°F with NPS 1 and NPS 1.5 CF8M body.

Figure 2. Fisher EAS Sectional




Table 6. Valve Body/Trim Temperature Capabilities for Metal Trim Parts Only

BODY/BONNET MATERIAL (ALSO FOR BOTTOM FLANGE IF USED)	TRIM DESIGNATION	VALVE SIZE AND DESIGN	MATERIAL TEMPERATURE CAPABILITY			
			°C		°F	
			Min.	Max.	Min.	Max.
Cast iron body with steel bonnet	1, 3, 27, 29, 37 or 57	All	-29	232	-20	450
CF3M	316L	All	-198 ⁽¹⁾	149 ⁽²⁾	-325 ⁽¹⁾	300 ⁽²⁾
	316L HF		-198 ⁽¹⁾	343	-325 ⁽¹⁾	650
CF8M (316 SST)	27	All	-198 ⁽¹⁾	343	-325 ⁽¹⁾	650
	28		-198 ⁽¹⁾	149	-325 ⁽¹⁾	300
	29		-198 ⁽¹⁾	149 ⁽²⁾	-325 ⁽¹⁾	300 ⁽²⁾
LCC steel	1	All	-29	343	-20	650
	4		-46	210	-50	410
	29		-46	149 ⁽²⁾	-50	300 ⁽²⁾
	37		-46	343	-50	650
WCC steel	1, 37 or 57	All	-29	427	-20	800
	29		-29	149 ⁽²⁾	-20	300 ⁽²⁾
	54		-29	260	-20	500
WC9 chrome moly steel	1, 37 or 57	All	-29	427	-20	800
	3		-29	427 ⁽³⁾	-20	800 ⁽³⁾
	3H		427	566	800	1050
	27	Through NPS 3 all designs; NPS 8 ES	-29	343	-20	650
		NPS 4 or 6 ES and EAS	-29	343	-20	650
	29	All	-29	149 ⁽²⁾	-20	300 ⁽²⁾

1. May be used down to -254°C / -425°F if manufacturing process includes Charpy impact test.
2. Lubricating service allows usage to 316°C / 600°F.
3. For Trim 3, upper temperature to 316°C / 600°F when used for Whisper Trim I cages.

Table 7. Bonnet Selection Guidelines

BONNET STYLE	PACKING MATERIAL	IN-BODY PROCESS TEMPERATURE LIMITS ⁽¹⁾	
		°C	°F
Plain: - Standard for all valves through NPS 6 with 2-13/16 yoke boss diameter - Standard for NPS 6 and 8 valves in cast iron and WCC steel bonnet material with 3-9/16 yoke boss diameter	PTFE V-ring	-18 to 232	0 to 450
	PTFE/Composition	-18 to 232	0 to 450
	Graphite ribbon/filament	-18 to maximum shown in Table 9	0 to maximum shown in Table 9
Style 1 Cast Extension: Standard for NPS 8 valves in S31600 bonnet material with 3-9/16 yoke boss diameter	PTFE V-ring	-46 to 427	-50 to 800
	PTFE/Composition		
	Graphite ribbon/filament	-46 to maximum shown in Table 9	-50 to maximum shown in Table 9
Style 2 Cast Extension: - Optional for NPS 2 through 4 valves with 2-13/16 in. yoke boss diameter - Optional for NPS 6 and 8 valves with 3-9/16 yoke boss diameter	PTFE V-ring	-101 to 427	-150 to 800
	PTFE/Composition		
	Graphite ribbon/filament	-101 to maximum shown in Table 9	-150 to maximum shown in Table 9
ENVIRO-SEAL bellows seal bonnet	PTFE	For exceptional stem sealing capabilities, see Bulletin 59.1:070, ENVIRO-SEAL Bellows Seal Bonnets (D101641X012), for pressure/temperature ratings.	For exceptional stem sealing capabilities, see Bulletin 59.1:070, ENVIRO-SEAL Bellows Seal Bonnets (D101641X012), for pressure/temperature ratings.
	Graphite ULF		

1. These in-body process temperatures assume an outside, ambient temperature of 21°C / 70°F and no insulation on the bonnet. When using any packing at low process temperatures, a cast extension bonnet may have to be used to prevent packing damage which could result from the formation of valve stem frost. Material selection for trim and other components will also be limiting factors.



Figure 3. ENVIRO-SEAL and HIGH-SEAL Packing Systems

Table 8. Maximum Flow Coefficients for Full-Sized Trim with Equal Percentage Cage and Normal Flow Direction⁽¹⁾

VALVE	VALVE SIZE, NPS	C _v AT MAX VALVE PLUG TRAVEL
ES	1/2	6.53 ⁽²⁾
	3/4	14.2 ⁽²⁾
	1, 1-1/4	17.4
	1-1/2	33.4
	2	56.2
	2-1/2	82.7
	3	121
EAS (flow down)	4	203
	6	357
	8	808
	1	19.0
	2	47.2
	3	148
	4	156
	6	328

1. Except where indicated, flow coefficients for linear and quick-opening cages normally are somewhat greater.
2. Quick-opening cage.

Figure 4. ENVIRO-SEAL Bellows Seal Bonnet



W5852

Table 9. Materials and Temperature Limits for All Other Parts

PART			MATERIAL	MATERIAL TEMPERATURE CAPABILITIES			
				°C		°F	
				Min.	Max.	Min.	Max.
Body-to-bonnet bolting. See Table 11 for NACE bolting materials and temperatures	Cast iron body	Cap screws	Steel SAE Grade 5	-29	232	-20	450
	WCC or WC9 body	Studs	Steel SA-193-B7	-29	427 ⁽¹⁾	-20	800 ⁽¹⁾
		Nuts	Steel SA-194-2H				
	CF3M or CF8M body	Studs	Steel SA-193-B7 (std)	-48	427 ⁽¹⁾	-55	800 ⁽¹⁾
		Nuts	Steel SA-194-2H (std)				
		Studs	304 stainless steel SA-320-B8	-198	38	-325	100
		Nuts	304 stainless steel SA-194-8				
		Studs	316 stainless steel SA-193-B8M (strain-hardened)	-198 ⁽²⁾	427 ⁽¹⁾	-325 ⁽²⁾	800 ⁽¹⁾
		Nuts	316 stainless steel SA-194-8M				
		Studs	316 stainless steel SA-194-B8M (annealed)	-198 ⁽²⁾	These materials not limiting factors	-325 ⁽²⁾	These materials not limiting factors
		Nuts	316 stainless steel SA-194-8M				
		Studs	Steel SA-193-B7	-46	343 ⁽¹⁾	-50	650 ⁽¹⁾
		Nuts	Steel SA-194-2H				
	LCC body	Studs	Steel SA-193-B16	-29	566 ⁽¹⁾	-20	1050 ⁽¹⁾
WC9 body	Nuts	Steel SA-194-7					
Optional disk			PTFE	-73	204	-100	400
Valve plug stem			316 stainless steel or 316L stainless steel	-198 ⁽²⁾	593	-325 ⁽²⁾	1100
Pin (ES or EAS valve only)			316 stainless steel or 316L stainless steel				
Load ring	(NPS 8 ES valve only)		17-4PH stainless steel	-101	316	-150	600
			N06600	-254	593	-425	1100
			N05500 Nickel Alloy	-240	260	-400	500
Restricted trim adaptors			Cast iron	-73	232	-100	450
			WCC steel	-29	427	-20	800
			316 stainless steel	-198 ⁽²⁾	593	-325 ⁽²⁾	1100
Seat ring, bonnet and cage gaskets			Flexible Graphite (standard)	-198	593 ⁽³⁾	-325	1100 ⁽³⁾
			PTFE-coated N04400 Nickel Alloy	-73	149	-100	300
Spiral wound gaskets			N06600 Nickel Alloy 600/graphite (Flexible Graphite) standard	-198	593 ⁽³⁾	-325	1100 ⁽³⁾
			N04400 Nickel Alloy/composition	-73	232	-100	450
Shim			316 stainless steel	These materials not limiting factors			
			N04400 Nickel Alloy	These materials not limiting factors			
Packing	(temperatures shown are material temperature capabilities)	See Table 7 for proper bonnet selection	PTFE V-ring	-40	232	-40	450
			PTFE/composition	-73	232	-100	450
			Graphite ribbon/filament	-198	538 ⁽⁴⁾	-325	1000 ⁽⁴⁾
			Graphite ribbon for high-temperature oxidizing service	371	649	700	1200
Packing flange studs and nuts when used with standard bonnet			316 stainless steel	-198 ⁽²⁾	593	-325 ⁽²⁾	1100
Packing follower and packing spring (single PTFE V-ring packing) or lantern ring (other packing arrangements)			316 stainless steel	-198 ⁽²⁾	593	-325 ⁽²⁾	1100
Packing box ring			316 stainless steel	-198 ⁽²⁾	593	-325 ⁽²⁾	1100
Extension bonnet bushing	Trims 1 and 4		416 stainless steel	-29	427	-20	800
	Other trims		316 stainless steel	-198 ⁽²⁾	593	-325 ⁽²⁾	1100

1. Lubricated nuts are standard.

2. May be used down to -254°C / -425°F if manufacturing process includes Charpy impact test.

3. Except 427°C / 800°F on oxidizing service.

4. Except 371°C / 700°F on oxidizing service.

1. Lubricated nuts are standard.

2. May be used down to -254°C / -425°F if manufacturing process includes Charpy impact test.

3. Except 427°C / 800°F on oxidizing service.


4. Except 371°C / 700°F on oxidizing service.

Table 10. Metal Trim Part Materials for Compatibility with NACE MR0175-2002 (Sour Service) Specifications, Environmental Restrictions Apply, Refer to Standard

TRIM DESIGNATION	VALVE PLUG	CAGE	SEAT RING FOR STANDARD METAL SEAT CONSTRUCTION	OPTIONAL LINER FOR METAL SEAT (EAS ONLY)	DISK SEAT AND RETAINER FOR OPTIONAL PTFE-SEAT CONSTRUCTION	VALVE STEM, PACKING FOLLOWER, LANTERN RING, PACKING BOX RING AND PIN	LOAD RING ⁽¹⁾
85 ⁽³⁾	S31600	316 SST with ENC	S31600	S31600	---	Valve stem is S20910 All other parts are S31600	N05500
85C ⁽²⁾⁽³⁾	S31600	316 SST with ENC	---	---	S31600		
86 ⁽³⁾	S31600 with seat hard faced with CoCr-A hard facing alloy	316 SST with ENC	R30006 (alloy 6)	---	---		
87	S31600 with seat and guide hard faced with CoCr-A hard facing alloy	316 SST with ENC	R30006 (alloy 6)	---	---		
87C ⁽²⁾	S31600 with seat and guide hard faced with CoCr-A hard facing alloy	316 SST with ENC	---	---	S31600		

1. NPS 8 valve only.
2. 85C and 87C are trims for PTFE-seat construction.
3. Not for use with Whisper Trim I with 136.5 mm / 5.375 in. and larger ports.

Figure 5. Typical Trim Used for NACE MR0175-2002, (Sour Service)



NOTE:

1. Do not exceed the maximum pressure and temperature for the pressure rating of the valve body material used, even though the trims shown may have higher capabilities.

Table 11. Bolting Materials and Temperature Limits for Bolting Compliance with NACE MR0175-2002, NACE MR0175/ISO 15156 and NACE MR0103. Environmental restrictions may apply.

VALVE BODY MATERIAL		BOLTING MATERIAL	TEMPERATURE CAPABILITIES			
			°C		°F	
			Min.	Max.	Min.	Max.
Non-exposed bolting (Standard)						
WCC	Studs	Steel SA-193-B7	-7	232	20	450
	Nuts	Steel SA-194-2H				
	Studs	Steel SA-193-B7	232	427	450	800
	Nuts	Steel SA-194-2H				
CF8M (316 SST)	Studs	Steel SA-193-B7 or B8M strain hardened	-48	232	-55	450
	Nuts	Steel SA-194-2H or 8M				
	Studs	Steel SA-193-B8M strain hardened or B7	232	427	450	800
	Nuts	Steel SA-194-8M lubricated or 2H				
Exposed bolting (Optional) Requires Derating of Valve ⁽²⁾ When These Body-to-Bonnet Bolting Materials are Used						
WCC and CF8M	Studs	Steel SA-193-B7M	-46 ⁽¹⁾	232	-50 ⁽¹⁾	450
	Nuts	Steel SA-194-2HM				
	Studs	Steel SA-193-B7M	232	427	450	800
	Nuts	Steel SA-194-2HM				

1. Minimum temperature is -29°C / -20°F with WCC valve body material.

2. Derating is not required for CL300 valves. Derating may be required for valves rated at CL600. Contact your [Emerson sales office](#) for assistance in determining the derating of valves when these body-to-bonnet bolting materials are used.

Table 12. Port Diameters, Valve Plug Travel and Stem and Yoke Boss Diameters

VALVE SIZE, NPS				PORT DIAMETER		MAX VALVE PLUG TRAVEL		STEM AND YOKE BOSS DIAMETERS							
ES		EAS						Standard				Optional			
								Stem		Yoke Boss		Stem		Yoke Boss	
Full-Sized Trim	Restricted-Capacity Trim	Full-Sized Trim	Restricted-Capacity Trim	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
1 or 1-1/4	1-1/2	1	2	33.3	1.3125	19	0.75	9.5	3/8	54	2-1/8	12.7	1/2	71	2-13/16
---	2	---	---	33.3	1.3125	19	0.75	12.7	1/2	71	2-13/16	---	---	---	---
1-1/2	---	2	---	47.6	1.875	19	0.75	9.5	3/8	54	2-1/8	12.7	1/2	71	2-13/16
---	2-1/2	---	3	47.6	1.875	19	0.75	12.7	1/2	71	2-13/16	---	---	---	---
2	3	---	4	58.7	2.3125	29	1.125	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16
2-1/2	4	3	6	73.0	2.875	38	1.5	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16
3	---	4	---	87.3	3.4375	38	1.5	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16
4	---	6	---	111.1	4.375	51	2	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16
												25.4	1	127	5
6	---	---	---	177.8	7	51	2	19.1	3/4	90	3-9/16	25.4 or 31.8	1 or 1-1/4	127	5
8	---	---	---	203.2	8	51	2								
						76	3								

Table 13. Port Diameter, Valve Plug Travel and Stem and Yoke Boss Diameters for Whisper NXG Trim⁽¹⁾ and Whisper III Trims⁽²⁾

VALVE SIZE, NPS		PORT DIAMETER		MAX VALVE PLUG TRAVEL		STEM AND YOKE BOSS DIAMETERS								PERFORMANCE LEVEL
ES	EAS					Standard				Optional				
						Stem		Yoke Boss		Stem		Yoke Boss		
		mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	
1	1	33.3	1-5/16	19	3/4	9.5	3/8	54	2-1/8	12.7	1/2	71	2-13/16	A1
1-1/2	2	47.6	1-7/8	19	3/4	9.5	3/8	54	2-1/8	12.7	1/2	71	2-13/16	A1
		33.3	1-5/16	19	3/4									A3, B1, B3, C1
		19.1	3/4	29	1-1/8									C1, C3, D1, D3
2	---	58.7	2-5/16	35	1-3/8	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16	A1
		33.3	1-5/16	29	1-1/8									A3, B1, B3,C1, C3, D1, D3
2-1/2	3	73.0	2-7/8	38	1-1/2	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16	A1
		47.6	1-7/8											A3, B1, B3,C1, C3, D1, D3
3	4	87.3	3-7/16	38	1-1/2	12.7	1/2	71	2-13/16	19.1	3/4	90	3-9/16	A1
		58.7	2-5/16											A3, B1, B3,C1, C3, D1, D3
4	6	111.1	4-3/8	51	2	12.7	1/2	71	3-9/16	19.1	3/4	90	3-9/16	A1
		87.3	3-7/16							25.4	1	127	5	A3, B1, B3,C1, C3, D1, D3
6	---	177.8	7	51	2	19.1	3/4	90	3-9/16	25.4 or 31.8	1 or 1 1/4	127	5	A1
		136.5	5-3/8	76	3					A3, B1, B3,C1, C3, D1, D3				
8	---	203.2	8	76	3	19.1	3/4	90	3-9/16	25.4 or 31.8	1 or 1 1/4	127	5	A1
				102	4									A3, B1, B3,C1, C3, D1, D3


1. Currently, Whisper NXG is only available to levels A1, B1 and C1.

2. Refer to Fisher Bulletin 80.1:010 Whisper Trim III (D100191X012) for more information.

1. Currently, Whisper NXG is only available to levels A1, B1 and C1.

2. Refer to Fisher Bulletin 80.1:010 Whisper Trim III (D100191X012) for more information.

Figure 6. Typical Trim Use for All Valve Bodies Except Those for NACE Specifications



C0459-5

NOTES:


1. Do not exceed the maximum pressure and temperature for the pressure rating of the valve body material used, even though the trims shown may have higher capabilities.
2. Be especially careful to specify service temperature if trim 3, 4 or 37 are selected, as different thermal expansion rates required special plug clearances. Also, use trim 37 instead of trim 4 for nonlubricating fluids such as superheated steam or dry gases between 149 and 316°C / 300 and 600°F.
3. Trims 4 and 29 can be used to pressure drop shown only with clean, dry gas. For other than clean, dry gas, trims 4 and 29 can be used only up to 21 bar / 300 psi.
4. Use trim 27 instead of trim 29 for non-lubricating fluids such as superheated steam or dry gases between 149 and 316°C / 300 and 600°F.

Table 14. Fisher ES Dimensions

VALVE SIZE, NPS	A									G(MAX)
	Scrd or SW	125 FF or 150 RF	150 RTJ	250 RF or 300 RF	300 RTJ	BW or 600 RF	600 RTJ	PN 16-40 ⁽¹⁾	PN 63-100 ⁽¹⁾	ES
mm										
1/2, 3/4	165	---	---	---	---	---	---	---	---	54
1	210	184	197	197	210	210	210	160	230	56
1-1/4	229	---	---	---	---	---	---	---	---	56
1-1/2	251	222	235	235	248	251	251	200	260	71
2	286	254	267	267	282	286	289	230	300	78
2-1/2	---	276	292	292	308	311	314	290	340	90
3	---	298	311	317	333	337	340	310	380	97
4	---	353	365	368	384	394	397	350	430	129
6	---	451	464	473	489	508	511	480	550	140
8	---	543	556	568	584	610	613	600	650	191
in.										
1/2, 3/4	6.50	---	---	---	---	---	---	See mm above	See mm above	2.12
1	8.25	7.25	7.75	7.75	8.25	8.25	8.25			2.38
1-1/4	9.00	---	---	---	---	---	---			2.38
1-1/2	9.88	8.75	9.25	9.25	9.75	9.88	9.88			2.81
2	11.25	10.00	10.50	10.50	11.12	11.25	11.38			3.06
2-1/2	---	10.88	11.38	11.50	12.12	12.25	12.38	See mm above	See mm above	3.56
3	---	11.75	12.25	12.50	13.12	13.25	13.38			3.81
4	---	13.88	14.38	14.50	15.12	15.50	15.62			5.06
6	---	17.75	18.25	18.62	19.25	20.00	20.12			5.5
8	---	21.38	21.88	22.38	23.00	24.00	24.12			7.50

1. Valves which meet EN flange standards and have DN face-to-face dimensions are available only from Europe. Valves which meet EN flange standards but not DN face-to-face standards are available in the US. Consult your Emerson Automation Solutions sales office.

Figure 7. Fisher ES Dimensions (also see Tables 14, 15 and 16)



AR4967-A
10A7397-B
B1534-1

NOTE:

1. $B = \frac{A}{2}$

Table 15. Fisher ES Dimensions

VALVE SIZE, NPS	D FOR PLAIN BONNET			
	ES			
	Stem Diameter			
	mm			
	9.5	12.7	19.1	25.4 or 31.8
1/2, 3/4, 1, 1-1/4	127	149	---	---
1-1/2	124	146	---	---
2	---	165	162	---
2-1/2	---	187	184	---
3	---	191	187	---
4	---	221	217	264
6 ⁽²⁾	---	---	251	270
6 ⁽³⁾	---	---	312	330
8	---	---	375 ⁽¹⁾	426
	in.			
	3/8	1/2	3/4	1 or 1-1/4
1/2, 3/4, 1, 1-1/4	5.00	5.88	---	---
1-1/2	4.88	5.75	---	---
2	---	6.50	6.38	---
2-1/2	---	7.38	7.25	---
3	---	7.50	7.38	---
4	---	8.69	8.56	10.38
6 ⁽²⁾	---	---	9.88	10.62
6 ⁽³⁾	---	---	12.26	13.00
8	---	---	14.75 ⁽¹⁾	16.75

1. Available only in cast iron or WCC steel for the stem diameter with plain bonnet.
2. For all NPS 6 valves except with Whisper III cages and Whisper NXG Trim.
3. For NPS 6 valves with Whisper III cages and Whisper NXG Trim.

Table 16. Fisher ES Dimensions


VALVE SIZE, NPS	D FOR EXTENSION AND ENVIRO-SEAL BELLOWS SEAL BONNETS (ES ONLY)									
	Style 1 Ext. Bonnet				Style 2 Ext. Bonnet			ENVIRO-SEAL Bellows Seal Bonnet		
	Stem Diameter				Stem Diameter			Stem Diameter		
	mm									
	9.5	12.7	19.1	25.4 or 31.8	9.5	12.7	19.1	9.5	12.7	19.1
1/2, 3/4, 1, 1-1/4	213	251	---	---	303	319	---	321	---	---
1-1/2	210	248	---	---	300	316	---	317	---	---
2	---	267	---	---	---	465	---	---	384	---
2-1/2	---	289	272	---	---	492	---	---	---	---
3	---	292	297	---	---	495	487	---	518	518
4	---	322	327	370	---	526	518	---	541	---
6 ⁽¹⁾	---	---	357	402	---	---	543	---	---	573
6 ⁽²⁾	---	---	418	462	---	---	604	---	---	---
8	---	---	421	450	---	---	621	---	---	---
VALVE SIZE, NPS	in.									
	3/8	1/2	3/4	1 or 1-1/4	3/8	1/2	3/4	3/8	1/2	3/4
1/2, 3/4, 1, 1-1/4	8.38	9.88	---	---	11.94	12.56	---	12.62	---	---
1-1/2	8.25	9.75	---	---	11.81	12.44	---	12.50	---	---
2	---	10.50	---	---	---	18.31	---	---	15.12	---
2-1/2	---	11.38	10.69	---	---	19.38	---	---	---	---
3	---	11.50	11.69	---	---	19.50	19.19	---	20.38	20.38
4	---	12.69	12.88	14.56	---	20.69	20.38	---	21.31	---
6 ⁽¹⁾	---	---	14.06	15.81	---	---	21.38	---	---	22.56
6 ⁽²⁾	---	---	16.44	18.19	---	---	23.76	--	--	--
8	---	---	16.56	17.75	---	---	24.44	---	---	---

1. For all NPS 6 valves except with Whisper III cages and Whisper NXG Trim.
2. For NPS 6 valves with Whisper III cages and Whisper NXG Trim.

Table 17. Fisher EAS Dimensions

VALVE SIZE, NPS	AA					
	CL150		CL300		CL600	
	RF	RTJ	RF	RTJ	BW, SW or RF	RTJ
	mm					
1	92	98	98	105	105	105
2	127	133	133	141	143	144
3	149	156	159	167	168	170
4	176	183	184	197	197	198
6	225	232	237	244	254	256
VALVE SIZE, NPS	in.					
1	3.62	3.88	3.88	4.12	4.12	4.12
2	5.00	5.25	5.25	5.56	5.62	5.69
3	5.88	6.12	6.25	6.56	6.62	6.69
4	6.94	7.19	7.25	7.56	7.75	7.81
6	8.88	9.12	9.31	9.62	10.00	10.06

**Figure 8. Fisher EAS Dimensions
(also see Tables 17 and 18)**



AU6190-A
A0927-1

NOTE:
For dimensions of valves with EN (or other) end connections,
consult your Emerson sales office.

Table 18. Fisher EAS Dimensions

VALVE SIZE, NPS	DD												
	Plain Bonnet				Style 1 Extension Bonnet			Style 2 Extension Bonnet			ENVIRO-SEAL Bellows Seal Bonnet		
	Stem Diameter												
	mm												
	9.5	12.7	19.1	25.4 or 31.8	9.5	12.7	19.1	9.5	12.7	19.1	9.5	12.7	19.1
1	111	133	---	---	197	235	---	291	305	---	Contact your Emerson sales office		
2	98	121	---	---	184	223	---	278	291	---			
3	---	149	146	---	---	251	256	---	454	---			
4	---	140	137	---	---	241	246	---	445	437			
6	---	144	141	187	---	246	251	---	449	441			
VALVE SIZE, NPS	in.												
	3/8	1/2	3/4	1 or 1-1/4	3/8	1/2	3/4	3/8	1/2	3/4	3/8	1/2	3/4
1	4.38	5.25	---	---	7.75	9.25	---	11.44	12.00	---	Contact your Emerson sales office		
2	3.88	4.75	---	---	7.25	8.75	---	10.94	11.44	---			
3	---	5.88	5.75	---	---	9.88	10.06	---	17.88	---			
4	---	5.50	5.38	---	---	9.50	9.69	---	17.50	17.19			
6	---	5.69	5.56	7.38	---	9.69	9.88	---	17.69	17.38			

 [LinkedIn.com/groups/3941826](https://www.linkedin.com/groups/3941826)
 [Fisher.com](https://www.fisher.com)

 [Facebook.com/FisherValves](https://www.facebook.com/FisherValves)
 [X.com/FisherValves](https://www.x.com/FisherValves)

D100021X012 © 1983, 2025 Fisher Controls International LLC. All rights reserved.

Neither Emerson, nor any of its affiliated entities assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

Fisher, easy-e, ENVIRO-SEAL, FIELDVUE, and Whisper Trim are marks owned by one of the companies in the Emerson business unit of Emerson Electric Co. Emerson and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson
Marshalltown, Iowa 50158 USA
Sorocaba, 18087 Brazil
Cernay, 68700 France
Dubai, United Arab Emirates
Singapore 128461 Singapore

www.fisher.com

FISHER™

