

# PR 642x

## Eddy Current Sensors



## **Copyright**

© 2026, Emerson. All rights reserved.

No part of this publication may be reproduced, transmitted, transcribed, stored in a retrieval system, or translated into any language in any form by any means without the written permission of Emerson.

## **Disclaimer**

This manual is provided for informational purposes. EMERSON MAKES NO WARRANTY OF ANY KIND WITH REGARD TO THIS MATERIAL, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Emerson shall not be liable for errors, omissions, or inconsistencies that may be contained herein or for incidental or consequential damages in connection with the furnishing, performance, or use of this material. Information in this document is subject to change without notice and does not represent a commitment on the part of Emerson. The information in this manual is not all-inclusive and cannot cover all unique situations.

## **Patents**

The product(s) described in this manual are covered under existing and pending patents.

# Contents

|                  |                                                            |           |
|------------------|------------------------------------------------------------|-----------|
| <b>Chapter 1</b> | <b>General.....</b>                                        | <b>4</b>  |
|                  | 1.1 Using this manual.....                                 | 4         |
|                  | 1.2 Symbol explanation.....                                | 4         |
|                  | 1.3 Liability and guarantee.....                           | 4         |
|                  | 1.4 Incoming goods inspection.....                         | 5         |
|                  | 1.5 Technical support.....                                 | 5         |
|                  | 1.6 Storage and transport.....                             | 6         |
|                  | 1.7 Disposal of the device.....                            | 6         |
|                  | 1.8 China RoHS Compliance.....                             | 6         |
|                  | 1.9 CCC Certification – Eddy current measuring chains..... | 7         |
|                  | 1.10 Installation awareness.....                           | 7         |
| <b>Chapter 2</b> | <b>Safety Instructions.....</b>                            | <b>8</b>  |
|                  | 2.1 Using the device.....                                  | 8         |
|                  | 2.2 Owner's responsibility.....                            | 8         |
| <b>Chapter 3</b> | <b>Application and Design.....</b>                         | <b>9</b>  |
|                  | 3.1 The Measuring Chain.....                               | 9         |
|                  | 3.2 The Sensors.....                                       | 9         |
| <b>Chapter 4</b> | <b>Installation and Mounting.....</b>                      | <b>10</b> |
|                  | 4.1 Measuring chain and material of measuring target.....  | 10        |
|                  | 4.2 Choosing the measuring place.....                      | 10        |
|                  | 4.3 Mount the sensor.....                                  | 11        |
|                  | 4.3.1 Requirements and hints for the sensor mounting.....  | 11        |
|                  | 4.3.2 PR 6426 installation.....                            | 15        |
|                  | 4.4 Wiring hints.....                                      | 16        |
|                  | 4.5 Sensor cables with LEMO adapter plug.....              | 17        |
| <b>Chapter 5</b> | <b>Technical data.....</b>                                 | <b>19</b> |
|                  | 5.1 Measuring targets.....                                 | 19        |
|                  | 5.2 Measuring ranges and sensitivity.....                  | 20        |
|                  | 5.3 Environmental conditions and mechanical design.....    | 21        |
| <b>Chapter 6</b> | <b>Drawings.....</b>                                       | <b>23</b> |
| <b>Chapter 7</b> | <b>Order Matrix.....</b>                                   | <b>28</b> |
| <b>Chapter 8</b> | <b>Certificates.....</b>                                   | <b>32</b> |

# 1 General

## 1.1 Using this manual

This manual contains information concerning the proper and correct use of the PR 6422, PR 6423, PR 6424, PR 6425 and PR 6426 eddy current transducers.

For correct and safe use of this device read the entire operating manual prior to installing and operating the device. In particular, comply with all safety instructions contained in the manual.

Do not transfer the device to third parties without including the operating manual.

---

### Note

When requesting technical support for this device, please indicate type and serial number as shown on the type plate as well as the used converter type.

---

Table 1-1 shows a list of documents that are referred to in this installation guide.

**Table 1-1: Referenced documents**

|           |                                                                                    |
|-----------|------------------------------------------------------------------------------------|
| MHM-97858 | Installation guide CON 011, Converter for PR 642x Eddy Current Sensors             |
| MHM-97859 | Installation guide CON 021 and CON 031, Converter for PR 642x Eddy Current Sensors |
| MHM-97860 | Installation guide CON 041, Converter for PR 642x Eddy Current Sensors             |

## 1.2 Symbol explanation

---

### Note

This symbol marks passages that contain important information.

---

### CAUTION

Operations that may lead to malfunctions or faulty measurements, without damaging the device, are marked with this symbol.

---

### DANGER

A Danger indicates actions that can lead to property damage or personal injuries.

---

## 1.3 Liability and guarantee

Emerson is not liable for damages that occur due to improper use. Proper use also includes knowledge of, and compliance with this operating manual.

Customer changes to the device that have not been approved expressly by Emerson, will result in the loss of guarantee.

Due to continuous research and further development Emerson reserves the right to change technical specifications without notice.

## 1.4 Incoming goods inspection

Check the content of the shipment to ensure that it is complete; visibly inspect the goods to determine if the device has been damaged during transport. The following parts are included in the scope of delivery and must be contained in the shipment.

- Eddy current sensor PR 6422, PR 6423, PR 6423, PR 6425 or PR 6426 (with protection cap)
- Lemo connection cable (only PR 642x/xxx-0xx types)
- Mounting nuts (respectively screws at PR 6426)
- Shrink sleeve for isolating the adapter plug (only PR642x/xxx-0xx types)
- Operating manual for installing and using the sensor

If the contents are incomplete, or if you observe any defects, file a complaint with the carrier immediately. Moreover, inform the responsible Emerson sales organization so your device can be replaced. In this case, attach to the device a non-detachable tag with customer name and the observed defect.

## 1.5 Technical support

You may need to ship this product for return, replacement, or repair to an Emerson Product Service Center. Before shipping this product, contact Emerson Product Support to obtain a Return Materials Authorization (RMA) number and receive additional instructions.

### Product Support

Emerson provides a variety of ways to reach your Product Support team to get the answers you need when you need them:

|              |                                                                                                                                          |
|--------------|------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Phone</b> | Toll free 1 800 833 8314 (U.S. and Canada)<br>+1 512 832 3774 (Latin America)<br>+63 2 8702 1111 (Asia Pacific, Europe, and Middle East) |
| <b>Email</b> | <a href="mailto:Guardian.GSC@Emerson.com">Guardian.GSC@Emerson.com</a>                                                                   |
| <b>Web</b>   | <a href="http://www.emerson.com/en-us/contact-us">http://www.emerson.com/en-us/contact-us</a>                                            |

To search for documentation, visit <http://www.emerson.com>.

To view toll free numbers for specific countries, visit

<http://www.emerson.com/technicalsupport>.

---

**Note**

If the equipment has been exposed to a hazardous substance, a Material Safety Data Sheet (MSDS) must be included with the materials returned. An MSDS is required by law to be available to people exposed to specific hazardous substances.

---

## 1.6 Storage and transport

Store and transport the device only in its original packaging. Technical data specifies the environmental conditions for storage and transport.

**Related information**

[Environmental conditions and mechanical design](#)

## 1.7 Disposal of the device

Provided that no repurchase or disposal agreement exists, recycle the following components at appropriate facilities:

- Recyclable metal
- Plastic elements

Sort the remaining components for disposal, based on their condition. National laws or provisions on waste disposal and protection of the environment apply.

---

**Note**

Environmental hazards! Electrical waste and electronic components are subject to treatment as special waste and may only be disposed by approved specialized companies.

---

## 1.8 China RoHS Compliance

Our products manufactured later than June 30, 2016, and those which are sold in the People's Republic of China are marked with one of the following two logos to indicate the Environmental Friendly Use Period in which it can be used safely under normal operating conditions.

Products that do not have the following marking were either manufactured before June 30, 2016, or are not electrical equipment products (EEP).



Circling arrow symbol with "e": The product contains no hazardous substances over the Maximum Concentration Value and it has an indefinite Environmental Friendly Use Period.



Circling arrow symbol with a number: This product contains certain hazardous substances over the Maximum Concentration Value and it can be used safely under normal operating conditions for the number of years indicated in the symbol. The names and contents of hazardous substances can be found in chapter "Certificates".

## 1.9 CCC Certification – Eddy current measuring chains

With the announcement of the Chinese market regulation authority SAMR (State Administration for Market Regulation), a Compulsory Product Certification (CCC certification) is mandatory for many explosion protection products. This explosion proof (“Ex”) product complies to the CCC obligation and is certified (certification number: 2020322315002448).



This China Compulsory Certificate mark (CCC), is a compulsory safety mark for many products imported, sold, or used in the Chinese market and indicates that the product is certified in accordance to GB/T 3836.1-2021 and GB/T 3836.4-2021. If the product label is too small to contain the CCC certification mark it is sufficient to have the mark printed on the minimum package and in the attached document.

## 1.10 Installation awareness

---

### Note

When planning a measurement, follow these guidelines:

- Consider environmental conditions which might have an influence on the measurement such as temperature, humidity, substances aggressive to the sensor, pressure, and pollution.
  - Always use a stiff and vibration-free sensor holder.
  - Define a suitable measuring range, not larger than necessary, in consultation with the operator of the plant.
  - Define the trip limit in consultation with the operator of the plant.
  - Take measurement deviations into account when defining trip limits.
  - Use a sensor that meets the requirements of the defined measuring range.
  - Ensure an EMC-compatible installation including the use of proper cables.
  - Ensure proper function of the measurement before activating the measurement in the production environment.
-

## 2 Safety Instructions

To ensure safe operation, carefully observe all instructions in this manual.

The correct and safe use of this device requires that operating and service personnel both understand and comply with general safety guidelines and observe the special safety comments listed in this manual. Where necessary, safety-sensitive points on the device are marked.

### DANGER

Since the sensor is electrical equipment, commissioning and service may be performed only by trained personnel. Maintenance may be carried out only by trained, specialized, and experienced personnel.

### 2.1 Using the device

Measuring systems with eddy current sensors as PR 6422, PR 6423, PR 6424; PR 6425 and PR 6426 serve in conjunction with eddy current converters as CON 011, CON 021, CON 041, the transmitters with integrated converters of the MMS 3000 series or the transmitter CSI 9360 the measurement of mechanical quantities, such as shaft vibration, shaft displacement and speed (not if CSI 9360 is used).

### 2.2 Owner's responsibility

If there is a reason to suspect that hazard-free operation, and thus, adequate machine protection is no longer possible, take the device out of operation and safeguard it from unintentional operation. This is the case:

- if the device shows visible damage.
- if the device no longer works.
- after any kind of overload that has exceeded the permissible limits (see technical data of the device for permissible limits).

### DANGER

If device tests must be completed during operation or if the device must be replaced or decommissioned, it will impair the machine protection and may cause the machine to shut down. Make sure to deactivate machine protection before starting such work and reactivate it after work has been completed.

#### Related information

[Technical data](#)

## 3 Application and Design

### 3.1 The Measuring Chain

Together with signal converters of the series CON 0x1, integrated converters of the AMS 3000 series, or the AMS 9360 transmitter, the sensors PR 6422 to PR 6426 form eddy current measuring chains for contactless distance, vibration and speed measurements. Different types of sensors and converters allow an optimal adaption to the requirements of the machine to be monitored.

A additional electronic components, like the AMS 6500 ATG system, allow static and dynamic distance measurements, which means it is possible to measure slow axial displacements and quick axial shaft vibrations of rotating machines.

To achieve a high accuracy, the measuring chains consisting of both converter and sensor are adjusted together and delivered as complete measuring chain.

### 3.2 The Sensors

The PR 642x series includes five eddy current sensor types in different variants as shown in chapter [Order Matrix](#).

Which sensor type is applicable for a measuring application depends on several requirements as desired measuring range, available measuring track, and maximum environmental temperature.

The characteristics of the measuring chain are adapted to the material mainly used for turbo machinery (reference material: 42 Cr Mo 4, according to SAE 4140). The standard adjustment of the measuring chains is generally related to this material; during installation at the machine, you only need to adjust the distance between the head of the sensor and the measuring target. The signal output of the converter determines how you should adjust the sensor.

## 4 Installation and Mounting

### 4.1 Measuring chain and material of measuring target

To achieve a high accuracy of relative distance measurements, you must adjust the measuring chain precisely on the target material. For this reason, the manufacturer requires information on the material to adjust the converter. For the materials listed in the table in section [Measuring targets](#), it is sufficient to indicate only the material. If you use another material, a sample of the target material with the following dimensions must be sent to the workshop: thickness  $\geq 5$  mm, diameter  $\geq 50$  mm.


If, while ordering, information regarding your material is not available, the measuring chain will be adjusted on the standard material 42 CrMo 4 (SAE 4140).

### 4.2 Choosing the measuring place

[Figure 4-1](#) is an example scheme for how to place the sensors at a turbine shaft to measure the axial displacement, shaft vibration, or speed. You must consider the minimum shaft diameter for this type of sensor, the minimum material width in front of the sensor head, and the minimum gap (refer to [Requirements and hints for the sensor mounting](#)).

To measure shaft vibration, Emerson recommends using a sensor holder between bearing and turbine housing as close as possible to the rotor.

**Figure 4-1: Example scheme where to place the sensors**



## 4.3 Mount the sensor

The following steps describe the mounting of sensor types PR 6422, PR 6423, PR 6424 and PR 6425. For mounting hints regarding the PR 6426 see [PR 6426 installation](#). See also the respective converter manuals as listed in [Table 1-1](#) for further details regarding sensor adjustment.

### Procedure

1. Screw in the sensor into the holder.  
Ensure that the threads are clean and smooth-running.  
Do not bend or twist the sensor cable. If the sensor cable has a LEMO adapter plug open it.  
To avoid touching the shaft during installation, the maximum distance between measuring target and sensor head must be adjusted first - screw in the sensor until the converter output voltage starts changing (approximately at -20V DC). Close the LEMO adapter plug for measuring the converter output voltage.
2. Adjust the distance between measuring target and sensor head in accordance to the measuring task.  
Use a voltmeter connected to the converter output to measure the output voltage. Open the LEMO adapter plug at every two turns of the sensor to untwist the cable. Ensure that in direction to the sensor head at least two of the threads remain free as shown in [Figure 4-2](#).
3. Secure the sensor by fixing the nuts.  
The maximum torque for fixing the nuts is:
  - PR 6422: 1 Nm (0,1 kpm)
  - PR 6423: 15 Nm (1,5 kpm)
  - PR 6424, PR 6425: 98 Nm (10 kpm)

### 4.3.1 Requirements and hints for the sensor mounting

This section contains information and installation requirements for the sensor. The final adjustment of the sensor depends on the measuring task and requires a complete measuring chain. The converter, MMS 3000 and CSI 9360 manuals, and the manuals for the evaluation electronics, contain detailed information regarding the final adjustment.

#### General holder requirement

To mount the sensor, use a stiff and vibration-free holder with a mounting thread for the relevant sensor (PR 6422 to PR6425).

#### General distance adjustment

For distance adjustment the complete measuring chain consisting of sensor and converter is required as the distance will be generally adjusted by means of the converter output voltage.

### Sensor fastening

- Use the enclosed nuts when installing sensors with mounting threads
- When installing sensors with mounting threads captive nuts must be used to avoid loosen of the sensor. Loose parts can fall into the machine and cause damages. A medium grade removable thread locked (for example Loctite® 242, blue) is recommended to secure the sensor.


### Measuring track on the measuring target

The measuring track on the measuring target must be free from irregularities as scratches, corrosion, stress concentrations, metallurgical segregation, high concentricity, etc. These irregularities may cause changes in the sensor output voltage which are not related to a real position or vibration signal. The signal caused by these irregularities is called runout. For the measuring track a surface finish of  $0.41\text{ }\mu\text{m}$  to  $0.76\text{ }\mu\text{m}$  is recommended.

### Free space

Ensure there is  $45^\circ$  of free space around the sensor head for all sensor types except PR 6426, as shown in the left diagram of Figure 4-2. The right drawing in Figure 4-2 shows the required free space around the PR 6426.

**Figure 4-2: Free space around sensor head**



Free space PR 6422, PR 6423, PR 6424 and PR 6425:  $\pm 45^\circ$

Free space PR 6426: minimum = 80 mm; for nominal range  $\pm 4\text{ mm}$  and for extended ranges


### ⚠ CAUTION

If you do not ensure the free space specifications, the measuring range at the upper end reduces and the linearity error increases.

### Maximum axial tilting angle

Ensure that the maximum axial tilting angle  $\alpha$  is  $< 2^\circ$  if using PR 6422, PR 6423, PR 6424 or PR 6425 as shown in Figure 4-3, or  $\alpha < 1.6^\circ$  if using PR 6426 as shown in Figure 4-4. There is no significant influence on the measuring result in this case.


**Figure 4-3: Maximum axial tilting if using PR 6422, PR 6423, PR 6424 or PR 6425**



S: distance between measuring target and sensor head

Alpha: max. axial tilting angle  $< 2^\circ$

**Figure 4-4: Maximum axial tilting if using PR 6426**



S: distance between measuring target and sensor head

Alpha: max. axial tilting angle  $< 1.6^\circ$

### Maximum tangential offset

Ensure the maximum tangential offset matches the values in [Table 4-1](#). [Figure 4-5](#) shows the definition of the tangential offset.


**Table 4-1: Maximum tangential offset**

| Sensor type | Max. offset X | Shaft diameter D |
|-------------|---------------|------------------|
| PR 6422     | 0.2 mm        | $\geq 15$ mm     |

**Table 4-1: Maximum tangential offset (continued)**

| Sensor type | Max. offset X | Shaft diameter D |
|-------------|---------------|------------------|
| PR 6423     | 0.5 mm        | $\geq 28$ mm     |
| PR 6424     | 0.5 mm        | $\geq 60$ mm     |
| PR 6425     | 0.5 mm        | $\geq 60$ mm     |

**Figure 4-5: Maximum tangential offset**



X: max. tangential offset

D: shaft diameter


#### Minimum measuring area

Ensure that the minimum measuring area matches the values in [Table 4-2](#). [Figure 4-6](#) defines of the minimum measuring area.

**Table 4-2: Minimum measuring area**

| Sensor type | X minimum | Sensor head diameter |
|-------------|-----------|----------------------|
| PR 6422     | 5 mm      | 5.2 mm               |
| PR 6423     | 3 mm      | 8 mm                 |
| PR 6424     | 3 mm      | 16 mm                |
| PR 6425     | 2 mm      | 15.8 mm              |
| PR 6426     | 2 mm      | 32 mm                |

**Figure 4-6: Minimum measuring area**




### 4.3.2

## PR 6426 installation

Figure 4-7 shows an installation example for the sensor PR 6426. Its reference area is the mounting plate. The nominal distance of the mounting plate to the measuring target in the center position is approx. 39.5 mm. After you fix the mounting screws, bend the safety plate (anti-twisting plate) to prevent the screws from getting loose.

Figure 4-7: Mounting example PR 6426



## 4.4 Wiring hints

This section contains general information and wiring hints regarding the sensor cable installation. The necessary measures for the proper cable installation depend always on the situation on-site. Observe the following points for a reliable cable installation:

- Do not bend or twist the sensor cables. Cables and connectors must be movable when the sensor is adjusted in its holder.
- Install the cable strain-free and spin-free such that it is protected against mechanical damages.
- Do not shorten the sensor cable or the extension cable of PR 6422 and PR 6423. Rollup the excess cable (rolling diameter  $\geq 100$  mm).
- Ensure that no parts of the cable, including the adapter plug, touch any rotating parts of the machine.
- Note that machines can expand or shrink due to temperature influences. Always install the sensor cable with a cable length reserve to compensate for the thermal behavior of the machine.
- Only install cables with a minimum bending radius of 25 mm. For sensor cables with metal protection tubes, the minimum bending radius is 35 mm.
- Avoid oil stream areas for sensor cableways. Be sure that no oil stream or other agitations will permanently move the cable.
- Avoid sensor cableways where the cable is permanently submerged into oil.
- Affix the sensor cable at recurring short distances.

- Do not bend or twist the sensor cables. Cables and connectors must be movable when the sensor is screwed into the holder.
- Do not squeeze the cable; for example, between metal plates for fixing. Squeezing the cable will damage the outer isolation, which could allow oil into the cable or causes short-circuits.
- Lead the sensor cable through the bearing pedestal wall (machine case), below the horizontal joint of the machine and above the residual oil level in the bearing pedestal. Do not lead the sensor cable through the upper and / or removable pedestal cover. This could cause problems during machine maintenance, and represents a safety concern.
- Place junction boxes on a higher level than the sensor to stop oil from entering the cable protection tubes. You can also use swan-necks for the same purpose.

## 4.5 Sensor cables with LEMO adapter plug

The sensor cables are available with open cable end or with a LEMO connector. Some sensor types have a LEMO adapter plug after the first meter of the sensor cable. The following hints apply, regardless of the size of the LEMO connector.


- To connect, push the LEMO plug into an according socket or counterpart. The LEMO connector locks with an audible click.
- To unlock the connector, pull it out of the socket.

### Note

The LEMO connector as well as the LEMO adaptor plug are pluggable connectors. Do not turn the connectors for opening.


Figure 4-8 is a label that is attached to the sensor cable. It illustrates how to properly disconnect the LEMO connectors.

Figure 4-8: Label: Use of LEMO plug



Cover the LEMO adapter plug with the shrink sleeve included into the delivery. The shrinking temperature of the shrink sleeve with an approximately length of 100 mm is approximately 200°C. Applying a shrink sleeve to the LEMO connector isolates and protects the connection and is always required - even when using metal protection tubes. Figure 4-9 shows the shrink sleeve.

**Figure 4-9: Measurement specifications for applying shrink sleeve**



A: Shrink sleeve

B: Adapter plug

C: Sensor cable

#### **Apply shrink sleeve to a connector**

1. At the open adapter connection, push the shrink sleeve over one connector so that the sleeve completely covers the sensor cable.
2. Close the LEMO connection.
3. Move the shrink sleeve over the closed connection. The LEMO adapter plug should be completely covered by the shrink sleeve. The shrink sleeve should evenly overlap the adapter plug.
4. Use a hot air gun to evenly shrink the sleeve. The required shrinking temperature is approximately 200°C.
5. Ensure that the shrank sleeve touches sensor cable and adapter plug. It is important that the shrink sleeve cannot slip form the adapter plug.

## 5 Technical data

Only specifications with tolerances are guaranteed. Data without tolerance or without error limits are informative data and not guaranteed.

All specifications are valid for a measuring chain consisting of a sensor PR 6422, PR 6423, PR 6424, PR 6425 or PR 6426 and one of the following converters CON 011, 021, 031 or 041 respectively an integrated converter in a MMS 3000 transmitter adjusted on it.

### Related information

[Owner's responsibility](#)

### 5.1 Measuring targets

| Measuring target                                 | shafts and plain surfaces       |         |                   |         |
|--------------------------------------------------|---------------------------------|---------|-------------------|---------|
| Sensor                                           | PR 6422                         | PR 6423 | PR 6424 / PR 6425 | PR 6426 |
| Shaft diameter                                   | >20 mm                          | >40 mm  | >80 mm            | ---     |
| Height of target (measuring collar) on the shaft | >20 mm                          | >25 mm  | >40 mm            | >80 mm* |
| Speed of shaft circumference                     | 0 ... 2500 m/s                  |         |                   |         |
| Object material                                  | electrical conducting materials |         |                   |         |
| Reference material                               | 1.7224 (42 Cr Mo 4; SAE 4140)   |         |                   |         |

\* may be less for special installation of the PR 6426

| Upon request, measuring chains can be adjusted on the following materials. | Material | Description  | Material | Description   |
|----------------------------------------------------------------------------|----------|--------------|----------|---------------|
|                                                                            | 1.7733   | 24 CrMo V5 5 | 1.7220   | 34 CrMo 4     |
|                                                                            | 1.0060   | St 60-2      | 1.7258   | 24 CrMo 5     |
|                                                                            | 1.0501   | C 35         | 1.1181   | CK 35         |
|                                                                            | 1.1191   | CK 45        | 1.8519   | 31 CrMo V9    |
|                                                                            | 1.4021   | X 20 Cr 13   | 1.4057   | X 22 CrNi 17  |
|                                                                            | 1.4122   | X 35 CrMo 17 | 1.4922   | X 20 CrMo V12 |
|                                                                            | 1.6582   | 34 NiCrMo 6  | 1.7218   | 25 CrMo 4     |

Adjustments on brass, copper or other electric conducting materials are possible – in this case differences of the specifications will apply, refer to section [Measuring chain and material of measuring target](#).

## 5.2 Measuring ranges and sensitivity

| Sensor                                                                                  | PR 6422                  | PR 6423                | PR 6424                  | PR 6425                | PR 6426                |
|-----------------------------------------------------------------------------------------|--------------------------|------------------------|--------------------------|------------------------|------------------------|
| Nominal measuring range, static measurements                                            | ±0,5 mm                  | ±1,0 mm                | ±2,0 mm                  | ±2,0 mm                | ±4,0 mm                |
| Nominal measuring range, dynamic, peak – peak (recommended)                             | 25 ... 250 µm            | 50 ... 500 µm          | 100 ... 1000 µm          | 100 ... 1000 ±m        | ---                    |
| Sensitivity for 42 Cr Mo 4                                                              | 16 V/mm                  | 8 V/mm                 | 4 V/mm                   | 4 V/mm                 | 2 V/mm                 |
| Approximate value for nominal distance at the center point of converter output signal * | approx. 0,8 mm           | approx. 1,5 mm         | approx. 2,7 mm           | approx. 2,6 mm         | approx. 5,5 mm         |
| Basic air gap *                                                                         | approx. 0,15 ... 0,35 mm | approx. 0,4 ... 0,7 mm | approx. 0,55 ... 0,95 mm | approx. 0,5 ... 1,0 mm | approx. 1,2 ... 1,8 mm |

\* With standard measuring ranges (not valid for use of extended measuring ranges)

The sensor PR 6423 corresponds to the API 670 / DIN 45670 standard.

Calibration: If no other material was stated, sensor and converter are adjusted on the standard material (42 Cr Mo 4), refer to section [Measuring chain and material of measuring target](#).

## 5.3 Environmental conditions and mechanical design

| Environmental temperature                                     |                                                                                                                                                                                           |
|---------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Reference value                                               | +23°C                                                                                                                                                                                     |
| Nominal operating range PR 6422 and PR6423                    | -35°C ... +180°C (short time , up to +200°C)                                                                                                                                              |
| Nominal operating range PR 6424                               | -35°C ... +120°C                                                                                                                                                                          |
| Nominal operating range PR 6426                               | -35°C ... +150°C                                                                                                                                                                          |
| PR 6425 only sensor and first part of the cable               | <ul style="list-style-type: none"> <li>nominal operating range: permanent 0 ... +380°C</li> <li>limit range: short time 0 ... +400°C (max. 4 hours, without vibration)</li> </ul>         |
| Nominal range for cable in protection hose and connector      | permanent 0 ...+175°C<br>short time up to +200°C                                                                                                                                          |
| Limits for storage and transport                              | -40°C ... +70°C                                                                                                                                                                           |
| Temperature error (according to API 670, only sensor)         | PR 6423, PR6424: 4 % per 100 K<br>PR 6425: 4 % per 100 K                                                                                                                                  |
| Resistance to chemicals (at room temperature)                 | Sensor and cable are resistant to: water, steam, natural gas, helium, bearing oils, gasoline, benzol, nitric acid, tetracarbonchloride, tetrachlorideethylen                              |
| Pressure                                                      |                                                                                                                                                                                           |
| Pressure resistance to sensor head                            | PR 6422, PR 6423, PR 6424: 10000 hPa<br>PR 6425: 2000 hPa                                                                                                                                 |
| Pressure and differential pressure resistance at cable outlet | On request                                                                                                                                                                                |
| Vibration                                                     |                                                                                                                                                                                           |
| max. Vibration                                                | 5g at 60 Hz                                                                                                                                                                               |
| Mechanical design                                             |                                                                                                                                                                                           |
| Dimensions                                                    | see <a href="#">Figure 6-1</a> to <a href="#">Figure 6-5</a>                                                                                                                              |
| Sensor and extension cable                                    | up to 200°C temperature resistant, PTFE cable resistant to oil and chemicals; connection of sensor cable and extension cable with coax connector.                                         |
| Connection to converter                                       | self arresting and water proof connector for CON 011, CON 021, respective devices of the AMS 3000 system and AMS 9360 or stripped cable ends with crimped sleeves for CON 031 and CON 041 |

|                                         |                                                                                                                                                                                |
|-----------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| PR 6425                                 | High temperature resistant cable at the head (up to 380°C) in a gas-proof metal protection hose, directly connected with PTFE - cable in a not gas-proof metal protection tube |
| Metal protection tube (PR 642x/x1x-xxx) | stainless steel, not gas-proof                                                                                                                                                 |

**Table 5-1: Additional error**

| Sensor type | Temperature range  | Zero point        | Sensitivity       |
|-------------|--------------------|-------------------|-------------------|
| PR 6425     | at +300 ... +380°C | ---               | 0.8% per 10 K     |
| PR 6426     | at +23 ...+100°C   | ≤ -0,3 % per 10 K | ≤ 0,15 % per 10 K |
|             | at +100 ...+175°C  | ≤ -0,6 % per 10 K | ≤ 0,65 % per 10 K |
|             | at -35 ... +23°C   | ≤ -0,2 % per 10 K | ≤ 0,20 % per 10 K |

### Related information

[Storage and transport](#)

## 6 Drawings

Figure 6-1: Dimensions standard types PR 6422





Figure 6-2: Dimensions standard types PR 6423



Technical drawing of cable assembly PR 6424/000-100. The drawing shows two views: a side view and a front view.

**Side View:**


- Thread:** PR 6424/000-100 M 18 x 1,5
- Cap material:** Epoxy resin
- Nut size 27**
- Size 15**
- Cable min. bedding rad. 25 mm**
- Shrink sleeve (clear) for identification**
- Lemo plug**
- Dimensions:** 30, 34, 50, 100, 4 m (Cable length)

**Front View:**

- Thread:** M 18 x 1,5
- Cap material:** Epoxy resin
- Nut size 27**
- Size 15**
- Cable min. bedding rad. 35 mm**
- Shrink sleeve (clear) for identification**
- Metal protection DN 4 stainless steel**
- Lemo plug**
- Dimensions:** 30, 34, 50, 100, 4 m (Cable length)

**PR 6424/000-100**

Figure 6-4: Dimensions standard type PR 6425



Technical drawings of two cable assemblies, PR 6425/000-100 and PR 6425/010-100.

**PR 6425/000-100:**

- Side View:** Shows a cable with a minimum bedding radius of 25 mm and a length of 4 m. The cable is terminated with a Lemo plug. A shrink sleeve (clear) for identification is shown.
- Cross-section:** Shows the cable's internal structure. Dimensions include:
  - Overall width: 40 mm
  - Top flange: 3 mm
  - Inner hole diameter: 9 mm
  - Inner diameter: 29 mm
  - Outer diameter: 29 mm
  - Inner hole diameter: 8 mm
  - Inner hole diameter: 3.5 mm
  - Outer hole diameter: 20 mm
  - Total height: 34 mm
- Mounting parts as accessories:**
  - 2 x washers 8.4 mm DIN 463
  - 2 x screws M8x20 DIN 933 A2 80
- Labels:** Type No. and series No., Cable length 4 m, Cable min. bedding rad. 25 mm, Shrink sleeve (clear) for identification, Lemo plug, PR 6425/000-100.

**PR 6425/010-100:**

- Side View:** Shows a cable with a minimum bedding radius of 35 mm and a length of 4 m. The cable is terminated with a Lemo plug. A shrink sleeve (clear) for identification is shown.
- Cross-section:** Shows the cable's internal structure. Dimensions include:
  - Overall width: 40 mm
  - Top flange: 3 mm
  - Inner hole diameter: 9 mm
  - Inner diameter: 29 mm
  - Outer diameter: 29 mm
  - Inner hole diameter: 8 mm
  - Inner hole diameter: 3.5 mm
  - Outer hole diameter: 20 mm
  - Total height: 34 mm
- Mounting parts as accessories:**
  - 2 x washers 8.4 mm DIN 463
  - 2 x screws M8x20 DIN 933 A2 80
- Labels:** Type No. and series No., Cable length 4 m, Cable min. bedding rad. 35 mm, Shrink sleeve (clear) for identification, Lemo plug, PR 6425/010-100.

## 7 Order Matrix

Different sensor versions of the PR642x can be set up by means of the following order matrix.

**Table 7-1: PR 6422/xxx-xxx**

| Order Matrix                       | PR 6422/                                                                                      | X      | X      | X | - | X      | X | X           |
|------------------------------------|-----------------------------------------------------------------------------------------------|--------|--------|---|---|--------|---|-------------|
| Sleeve Thread                      | M6x0.5<br>¼-28UNF-2A                                                                          | 0<br>1 |        |   |   |        |   |             |
| Armored Cable                      | WITH<br>WITHOUT                                                                               |        | 1<br>0 |   |   |        |   |             |
| Total Sensor Length<br>C=Cx+5.3 mm | 0(Cx=25 mm), 1(30 mm), 2(40 mm),<br>3(50 mm), 5(70 mm), 6(80 mm),<br>7(90 mm), 8(100 mm)<br>1 |        |        | X |   |        |   |             |
| Adapter Plug                       | WITH<br>WITHOUT                                                                               |        |        |   |   | 0<br>1 |   |             |
| Total Cable Length                 | 0(4 m), 1(5 m), F(9 m), 4(10 m)                                                               |        |        |   |   |        | X |             |
| Cable End                          | LEMO<br>OPEN<br>A9360 CONNECTION                                                              |        |        |   |   |        |   | 0<br>1<br>2 |

1 Maximum length with armored cable is 70 mm.

**Table 7-2: PR 6422/xxx-xxx – Special versions**

| Version             | Description                                                                                        |
|---------------------|----------------------------------------------------------------------------------------------------|
| PR 6422/xAx-xxx     | Sensor cable with armor and extension cable without armor, available for sensors with adapter plug |
| PR 6422/xxZ-xxx     | 15 mm case length                                                                                  |
| PR 6422/xxx-x2x     | 6 m cable length                                                                                   |
| PR 6422/xxx-x5x     | 15 m cable length                                                                                  |
| PR 6422/xxx-xDx     | 2.5 m sensor cable plus 2.5 m extension cable                                                      |
| PR 6422/xxx-xxx-RAD | Radiation resistant                                                                                |
| PR 6422/xxx-xxx-SA  | Special sleeve                                                                                     |
| PR 6422/xxx-xxx-SA1 | Special sleeve                                                                                     |
| PR 6422/xxx-xxx-SA2 | Additional shrink sleeve, first 1.5 m of sensor cable                                              |

**Table 7-3: PR 6423/xxx-xxx**

| Order Matrix                     | PR 6423/                                                                                                                                                    | X      | X      | X | - | X      | X | X           |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|--------|---|---|--------|---|-------------|
| Sleeve Thread                    | M10x1<br>3/8-24UNF-2A                                                                                                                                       | 0<br>1 |        |   |   |        |   |             |
| Armored Cable                    | WITH<br>WITHOUT                                                                                                                                             |        | 1<br>0 |   |   |        |   |             |
| Total Sensor Length<br>C=Cx+9 mm | 0(Cx=25 mm), 1(35 mm), 2(45 mm),<br>3(55 mm), 4(65 mm), 5(75 mm),<br>6(85 mm), 7(95 mm), 8(105 mm),<br>9(115 mm), E(155 mm), H(195 mm),<br>R(Reverse Mount) |        |        | X |   |        |   |             |
| Adapter Plug                     | WITH<br>WITHOUT                                                                                                                                             |        |        |   |   | 0<br>1 |   |             |
| Total Cable Length               | 0(4 m), 1(5 m), F(9 m), 4(10 m)                                                                                                                             |        |        |   |   |        | X |             |
| Cable End                        | LEMO<br>OPEN<br>A9360 CONNECTION                                                                                                                            |        |        |   |   |        |   | 0<br>1<br>2 |

**Table 7-4: PR 6423/xxx-xxx – Special versions**

| Version             | Description               |
|---------------------|---------------------------|
| PR 6423/xxS-xxx     | 245 mm sensor length      |
| PR 6423/xxx-x3x     | 8 m cable length          |
| PR 6423/xxx-xDx     | 30 m cable length         |
| PR 6423/xxx-xxx-AS  | Additional sealing        |
| PR 6423/xxx-xxx-HT  | High temperature          |
| PR 6423/xxx-xxx-RAD | Radiation resistance      |
| PR 6423/xxx-xxx-S1  | 65 mm unthreaded length   |
| PR 6423/xxx-xxx-S2  | 140 mm unthreaded length  |
| PR 6423/xxx-xxx-S5  | 62 mm unthreaded length   |
| PR 6423/xxx-xxx-S10 | 170 mm unthreaded length  |
| PR 6423/xxx-xxx-SA1 | Special adaptation sleeve |

**Table 7-5: PR 6424/xxx-xxx**

| Order Matrix  | PR 6424/        | X | X      | X | - | X | X | X |
|---------------|-----------------|---|--------|---|---|---|---|---|
| Sleeve Thread | M18x1.5         | 0 |        |   |   |   |   |   |
| Armored Cable | WITH<br>WITHOUT |   | 1<br>0 |   |   |   |   |   |

**Table 7-5: PR 6424/xxx-xxx (continued)**

| Order Matrix                        | PR 6424/                                                                                                                      | X | X | X | - | X      | X | X      |
|-------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|---|---|---|---|--------|---|--------|
| Total Sensor Length<br>C=Cx+12.5 mm | 0(Cx=40 mm), 1(50 mm), 2(60 mm),<br>3(70 mm), 4(80 mm), 5(90 mm),<br>6(100 mm), 8(150 mm), G(200 mm),<br>M(250 mm), R(290 mm) |   |   | X |   |        |   |        |
| Adapter Plug                        | WITH<br>WITHOUT                                                                                                               |   |   |   |   | 0<br>1 |   |        |
| Total Cable Length                  | 0(4 m), 1(5 m), 4(10 m)                                                                                                       |   |   |   |   |        | X |        |
| Cable End                           | LEMO<br>OPEN                                                                                                                  |   |   |   |   |        |   | 0<br>1 |

**Table 7-6: PR 6424/xxx-xxx – Special versions**

| Version         | Description      |
|-----------------|------------------|
| PR 6424/xxx-x3x | 8 m cable length |

**Table 7-7: PR 6425/xxx-xxx**

| Order Matrix        | PR 6425/                        | X | X | X | - | X | X | X      |
|---------------------|---------------------------------|---|---|---|---|---|---|--------|
| Sleeve Thread       | M18x1.5                         | 0 |   |   |   |   |   |        |
| Armored Cable       | WITH                            |   | 1 |   |   |   |   |        |
| Total Sensor Length | 0(69 mm)                        |   |   | 0 |   |   |   |        |
| Adapter Plug        | WITHOUT                         |   |   |   |   | 1 |   |        |
| Total Cable Length  | 0(4 m), 1(5 m), 3(8 m), 4(10 m) |   |   |   |   |   | X |        |
| Cable End           | LEMO<br>OPEN                    |   |   |   |   |   |   | 0<br>1 |

**Table 7-8: PR 6426/xxx-xxx**

| Order Matrix        | PR 6426/                                | X | X      | X | - | X      | X | X      |
|---------------------|-----------------------------------------|---|--------|---|---|--------|---|--------|
| Sleeve Thread       | NO THREAD                               | 0 |        |   |   |        |   |        |
| Armored Cable       | WITH<br>WITHOUT                         |   | 1<br>0 |   |   |        |   |        |
| Total Sensor Length | Mounting Plate 80 mm x 40 mm            |   |        | 0 |   |        |   |        |
| Adapter Plug        | WITH<br>WITHOUT                         |   |        |   |   | 0<br>1 |   |        |
| Total Cable Length  | 0(4 m), 1(5 m), 2(6 m), 3(8 m), 4(10 m) |   |        |   |   |        | X |        |
| Cable End           | LEMO<br>OPEN                            |   |        |   |   |        |   | 0<br>1 |

**Table 7-9: PR 6426/xxx-xxx – Special versions**

| Version            | Description        |
|--------------------|--------------------|
| PR 6426/xxx-x2x    | 6 m cable length   |
| PR 6426/xxx-x3x    | 8 m cable length   |
| PR 6426/xxx-xxx-AS | Additional sealing |

## 8 Certificates



### EU-Declaration of Conformity (Translation)

**We: epro GmbH, Jöbkesweg 3, 48599 Gronau**  
**declare under our sole responsibility that following product(s):**

**Part numbers:** CON011, CON011 / 91(2-6) - (015-240)  
CON021, CON021 / 91(2-6) - (015-240)  
CON031, CON031 / 91(2-6) - (015-240)  
CON041, CON041 / 91(2-6) - (015-240)  
**with**  
PR 6422 / (0-1) (0-1) (0-8) – (0-1) (0-4, F) (0-2)  
PR 6423 / (0-1) (0-1) (0-9, E, H, S) – (0-1) (0-4, F) (0-2)  
PR 6423 / (0-1) (0-1) (0-9, E, H, S) – (0-1) (0-4, F) (0-2)-HT  
PR 6424 / (0-1) (0-1) (0-6, B, G, M, R) – (0-1) (0-4) (0-1)  
PR 6425 / 0 1 0 – 1 (0-4) (0-1)  
PR 6426 / 0 (0-1) 0 – (0-1) (0-4) (0-1)

**Product description:** Signal converter for eddy current measuring chains with sensors PR642x

**are in conformity with the terms of the directives mentioned below including any amendment valid at the date of declaration:**

|                          |                                                                                                   |
|--------------------------|---------------------------------------------------------------------------------------------------|
| 2014/30/EU               | Electromagnetic compatibility                                                                     |
| 2014/34/EU <sup>1)</sup> | Equipment and protective system intended for use in potentially explosive atmospheres             |
| 2011/65/EU               | The restriction of the use of certain hazardous substances in electrical and electronic equipment |

**Following harmonized standards have been applied:**

|                          |             |                                                                                                                                          |
|--------------------------|-------------|------------------------------------------------------------------------------------------------------------------------------------------|
| 2014/30/EU               | EN 61326-1  | Electrical equipment for measurement, control and laboratory use. EMC requirements.                                                      |
|                          |             | Part 1. General requirements                                                                                                             |
| 2014/34/EU <sup>1)</sup> | EN 60079-0  | Explosive atmospheres -                                                                                                                  |
|                          |             | Part 0: Equipment - General requirements                                                                                                 |
|                          | EN 60079-11 | Explosive atmospheres -                                                                                                                  |
|                          |             | Part 11: Equipment protection by intrinsic safety "i"                                                                                    |
|                          | EN 60079-26 | Explosive atmospheres -                                                                                                                  |
|                          |             | Part 26: Equipment with Equipment Protection Level (EPL) Ga                                                                              |
| 2011/65/EU               | EN 63000    | Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances |

**For the type examination according to EN 60079-0, EN 60079-11 and EN 60079-26 the following notified body has been involved;**

PTB Braunschweig  
Type examination certificate PTB 03 ATEX 2151

**Authorized person for technical documentation:**

Bruno Hecker, Jöbkesweg 3, 48599 Gronau

Gronau, 19 December, 2024  
Place, Date

Managing Director

Quality



**EU-Declaration of Conformity (Translation)**



**We: epro GmbH, Jöbkesweg 3, 48599 Gronau**  
**declare under our sole responsibility that following product(s):**

**Part numbers:** CON011/SF, CON011 / 91(2-4) - (015-080)/SF  
CON041/SF, CON041 / 91(2-4) - (015-080)/SF  
**with**  
PR 6422 / (0-1) (0-1) (0-8) – (0-1) (0-4, F) (0-2)  
PR 6423 / (0-1) (0-1) (0-9, E, H, S) – (0-1) (0-4, F) (0-2)  
PR 6424 / (0-1) (0-1) (0-6, B, G, M, R) – (0-1) (0-4) (0-1)

**Product description:** Signal converter for eddy current measuring chains with sensors PR642x

**are in conformity with the terms of the directives mentioned below including any amendment valid at the date of declaration:**

|            |                                                                                                   |
|------------|---------------------------------------------------------------------------------------------------|
| 2014/30/EU | Electromagnetic compatibility                                                                     |
| 2014/34/EU | Equipment and protective system intended for use in potentially explosive atmospheres             |
| 2011/65/EU | The restriction of the use of certain hazardous substances in electrical and electronic equipment |
| 2006/42/EC | Machinery Directive                                                                               |

**Following harmonized standards have been applied:**

|            |              |                                                                                                                                          |
|------------|--------------|------------------------------------------------------------------------------------------------------------------------------------------|
| 2014/30/EU | EN 61326-1   | Electrical equipment for measurement, control and laboratory use. EMC requirements.                                                      |
|            |              | Part 1: General requirements                                                                                                             |
| 2014/34/EU | EN 60079-0   | Explosive atmospheres -                                                                                                                  |
|            |              | Part 0: Equipment - General requirements                                                                                                 |
|            | EN 60079-11  | Explosive atmospheres -                                                                                                                  |
|            |              | Part 11: Equipment protection by intrinsic safety "i"                                                                                    |
|            | EN 60079-26  | Explosive atmospheres -                                                                                                                  |
|            |              | Part 26: Equipment with Equipment Protection Level (EPL) Ga                                                                              |
| 2011/65/EU | EN 63000     | Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances |
| 2006/42/EC | DIN EN 62061 | Safety of machinery -                                                                                                                    |
|            |              | Functional safety of safety-related electrical, electronic and programmable electronic control systems                                   |

**For the type examination according to EN 60079-0, EN 60079-11 and EN 60079-26 the following notified body has been involved;**

PTB Braunschweig  
Type examination certificate PTB 03 ATEX 2151

**Authorized person for technical documentation:**

Bruno Hecker, Jöbkesweg 3, 48599 Gronau

Gronau, 19 December 2024  
**Place, Date**

  
**Managing Director**

  
**Quality**



Emerson Process Management  
1100 W. Louis Henna Blvd.  
Round Rock, TX 78681

**Statement Regarding the China RoHS Compliance of Emerson Product - PR6422/xxx-xxx**

Please refer to Table 1 for the names and contents of the toxic or hazardous substances or elements contained in Emerson products.

**Table 1: Names and Contents of Toxic or Hazardous Substances or Elements**

表1：有毒有害物质或元素的名称及含量

| 部件名称<br>Part Name                                                                                                                                                                                                                                                                                   | 有毒有害物质或元素<br>Toxic or hazardous Substances and Elements |                      |                      |                                         |                                           |                                                   |    |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------|----------------------|----------------------|-----------------------------------------|-------------------------------------------|---------------------------------------------------|----|
|                                                                                                                                                                                                                                                                                                     | 铅<br>Lead<br>(Pb)                                       | 汞<br>Mercury<br>(Hg) | 镉<br>Cadmium<br>(Cd) | 六价铬<br>Hexavalent Chromium<br>(Cr (VI)) | 多溴联苯<br>Polybrominated biphenyls<br>(PBB) | 多溴二苯醚<br>Polybrominated diphenyl ethers<br>(PBDE) |    |
| 传感器<br>SENSOR                                                                                                                                                                                                                                                                                       | X                                                       | O                    | O                    | O                                       | O                                         | O                                                 | 25 |
|                                                                                                                                                                                                                                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
|                                                                                                                                                                                                                                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
|                                                                                                                                                                                                                                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
| O 表示该有毒有害物质在该部件所有均质材料中的含量均在GB/T 26572规定的限量要求以下<br>O: Indicates that this toxic or hazardous substance contained in all of the homogeneous materials for this part is below the limit requirement in GB/T 26572.                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
| X 表示该有毒有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572规定的限量要求。<br>X: Indicates that this toxic or hazardous substance contained in at least one of the homogeneous materials used for this part is above the limit requirement in GB/T 26572                                                                      |                                                         |                      |                      |                                         |                                           |                                                   |    |
| 环保期限（EFUP）的产品及其部件是每个列出的符号，除非另有标明，使用期限只适用于产品在产品手册中规定的条件下工作<br>The Environmentally Friendly Period (EFUP) for the product and its parts are per the symbol listed, unless otherwise marked. Use Period is valid only when the product is operated under the conditions defined in the product manual. |                                                         |                      |                      |                                         |                                           |                                                   |    |

James McFerrin  
Environmental Compliance Manager PSG  
T 512 832 3271 E james.mcferrin@emerson.com



Emerson Process Management  
1100 W. Louis Henna Blvd.  
Round Rock, TX 78681

Statement Regarding the China RoHS Compliance of Emerson Product - PR6423/xxx-xxx

Please refer to Table 1 for the names and contents of the toxic or hazardous substances or elements contained in Emerson products.

Table 1: Names and Contents of Toxic or Hazardous Substances or Elements

表1：有毒有害物质或元素的名称及含量

| 部件名称<br>Part Name                                                                                                                                                                                                                                                                                   |                   | 有毒有害物质或元素<br>Toxic or hazardous Substances and Elements |                      |                                         |                                           |                                                   |    |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|---------------------------------------------------------|----------------------|-----------------------------------------|-------------------------------------------|---------------------------------------------------|----|
|                                                                                                                                                                                                                                                                                                     | 铅<br>Lead<br>(Pb) | 汞<br>Mercury<br>(Hg)                                    | 镉<br>Cadmium<br>(Cd) | 六价铬<br>Hexavalent Chromium<br>(Cr (VI)) | 多溴联苯<br>Polybrominated biphenyls<br>(PBB) | 多溴二苯醚<br>Polybrominated diphenyl ethers<br>(PBDE) |    |
| 传感器<br>SENSOR                                                                                                                                                                                                                                                                                       | X                 | O                                                       | O                    | O                                       | O                                         | O                                                 | 25 |
|                                                                                                                                                                                                                                                                                                     |                   |                                                         |                      |                                         |                                           |                                                   |    |
|                                                                                                                                                                                                                                                                                                     |                   |                                                         |                      |                                         |                                           |                                                   |    |
|                                                                                                                                                                                                                                                                                                     |                   |                                                         |                      |                                         |                                           |                                                   |    |
| O 表示该有毒有害物质在该部件所有均质材料中的含量均在GB/T 26572规定的限量要求以下<br>O: Indicates that this toxic or hazardous substance contained in all of the homogeneous materials for this part is below the limit requirement in GB/T 26572.                                                                                     |                   |                                                         |                      |                                         |                                           |                                                   |    |
| X 表示该有毒有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572规定的限量要求。<br>X: Indicates that this toxic or hazardous substance contained in at least one of the homogeneous materials used for this part is above the limit requirement in GB/T 26572                                                                      |                   |                                                         |                      |                                         |                                           |                                                   |    |
| 环保期限（EFUP）的产品及其部件是每个列出的符号，除非另有标明，使用期限只适用于产品在产品手册中规定的条件下工作<br>The Environmentally Friendly Period (EFUP) for the product and its parts are per the symbol listed, unless otherwise marked. Use Period is valid only when the product is operated under the conditions defined in the product manual. |                   |                                                         |                      |                                         |                                           |                                                   |    |

James McFerrin  
Environmental Compliance Manager PSG  
T 512 832 3271 E james.mcferrin@emerson.com



Emerson Process Management  
1100 W. Louis Henna Blvd.  
Round Rock, TX 78681

**Statement Regarding the China RoHS Compliance of Emerson Product - PR6424/xxx-xxx**

Please refer to Table 1 for the names and contents of the toxic or hazardous substances or elements contained in Emerson products.

**Table 1: Names and Contents of Toxic or Hazardous Substances or Elements**

表1：有毒有害物质或元素的名称及含量

| 部件名称<br>Part Name                                                                                                                                                                                                                                                                                   | 有毒有害物质或元素<br>Toxic or hazardous Substances and Elements |                      |                      |                                         |                                           |                                                   |    |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------|----------------------|----------------------|-----------------------------------------|-------------------------------------------|---------------------------------------------------|----|
|                                                                                                                                                                                                                                                                                                     | 铅<br>Lead<br>(Pb)                                       | 汞<br>Mercury<br>(Hg) | 镉<br>Cadmium<br>(Cd) | 六价铬<br>Hexavalent Chromium<br>(Cr (VI)) | 多溴联苯<br>Polybrominated biphenyls<br>(PBB) | 多溴二苯醚<br>Polybrominated diphenyl ethers<br>(PBDE) |    |
| 传感器<br>SENSOR                                                                                                                                                                                                                                                                                       | X                                                       | O                    | O                    | O                                       | O                                         | O                                                 | 25 |
|                                                                                                                                                                                                                                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
|                                                                                                                                                                                                                                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
|                                                                                                                                                                                                                                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
| O 表示该有毒有害物质在该部件所有均质材料中的含量均在GB/T 26572规定的限量要求以下<br>O: Indicates that this toxic or hazardous substance contained in all of the homogeneous materials for this part is below the limit requirement in GB/T 26572.                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
| X 表示该有毒有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572规定的限量要求。<br>X: Indicates that this toxic or hazardous substance contained in at least one of the homogeneous materials used for this part is above the limit requirement in GB/T 26572                                                                      |                                                         |                      |                      |                                         |                                           |                                                   |    |
| 环保期限（EFUP）的产品及其部件是每个列出的符号，除非另有标明，使用期限只适用于产品在产品手册中规定的条件下工作<br>The Environmentally Friendly Period (EFUP) for the product and its parts are per the symbol listed, unless otherwise marked. Use Period is valid only when the product is operated under the conditions defined in the product manual. |                                                         |                      |                      |                                         |                                           |                                                   |    |

James McFerrin  
Environmental Compliance Manager PSG  
T 512 832 3271 E james.mcferrin@emerson.com



Emerson Process Management  
1100 W. Louis Henna Blvd.  
Round Rock, TX 78681

Statement Regarding the China RoHS Compliance of Emerson Product - PR6425/xxx-xxx

Please refer to Table 1 for the names and contents of the toxic or hazardous substances or elements contained in Emerson products.

Table 1: Names and Contents of Toxic or Hazardous Substances or Elements

表1：有毒有害物质或元素的名称及含量

| 部件名称<br>Part Name                                                                                                                                                                                                                                                                                   | 有毒有害物质或元素<br>Toxic or hazardous Substances and Elements |                      |                      |                                         |                                           |                                                   |    |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------|----------------------|----------------------|-----------------------------------------|-------------------------------------------|---------------------------------------------------|----|
|                                                                                                                                                                                                                                                                                                     | 铅<br>Lead<br>(Pb)                                       | 汞<br>Mercury<br>(Hg) | 镉<br>Cadmium<br>(Cd) | 六价铬<br>Hexavalent Chromium<br>(Cr (VI)) | 多溴联苯<br>Polybrominated biphenyls<br>(PBB) | 多溴二苯醚<br>Polybrominated diphenyl ethers<br>(PBDE) |    |
| 传感器<br>SENSOR                                                                                                                                                                                                                                                                                       | X                                                       | O                    | O                    | O                                       | O                                         | O                                                 | 25 |
|                                                                                                                                                                                                                                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
|                                                                                                                                                                                                                                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
|                                                                                                                                                                                                                                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
| O 表示该有毒有害物质在该部件所有均质材料中的含量均在GB/T 26572规定的限量要求以下<br>O: Indicates that this toxic or hazardous substance contained in all of the homogeneous materials for this part is below the limit requirement in GB/T 26572.                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
| X 表示该有毒有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572规定的限量要求。<br>X: Indicates that this toxic or hazardous substance contained in at least one of the homogeneous materials used for this part is above the limit requirement in GB/T 26572                                                                      |                                                         |                      |                      |                                         |                                           |                                                   |    |
| 环保期限（EFUP）的产品及其部件是每个列出的符号，除非另有标明，使用期限只适用于产品在产品手册中规定的条件下工作<br>The Environmentally Friendly Period (EFUP) for the product and its parts are per the symbol listed, unless otherwise marked. Use Period is valid only when the product is operated under the conditions defined in the product manual. |                                                         |                      |                      |                                         |                                           |                                                   |    |

James McFerrin  
Environmental Compliance Manager PSG  
T 512 832 3271 E james.mcferrin@emerson.com



Emerson Process Management  
1100 W. Louis Henna Blvd.  
Round Rock, TX 78681

**Statement Regarding the China RoHS Compliance of Emerson Product - PR6426/xxx-xxx**

Please refer to Table 1 for the names and contents of the toxic or hazardous substances or elements contained in Emerson products.

**Table 1: Names and Contents of Toxic or Hazardous Substances or Elements**

表1：有毒有害物质或元素的名称及含量

| 部件名称<br>Part Name                                                                                                                                                                                                                                                                                   | 有毒有害物质或元素<br>Toxic or hazardous Substances and Elements |                      |                      |                                         |                                           |                                                   |    |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------|----------------------|----------------------|-----------------------------------------|-------------------------------------------|---------------------------------------------------|----|
|                                                                                                                                                                                                                                                                                                     | 铅<br>Lead<br>(Pb)                                       | 汞<br>Mercury<br>(Hg) | 镉<br>Cadmium<br>(Cd) | 六价铬<br>Hexavalent Chromium<br>(Cr (VI)) | 多溴联苯<br>Polybrominated biphenyls<br>(PBB) | 多溴二苯醚<br>Polybrominated diphenyl ethers<br>(PBDE) |    |
| 传感器<br>SENSOR                                                                                                                                                                                                                                                                                       | X                                                       | O                    | O                    | O                                       | O                                         | O                                                 | 25 |
|                                                                                                                                                                                                                                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
|                                                                                                                                                                                                                                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
|                                                                                                                                                                                                                                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
| O 表示该有毒有害物质在该部件所有均质材料中的含量均在GB/T 26572规定的限量要求以下<br>O: Indicates that this toxic or hazardous substance contained in all of the homogeneous materials for this part is below the limit requirement in GB/T 26572.                                                                                     |                                                         |                      |                      |                                         |                                           |                                                   |    |
| X 表示该有毒有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572规定的限量要求。<br>X: Indicates that this toxic or hazardous substance contained in at least one of the homogeneous materials used for this part is above the limit requirement in GB/T 26572                                                                      |                                                         |                      |                      |                                         |                                           |                                                   |    |
| 环保期限（EFUP）的产品及其部件是每个列出的符号，除非另有标明，使用期限只适用于产品在产品手册中规定的条件下工作<br>The Environmentally Friendly Period (EFUP) for the product and its parts are per the symbol listed, unless otherwise marked. Use Period is valid only when the product is operated under the conditions defined in the product manual. |                                                         |                      |                      |                                         |                                           |                                                   |    |

James McFerrin  
Environmental Compliance Manager PSG  
T 512 832 3271 E james.mcferrin@emerson.com



**Emerson**  
12001 Technology Drive  
Eden Prairie, MN 55344 USA  
T 1(952)828-3000  
[www.Emerson.com](http://www.Emerson.com)

**Emerson**  
835 Innovation Drive  
Knoxville, TN 37932 USA  
T +1 865-675-2400  
F +1 865-218-1401  
[www.Emerson.com](http://www.Emerson.com)

**Emerson**  
Jöbkesweg 3  
48599 Gronau  
Germany  
T +49 2562 709 0  
F +49 2562 709 401  
[www.Emerson.com/ams](http://www.Emerson.com/ams)

©2026, Emerson. All rights reserved.

The contents of this publication are presented for informational purposes only, and while diligent efforts were made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice.

The Emerson logo is a trademark and service mark of Emerson Electric Co. The AMS logo is a mark of one of the Emerson family of companies. All other marks are the property of their respective owners.

